

# Microbiological incubators

## Basic incubation applications



- Ideal for microbiological incubation and heated storage
- Maximum temperature 75°C
- Single set point digital control
- Inner glass door for minimal disturbance while viewing samples
- Stackable, no tools or kit required
- Access port standard
- Stainless steel interior
- Two year parts and labour warranty
- CE marked
- Two perforated stainless steel shelves included as standard
- Extra shelves also available



### Specifications and ordering information

Cat. No	15895901	15815911	15835911
Chamber size, L	75	117	194
Convection	Gravity	Gravity	Gravity
Temperature range	Ambient +7 to 75°C	Ambient +7 to 75°C	Ambient +7 to 75°C
Uniformity at 37°C	±0.8°C	±0.8°C	±0.8°C
Stability at 37°C	±0.3°C	±0.3°C	±0.3°C
Internal dimensions (d x w x h) mm	414 x 354 x 508	414 x 464 x 608	589 x 464 x 708
External dimensions <sup>1</sup> (d x w x h) mm	565 x 530 x 720	565 x 640 x 820	738 x 640 x 920
Shelves supplied/max	2/13	2/16	2/19
Shelf load, kg	25	25	25
Extra shelf Cat. No	15876392	15886392	15896392
Shelf dimensions, mm	329 x 376	439 x 376	439 x 551
Electrical/Plug type	230V, 50/60Hz, 140W, 0.6A CEE7/7 plug for EU and BS1363/A for UK	230V, 50/60Hz, 185W, 0.8A CEE7/7 plug for EU and BS1363/A for UK	230V, 50/60Hz, 345W, 1.5A CEE7/7 plug for EU and BS1363/A for UK
Unit weight, kg	41	47	66

<sup>1</sup>Depth of handle/display not included in depth (65mm), adjustable feet not included in height (35mm) – required distance to rear wall: 80mm.  
Note: All figures in table are typical average values for series devices, based on factory standard following norm DIN12880.

Find out more at [eu.fishersci.com/go/fisherbrand](http://eu.fishersci.com/go/fisherbrand)

Austria: +43(0)800-20 88 40 Belgium: +32 (0)56 260 260 Denmark: +45 70 27 99 20  
Germany: +49 (0)2304 9325 Ireland: +353 (0)1 885 5854 Italy: +39 02 950 59 478  
Finland: +358 (0)9 8027 6280 France: +33 (0)3 88 67 14 14 Netherlands: +31 (0)20 487 70 00  
Norway: +47 22 95 59 59 Portugal: +351 21 425 33 50 Spain: +34 902 239 303  
Sweden: +46 31 352 32 00 Switzerland: +41 (0)56 618 41 11 UK: +44 (0)1509 555 500