


CATALOG NO.....:	130-4020		130-4045	
SIZE/NOM. CAPACITY (mL):	150		150	
UPPER BRIM CAP. (mL)....:	190		190	
NOM. WT (gms).....:	70		70	
MEMBRANE PORE SIZE (µm):	0.2		0.45	
	INCHES	MM	INCHES	MM
A DIA. (UPPER I.D.).....:	2.82 ±0.04	71.6 ±1.0	2.82 ±0.04	71.6 ±1.0
B DIA. (COVER O.D.).....:	3.01 ±0.04	76.5 ±1.0	3.01 ±0.04	76.5 ±1.0
C (W/ ADAPTER).....:	5.00 ±0.06	127.0 ±1.5	5.00 ±0.06	127.0 ±1.5
D DIA. (LOWER BASE).....:	2.80 ±0.04	71.1 ±1.0	2.80 ±0.04	71.1 ±1.0
H (W/ COVER).....:	5.44 ±0.06	138.2 ±1.5	5.44 ±0.06	138.2 ±1.5

COMPONENT	MATERIAL
ADAPTER.....	WHITE LOPE
VENT PLUG.....	CA
LOWER.....	PS
O-RING.....	SILICONE
UPPER.....	PPCO
SUPPORT PLATE...	BLUE PS
MEMBRANE.....	CN
COVER.....	PS



SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE IN CHINA	CARNEY	APP'D PVC	1/11/96	PSS-00-0130-40XX-1	REV. 0196
DESCRIPTION: ANALYTICAL FILTER UNITS					