


CAT. NO.....:	290-3320		290-3345		290-4520		290-4545	
PORE SIZE (um).....:	0.2		0.45		0.2		0.45	
UPPER CAP. (mL).....:	150		150		150		150	
BOTTLE NECK SIZE.....:	33nn		33nn		45nn		45nn	
MEMBRANE COLOR.....:	WHITE		WHITE		WHITE		WHITE	
MEMBRANE DIA (nn)....:	50		50		50		50	
	INCHES	MM	INCHES	MM	INCHES	MM	INCHES	MM
A (UPPER I.D.).....:	3.15	80.0	3.15	80.0	3.15	80.0	3.15	80.0
B HEIGHT.....:	3.6	91	3.6	91	3.6	91	3.6	91
C DIA (BASE).....:	1.4	36	1.4	36	1.9	48	1.9	48
D DIM.....:	2.5	64	2.5	64	3.0	76	3.0	76
NOM. WT. (gms).....:	38		38		40		40	

MATERIALS	
UPPER CONTAINER	PS
COVER	PS
COLLAR	YELLOW PS
ADAPTOR	WHITE LOPE
GASKET	FOAMED LOPE
MEMBRANE	SFCA
VENT PLUG	CA

NOTES:

- ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
- THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE	MC ²	APP'D	PVC	PSS 00-0290-XXXX	REV. 0802
CHK'D	PVC	8/27/02			
DESCRIPTION:					
BOTTLE TOP FILTERS					