


CATALOG NUMBER.....	145-0020		145-0045		145-2020		145-2045	
NOM. CAP. (mL).....	100		100		250		250	
MEMBRANE DIA (mm)...	47		47		47		47	
MEMBRANE COLOR/GRID:	WHITE/NONE		WHITE/GRAY		WHITE/NONE		WHITE/GRAY	
PORE SIZE (µm).....	0.2		0.45		0.2		0.45	
NOM. WT. (gms).....	30		30		40		40	
	INCH	MM	INCH	MM	INCH	MM	INCH	MM
A (UPPER I.D.).....	2.1	53	2.1	53	2.8	71	2.8	71
B (COVER O.D.).....	2.4	61	2.4	61	3.0	77	3.0	77
C (SUPPORT I.D.)....	2.0	51	2.0	51	2.0	51	2.0	51
E (BODY HEIGHT).....	2.9	74	2.9	74	3.9	99	3.9	99
H (OVERALL HEIGHT)..	5.0	127	5.0	127	6.0	152	6.0	152

CATALOG NUMBER.....	147-0045	
NOM. CAP. (mL).....	100	
MEMBRANE DIA (mm)...	47	
MEMBRANE COLOR/GRID:	GRAY/WHITE	
PORE SIZE (µm).....	0.45	
NOM. WT. (gms).....	30	
	INCH	MM
A (UPPER I.D.).....	2.1	53
B (COVER O.D.).....	2.4	61
C (SUPPORT I.D.)....	2.0	51
E (BODY HEIGHT).....	2.9	74
H (OVERALL HEIGHT)..	5.0	127

MATERIALS	
COVER	CLEAR PS
UPPER	PPCO
FUNNEL SUPPORT	BLUE PS
FUNNEL ADAPTOR	PP
MEMBRANE	CN
SUPPORT PAD	CELLULOSE



SPECS ON BACK

NOT TO SCALE

- NOTES:
1. ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
 2. THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE	MC ²	APP'D	PVC	PSS 00-14X-00XX	REV.
CK'D	PVC		3/25/04		0304
DESCRIPTION:					
ANALYTICAL TEST FILTER FUNNELS					