


CATALOG NO.	NOMINAL CAPACITY, (oz)						MATERIALS	
							BOTTLE	CLOSURE
312085	1	2	4	8	16	32	OPAQUE AMBER HDPE	OPAQUE AMBER PP

SIZE CODE.....:	-0001		-0002		-0004	
SIZE (NOM VOL mL/oz):	30/1		60/2		125/4	
NOM. BRIM CAP. (mL):	34		63		143	
NECK FINISH (mm)....:	20-415		20-415		24-415	
THREAD (T.P.I.).....:	8		8		8	
NOM. WEIGHT W/CLOSURE (gms).....:	8		12		16	
	INCH	MM	INCH	MM	INCH	MM
A (NECK I.D.).....:	0.54 ±0.02	13.7 ±0.5	0.54 ±0.02	13.7 ±0.5	0.69 ±0.02	17.5 ±0.5
B (HT. W/CLOSURE)....:	2.40 ±0.07	61.0 ±1.8	3.36 ±0.08	85.3 ±2.0	3.97 ±0.08	100.8 ±2.0
C (HT. W/O CLOSURE):	2.30 ±0.07	58.4 ±1.8	3.25 ±0.08	82.6 ±2.0	3.87 ±0.08	98.3 ±2.0
D (DIA).....:	1.35 ±0.05	34.3 ±1.3	1.52 ±0.06	38.6 ±1.5	1.99 ±0.06	50.5 ±1.5
W.T.(NOM. WALL THK):	0.035	0.90	0.035	0.90	0.030	0.76
T (DIA).....:	0.770 ^{+0.020} _{-0.010}	19.56 ^{+0.51} _{-0.25}	0.770 ^{+0.020} _{-0.010}	19.56 ^{+0.51} _{-0.25}	.930 ±0.020	23.62 ±0.51

SIZE CODE.....:	-0008		-0016		-0032	
SIZE (NOM VOL mL/oz):	250/8		500/16		1000/32	
NOM. BRIM CAP. (mL):	289		525		1090	
NECK FINISH (mm)....:	24-415		28-415		38-430	
THREAD (T.P.I.).....:	8		6		6	
NOM. WEIGHT W/CLOSURE (gms).....:	26		40		78	
	INCH	MM	INCH	MM	INCH	MM
A (NECK I.D.).....:	0.69 ±0.02	17.5 ±0.5	0.84 ±0.02	21.3 ±0.5	1.080 ±0.025	27.4 ±0.6
B (HT. W/CLOSURE)....:	5.23 ±0.08	132.8 ±2.0	6.73 ±0.09	170.9 ±2.3	8.51 ±0.10	216.2 ±2.5
C (HT. W/O CLOSURE):	5.14 ±0.08	130.6 ±2.0	6.61 ±0.09	167.9 ±2.3	8.37 ±0.10	212.6 ±2.5
D (DIA).....:	2.40 ±0.07	61.0 ±1.8	2.87 ±0.08	72.9 ±2.0	3.60 ±0.08	91.4 ±2.0
W.T.(NOM. WALL THK):	0.030	0.76	0.040	1.02	0.035	0.90
T (DIA).....:	.930 ±0.020	23.62 ±0.51	1.082 ±0.010	27.48 ±0.25	1.460 ±0.020	37.08 ±0.51

NOTES:

- ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
- THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE TL	APP'D	PSS 31-2085-XXXX-S	REV.
CK'D DM	GRP		1209
DESCRIPTION: NARROW MOUTH, ROUND PACKAGING BOTTLES			