
thermo scientific



Your samples – our obsession



Thermo Scientific GP Series Freezers

Reliable sample protection and storage

Ideal for the demanding requirements of daily lab applications, our range of general purpose (GP) freezers.

Our line of GP Series freezers provide the reliability and security essential for the protection of sensitive lab samples in the -30°C range.

Thermo Scientific GP Series freezers deliver the performance, security and quality features you have come to depend on from us.

- Freezer capacities of 24, 34, and 48 cu. ft
- Exceptional security features
- Outstanding temperature stability
- Intuitive digital controls
- Quality, robust construction



Thermo Scientific GP Series Freezer

Thermo Scientific GP Series Freezers

Reliable cold storage for general-purpose applications

Our GP Series freezers offer the dependability and safety required for your daily lab applications.

- Range of sizes to suit your lab space needs
- · Stainless steel interior finish
- Available with or without chart recorders

Performance

- Freezer cabinet temperature range: -12° to -30°C (factory setpoint -30°C)
- Digital temperature controller with intuitive interface
- High-density, fluorine free insulation
- Automatic defrost



Security

- Keyed on/off switch
- Optional chart recorder
- High/Low Temperature, Visual/Audio alarms
- Keyed door lock
- Easily accessible contacts for backup monitoring
- Door ajar alarm
- Control panel with key lock

Quality

- Painted, high-quality steel exterior
- Stainless steel interior
- Casters for easy mobility with leveling for better stability
- Noise levels quiet refrigeration system
- 1" rear access port
- Certifications: UL listed

Thermo Scientific GP Series Freezers

Reliable sample protection and storage

Thermo Scientific

GP Series Freezers

Cat. No.	Cap., cu ft.	Voltage	Plug Type	Interior Finish	Doors	No. of Shelves	Interior Dimensions D x W x H	Exterior Dimensions* D x W x H	Chart Re- corder	Shipping Weight, Ibs.
MF25SS-SAEE-TS	24	115V 60Hz	5-15P	Stainless Steel	Solid stainless- steel door, single	3	28 x 22 x 60"	32 x 26 x 78.5" (Add 1 3/4" to Depth for handle)	No	392
MF25SS-SARE-TS	24	115V 60Hz	5-15P	Stainless Steel	Solid stainless- steel door, single	3	28 x 22 x 60"	32 x 26 x 78.5" (Add 1 3/4" to Depth for handle)	Yes	392
MF34SS-SAEE-TS	34	115V 60Hz	5-15P	Stainless Steel	Solid stainless- steel door, single	3	28 x 31 x 60"	32 x 35 x 78.5" (Add 1 3/4" to Depth for handle)	No	429
MF34SS-SARE-TS	34	115V 60Hz	5-15P	Stainless Steel	Solid stainless- steel door, single	3	28 x 31 x 60"	32 x 35 x 78.5" (Add 1 3/4" to Depth for handle)	Yes	429
MF49SS-SAEE-TS	48	208- 230V 60Hz	L14- 20	Stainless Steel	Solid stainless- steel door, double	6	28 x 48 x 60"	32 x 52 x 78.5" (Add 1 3/4" to Depth for handle)	No	630
MF49SS-SARE-TS	48	208- 230V 60Hz	L14- 20	Stainless Steel	Solid stainless- steel door, double	6	28 x 48 x 60"	32 x 52 x 78.5" (Add 1 3/4" to Depth for handle)	Yes	630

^{*} Add 3" to exterior height if using provided standard casters

Services designed to help you achieve your goals!

Responsive and knowledgeable laboratory service is only a phone call or email away, providing you with peace of mind:

- Increased equipment uptime, ensuring continuity of operations
- Broad network of factory trained and certified technicians
- Convenient and dependable access to our expertise and original parts
- A fixed cost solution with service maintenance options

Thermo Scientific Labware

Thermo Scientific plastic and glass labware offer a complete range of tubes, bottles, flasks and vials for all of your cold storage applications.

Our labware products are designed and manufactured for tough applications under rigorous laboratory conditions. For more information, visit

thermofisher.com/labwareandsupplies

Find out more at thermofisher.com/cold

