

Disposable inoculating loops and needles

Start sample growth analysis the right way with proper specimen setup

Color-coded Fisherbrand™ disposable inoculating loops and needles are precision-molded from USP Class VI—compliant, nontoxic, rigid polystyrene (PS) material. They are flexible, providing a smooth loop surface, and are ideal for a wide range of applications within the microbiology environment, including plating fluid samples, as well as more viscous samples, such as pus and feces. Needles are ideal for picking individual colonies and for stab inoculations in solid media. Loops enable accurate volume transfer and eliminate the potential of cross contamination during everyday sample handling.

Features and benefits include:

- **Loops available in 1 µL and 10 µL sizes**—calibrated using the Evans blue dye method
- **Flexible combinations**—choose from both loop–needle and loop–loop options
- **Enhanced droplet adhesion**—treated surface enables correct droplet size and complete transfer from the loop
- **Smooth loop surface**—prevents gouging of the media
- **Flexible and rigid product offerings**—get the right product for the right application and touch
- **Supplied sterile in easy-to-open, paper–plastic peel pouches**—choice of individual and 10 packs
- **Square handle with grip**—enables controlled handling and loop rotation
- **No flaming required**—single use, with no potential of harmful aerosols



Product	Loop/needle size	Color	Type	Flexibility/type	Volume	Quantity/pack	Quantity/case	Packs/case	Cat. No.
Inoculating Loop and Needle, flexible, high impact polystyrene (HIPS)	1 µL	Blue	Loop	Flexible	1 µL	960	9,600	10	22-363-595
Inoculating Needle, flexible, HIPS	Needle	Natural	Needle	Flexible	N/A	960	9,600	10	22-363-596
Inoculating Loop and Needle, flexible, HIPS	10 µL	Yellow	Loop	Flexible	10 µL	960	9,600	10	22-363-597
Inoculating Loop and Needle, flexible, HIPS, individually wrapped	10 µL	Yellow	Loop	Flexible	10 µL	250	250	1	22-363-600
Combo Inoculation Fisherbrand Combi Loop loop, flexible, HIPS	1 µL, 10 µL	White	Loop	Flexible	1 µL, 10 µL	250	250	1	22-363-601
Flexible Inoculating Combi Loop loop, HIPS	1 µL, 10 µL	White	Loop	Flexible	1 µL, 10 µL	500	5,000	10	22-363-602
Inoculating Loop and Needle, flexible, HIPS, individually wrapped	1 µL	Blue	Loop	Flexible	1 µL	250	250	1	22-363-608
Inoculating Loop and Needle, rigid, PS	1 µL	Clear	Loop	Rigid	1 µL	1,000	1,000	1	22-363-598
Inoculating Loop and Needle, rigid, PS, individually wrapped	10 µL	Blue	Loop	Rigid	10 µL	1,000	1,000	1	22-363-599
Inoculating Loop and Needle, rigid, PS, individually wrapped	1 µL	Blue	Loop	Rigid	1 µL	250	250	1	22-363-603
Inoculating Loop and Needle, rigid, PS	1 µL	Blue	Loop	Rigid	1 µL	960	9,600	10	22-363-604
Inoculating Loop and Needle, rigid, PS, individually wrapped	10 µL	Yellow	Loop	Rigid	10 µL	250	250	1	22-363-605
Inoculating Loop and Needle, rigid, PS	10 µL	Yellow	Loop	Rigid	10 µL	1,000	1,000	1	22-363-606
Inoculating Loop and Needle, rigid, PS	10 µL	Yellow	Loop	Rigid	10 µL	960	9,600	10	22-363-607



Find out more at fishersci.com/loops-needles and fishersci.ca/loops-needles

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com

Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca

Call customer service: 1-800-234-7437

