

SENSITITRE™ GRAM POSITIVE NARMS PLATE FORMAT

Plate Code: **CMV3AGPF**

	1	2	3	4	5	6	7	8	9	10	11	12
A	TGC 0.015	TGC 0.03	TGC 0.06	TGC 0.12	TGC 0.25	TGC 0.5	ERY 0.25	ERY 0.5	ERY 1	ERY 2	ERY 4	ERY 8
B	TET 1	TET 2	TET 4	TET 8	TET 16	TET 32	CIP 0.12	CIP 0.25	CIP 0.5	CIP 1	CIP 2	CIP 4
C	CHL 2	CHL 4	CHL 8	CHL 16	CHL 32	PEN 0.25	PEN 0.5	PEN 1	PEN 2	PEN 4	PEN 8	PEN 16
D	DAP 0.25	DAP 0.5	DAP 1	DAP 2	DAP 4	DAP 8	DAP 16	VAN 0.25	VAN 0.5	VAN 1	VAN 2	VAN 4
E	STR 512	STR 1024	STR 2048	NIT 2	NIT 4	NIT 8	NIT 16	NIT 32	NIT 64	VAN 8	VAN 16	VAN 32
F	TYLT 0.25	TYLT 0.5	TYLT 1	TYLT 2	TYLT 4	TYLT 8	TYLT 16	TYLT 32	GEN 128	GEN 256	GEN 512	GEN 1024
G	SYN 0.5	SYN 1	SYN 2	SYN 4	SYN 8	SYN 16	SYN 32	LIN 1	LIN 2	LIN 4	LIN 8	NEG
H	LZD 0.5	LZD 1	LZD 2	LZD 4	LZD 8	KAN 128	KAN 256	KAN 512	KAN 1024	POS	POS	POS

ANTIMICROBICS

TGC	Tigecycline
TET	Tetracycline
CHL	Chloramphenicol
DAP	Daptomycin
STR	Streptomycin
TYLT	Tylosin tartrate
SYN	Quinupristin / dalfopristin
LZD	Linezolid
NIT	Nitrofurantoin
PEN	Penicillin
KAN	Kanamycin
ERY	Erythromycin
CIP	Ciprofloxacin
VAN	Vancomycin
LIN	Lincomycin
GEN	Gentamicin
POS	Positive Control
NEG	Negative Control