

836 North Street - Life Sciences
Tewksbury MA 01876 USA
www.corning.com/lifesciences
Refer to website for regional contact information.

Page: 1 / 1

Product Name	: Cell Strainer 40um Blue 1pk	Manufacture Date	: 2025-06-18
Catalog Number	: 352340		
Lot ID	: 277423		
Expiration Date	: Unconfirmed Validity		

Quality Management System - Complies with the current version of the EN ISO 13485 Standard and the FDA CFR 21 Part 820, current Good Manufacturing Practices (cGMP).

BSE/TSE - Product complies with the latest revision of EMA/410/01 "Note for Guidance on minimising the risk of transmitting animal spongiform encephalopathy agents via human and veterinary medicinal products" by virtue of all bovine derived material having been processed per specific conditions of section 6.4 of EMA/410/01.

USP Class VI Testing - All material resin is tested, qualified and shown to be non-toxic as established in the Standards USP Class VI Chapter<87>, "Biological reactivity Tests, in Vitro" and Chapter<88>, "Biological Reactivity Tests, in vivo".

Non-Pyrogenic - Tested and met the criteria established in the current version of United States Pharmacopeia (USP) Chapter <85>, "Bacterial Endotoxins Test". The acceptance level for product is ≤ 0.125 EU/ml or ≤ 5 EU/device.

Sterility - Product has been sterilized and dosimetrically released per the requirements of ANSI/AAMI/ISO 11137, "Sterilization of health care products- Radiation". Products meet a minimum Sterility Assurance Level (SAL) of 10^{-3} .

Quality Control Testing - Representative production samples are collected and inspected in accordance with current applicable product specifications. Inspection records are reviewed and approved by qualified personnel for product release.

- This product met Corning Incorporated - Life Sciences' high standards of quality at the time of batch/lot release.



ANDREW J (ANDY) FRANKS
CMO Quality Manager