

Test Report

– Eppendorf PCR clean –

1 Set epT.I.P.S.[®] Motion Reloads

20 - 300 µL, 2304 pcs.
Eppendorf Filtertips in Trays
PCR clean



Read the instruction for use on
www.eppendorf.com/manuals



2026-12-28

LOT K200430R

Eppendorf AG
22331 Hamburg · Germany
E-Mail: eppendorf@eppendorf.com
www.eppendorf.com

Order no.: 0030 014.472

Distributed in North America by
Eppendorf North America, Inc. · USA
E-Mail: info@eppendorf.com
www.eppendorfnna.com

Made in Germany

Cat. no.: 0030014472

eppendorf

• **Human DNA**

Method: *real-time* PCR acc. to SOP 99880/V2
Limit: < 2 pg; less than one human cell

• **DNase**

Method: DNA Digestion acc. to SOP 100570/V1
Limit: Not detectable (LOD: 1.0×10^{-6} Kunitz units)

• **PCR inhibition**

Method: *real-time* PCR acc. to SOP 100559/V1
Limit: Less than 10 targets amplifiable

• **RNase**

Method: RNA Digestion acc. to SOP 100571/V1
Limit: Not detectable (LOD: 1.0×10^{-9} Kunitz units)

Customer: Eppendorf AG, Barkhausenweg 1, D-22339 Hamburg

Date of sample receipt / examination:

Testing of the above described lot showed conformity within the limits of detection.

16.12.21
Date of release

Epp 2112-9978
Registration number

Fr. Weigel
Dipl.-Biol. Thomas Weigel (Head)

The test results refer exclusively to the items tested as arrived. The test report must not be copied partially without the approval of LADR GmbH.

page 1 of 1