

Test Report – Eppendorf Consumables –

1 Set Conical Tubes 50 mL, BioBased

Screw cap, sterile, free of detectable
pyrogens, RNase & DNase, DNA
500 Eppendorf Tubes[®] (25/bag)

 2030-04 -28

  Read the instructions for use on
www.eppendorf.com/manuals

REF 0030 122 542
GTIN 04043758040399
LOT 0220334J

  **STERILE R**
 (01) 04043758040399
(10) 0220334J
(17) 300428
(240) 0030122542
(30) 1



 Eppendorf SE
Barkhausenweg 1
22339 Hamburg · Germany
eppendorf@eppendorf.com
www.eppendorf.com

Distributed in North America by
Eppendorf North America, Inc. · USA
info@eppendorf.com
www.eppendorfna.com

Made in Germany

eppendorf

• **Human DNA**

Method: *real-time* PCR acc. to SOP 99880/V8
Limit: < 2 pg; less than one human cell

• **Bacterial DNA**

Method: *real-time* PCR acc. to SOP 100567/V5
Limit: < 50 fg; less than 10 *E. coli* cells

• **DNase**

Method: DNA Digestion acc. to SOP 100570/V4
Limit: Not detectable
(LOD: 1.0×10^{-7} Kunitz units)

• **RNase**

Method: RNA Digestion acc. to SOP 100571/V4
Limit: Not detectable
(LOD: 1.0×10^{-9} Kunitz units)

• **Sterility**

Method: Sterilization with SAL 10^{-6} by
 Irradiation according DIN EN ISO 11137
Test method: USP, Ph. Eur. 10.0 / 2.6.12

• **Endotoxin**

Method: Kinetic-chromogenic LAL test (Ph. Eur. 10.0 / 2.6.14)
Limit: < 0.001 EU/mL

Customer: Eppendorf SE, Barkhausenweg 1, D-22339 Hamburg

Date of sample receipt / examination: 09.07.25

Testing of the rinse solution of the above described lot showed conformity within the limits of detection.

16.07.25
Date of release

Epp 2807-6022
Registration number

i.v. P. Kuhnert
Dr. rer. nat. Sybille Kuhnert (Head)

The test results refer exclusively to the items tested as arrived. The test report must not be copied partially without the approval of LADR GmbH.

page 1 of 1