

CERTIFICATE OF CONFORMITY & CERTIFICATE OF ANALYSIS

Brand	Nitrilite®
Size(s)	S (6.5 - 7),M (7.5 - 8),L (8.5 - 9),XL (9.5 - 10)
Material	Nitrile
Style	93-401
Short Description	Non-sterile Disposable Nitrile Cleanroom Glove
Lot Number	2501EV
Batch Number	25014014EV
Manufacturing Date	2025-01
Expiration Date	2029-12

DECLARATION OF CONFORMITY

Ansell certifies that the above product is manufactured in accordance with Ansell product specifications and is in conformity with the following standards or normative documents:

Standard/Normative Document	Result
FDA 21 CFR 177-2600	Conforms
Free from BSE/TSE (EMA/410/01)	Conforms
PPER (EU) 2016/425	Conforms
Reach Regulation	Conforms

DECLARATION OF ANALYSIS

Property	Test Method	Specification	Result
Glove Length (mm)	ASTM D3767/EN420	Min. 300	Conforms
Palm Thickness (mm)	ASTM D3767/EN420	0.09-0.13	Conforms
Tensile Strength (MPa)	ASTM D412	Min. 18	Conforms
Ultimate Elongation (%)	ASTM D412	Min. 500	Conforms
Freedom from Holes - Final Release	EN455-1/ASTM D3577	G1, AQL 1.5	Conforms
Liquid Particle Count 0.5-20 µ (particles/cm²)	IEST-RP-CC005.4	<400	Conforms
Non Volatile Residue NVR (µg/cm²)	IEST-RP-CC005.4	<5.0	Conforms
Silicone, Amide, DOP - FTIR	IEST-RP-CC005.4	Not detectable	Conforms
Aluminium Al3+ (µg/cm²)	IEST-RP-CC005.4	<0.010	Conforms
Calcium Ca2+ (µg/cm²)	IEST-RP-CC005.4	<0.300	Conforms
Iron Fe <0.01 µg/cm²	IEST-RP-CC005.4	<0.010	Conforms
Chloride Cl- (µg/cm²)	IEST-RP-CC005.4	<0.200	Conforms
Copper Cu2+ (µg/cm²)	IEST-RP-CC005.4	<0.0004	Conforms
Lithium Li+ (µg/cm²)	IEST-RP-CC005.4	<0.0001	Conforms
Magnesium Mg2+ (µg/cm²)	IEST-RP-CC005.4	<0.001	Conforms
Nitrate NO3- (µg/cm²)	IEST-RP-CC005.4	<0.100	Conforms

Property	Test Method	Specification	Result
Potassium K+ ($\mu\text{g}/\text{cm}^2$)	IEST-RP-CC005.4	<0.020	Conforms
Sodium Na+ ($\mu\text{g}/\text{cm}^2$)	IEST-RP-CC005.4	<0.050	Conforms
Sulphate SO ₄ 2- ($\mu\text{g}/\text{cm}^2$)	IEST-RP-CC005.4	<0.010	Conforms
Zinc Zn ²⁺ ($\mu\text{g}/\text{cm}^2$)	IEST-RP-CC005.4	<0.050	Conforms

Electronically Signed by:

Amy Jones

Manager, QA

Date: 7 February 2025

For additional information visit us at www.ansell.com, or call us at:

Europe, Middle East & Africa Region

Ansell Healthcare Europe N.V.

T: +32 (0) 2 528 74 00

F: +32 (0) 2 528 74 01

Australia

Ansell Limited

T: +61 1800 337 041

F: +61 1800 803 578

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.

T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare products LLC

T: +1 800 800 0444

F: +1 800 800 0445

Asia Pacific Region

Ansell Global Trading Center

(Malaysia) Sdn Bhd

T: +603 8310 6688

F: +603 8310 6699