

CERTIFICATE OF CONFORMITY & CERTIFICATE OF ANALYSIS

Brand	TouchNTuff®
Size(s)	S (6.5 - 7),M (7.5 - 8),L (8.5 - 9),XL (9.5 - 10)
Material	Nitrile
Style	93-700
Short Description	Sterile Disposable Nitrile Cleanroom Glove
Lot Number	2502SW
Batch Number	25027002SW
Manufacturing Date	2025-02
Expiration Date	2028-01

CERTIFICATE OF CONFORMITY

Ansell certifies that the above product is manufactured in accordance with Ansell product specifications and is in conformity with the following standards or normative documents:

Standard/Normative Document	Result
FDA 21 CFR 177-2600	Conforms
Free from BSE/TSE (EMA/410/01)	Conforms
ISO 11137-1	Conforms
PPER (EU) 2016/425	Conforms
Reach Regulation	Conforms

CERTIFICATE OF ANALYSIS

Property	Test Method	Specification	Result
Freedom from Holes - Final Release	EN455-1/ASTM D5151	G1, AQL 1.5	Conforms
Dimension Test	ASTM D3767	S-2, AQL 4.0	Conforms
Glove Length (mm)	ASTM D3767	Min. 300	Conforms
Palm Thickness (mm)	ASTM D3767	0.11-0.15	Conforms
Finger Thickness (mm)	ASTM D3767	0.14–0.20	Conforms
Physical Properties	ASTM D412	S-2, AQL 4.0	Conforms
Tensile Strength (MPa)	ASTM D412	Min. 14	Conforms
Ultimate Elongation (%)	ASTM D412	Min. 500	Conforms
Liquid Particle Count 0.5-20 µ (particles/cm ²)	IEST-RP-CC005.4	< 1200	Conforms
Aluminium Al ³⁺ (µg/cm ²)	IEST-RP-CC005.4	<0.050	Conforms
Calcium Ca ²⁺ (µg/cm ²)	IEST-RP-CC005.4	<0.500	Conforms
Chloride Cl ⁻ (µg/cm ²)	IEST-RP-CC005.4	<0.600	Conforms
Copper Cu ²⁺ (µg/cm ²)	IEST-RP-CC005.4	<0.050	Conforms
Iron Fe ³⁺ (µg/cm ²)	IEST-RP-CC005.4	<0.050	Conforms
Lithium Li ⁺ (µg/cm ²)	IEST-RP-CC005.4	<0.0004	Conforms

Property	Test Method	Specification	Result
Magnesium Mg ²⁺ (µg/cm ²)	IENT-RP-CC005.4	<0.050	Conforms
Nitrate NO ₃ ⁻ (µg/cm ²)	IENT-RP-CC005.4	<0.8	Conforms
Potassium K ⁺ (µg/cm ²)	IENT-RP-CC005.4	<0.050	Conforms
Protein Content (µg/g)	EN 455-3	Not applicable	Not applicable
Silicone, Amide, DOP - FTIR	IENT-RP-CC005.4	Not detectable	Conforms
Sodium Na ⁺ (µg/cm ²)	IENT-RP-CC005.4	<0.500	Conforms
Sulphate SO ₄ 2 ⁻ (µg/cm ²)	IENT-RP-CC005.4	<0.200	Conforms
Zinc Zn ²⁺ (µg/cm ²)	IENT-RP-CC005.4	<0.300	Conforms

Electronically Signed by:

Amy Jones

Manager, QA

Date: 2 April 2025

For additional information visit us at www.ansell.com, or call us at:

Europe, Middle East & Africa Region

Ansell Healthcare Europe N.V.

T: +32 (0) 2 528 74 00

F: +32 (0) 2 528 74 01

Australia

Ansell Limited

T: +61 1800 337 041

F: +61 1800 803 578

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.

T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare products LLC

T: +1 800 800 0444

F: +1 800 800 0445

Asia Pacific Region

Ansell Global Trading Center

(Malaysia) Sdn Bhd

T: +603 8310 6688

F: +603 8310 6699