

## CERTIFICATE OF CONFORMITY & CERTIFICATE OF ANALYSIS

|                    |                                                 |
|--------------------|-------------------------------------------------|
| Brand              | TouchNTuff®                                     |
| Size(s)            | 6.5                                             |
| Material           | PI (Polyisoprene)                               |
| Style              | 83-500                                          |
| Short Description  | Sterile Disposable Polyisoprene Cleanroom Glove |
| Lot Number         | 250105                                          |
| Batch Number       | 2501061805                                      |
| Manufacturing Date | 2025-01                                         |
| Expiration Date    | 2029-12                                         |

### CERTIFICATE OF CONFORMITY

Ansell certifies that the above product is manufactured in accordance with Ansell product specifications and is in conformity with the following standards or normative documents:

| Standard/Normative Document    | Result   |
|--------------------------------|----------|
| FDA 21 CFR 177-2600            | Conforms |
| Free from BSE/TSE (EMA/410/01) | Conforms |
| ISO 11137-1                    | Conforms |
| PPER (EU) 2016/425             | Conforms |
| Reach Regulation               | Conforms |

### CERTIFICATE OF ANALYSIS

| Property                                                    | Test Method        | Specification  | Result         |
|-------------------------------------------------------------|--------------------|----------------|----------------|
| Freedom from Holes - Final Release                          | EN455-1/ASTM D3577 | G1, AQL 0.65   | Conforms       |
| Dimension Test                                              | ASTM D3767         | S-2, AQL 4.0   | Conforms       |
| Glove Length (mm)                                           | ASTM D3767         | Min. 295       | Conforms       |
| Palm Thickness (mm)                                         | ASTM D3767         | 0.17 – 0.25    | Conforms       |
| Physical Properties                                         | ASTM D412          | S-2, AQL 4.0   | Conforms       |
| Tensile Strength (MPa)                                      | ASTM D412          | Min. 17        | Conforms       |
| Ultimate Elongation (%)                                     | ASTM D412          | Min. 650       | Conforms       |
| Modulus at 500% elongation (MPa)                            | ASTM D412          | Max. 7.0       | Conforms       |
| Tensile Strength (MPa) after accelerated aging              | ASTM D412          | Min. 12        | Conforms       |
| Ultimate Elongation (%) after accelerated aging             | ASTM D412          | Min. 490       | Conforms       |
| Liquid Particle Count 0.5-20 µ (particles/cm <sup>2</sup> ) | IEST-RP-CC005.4    | ≤2500          | Conforms       |
| Residual Powder Content (mg/glove)                          | ASTM D6124         | Max. 2.0       | Conforms       |
| Protein Content (µg/g)                                      | EN 455-3           | Not applicable | Not applicable |



Electronically Signed by:

**Amy Jones**

Manager, QA

Date: 30 April 2025

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at:

**Europe, Middle East & Africa Region**

Ansell Healthcare Europe N.V.

T: +32 (0) 2 528 74 00

F: +32 (0) 2 528 74 01

**Australia**

Ansell Limited

T: +61 1800 337 041

F: +61 1800 803 578

**Latin America & Caribbean Region**

Ansell Commercial Mexico S.A. de C.V.

T: +52 442 248 1544 / 248 3133

**North America Region**

Ansell Healthcare products LLC

T: +1 800 800 0444

F: +1 800 800 0445

**Asia Pacific Region**

Ansell Global Trading Center

(Malaysia) Sdn Bhd

T: +603 8310 6688

F: +603 8310 6699