

## CERTIFICATE OF CONFORMITY & CERTIFICATE OF ANALYSIS

|                    |                                                               |
|--------------------|---------------------------------------------------------------|
| Brand              | TouchNTuff®                                                   |
| Size(s)            | 8.5                                                           |
| Material           | Neoprene (Polychloroprene)                                    |
| Style              | 73-500                                                        |
| Short Description  | Sterile Disposable Neoprene (Polychloroprene) Cleanroom Glove |
| Lot Number         | 250305                                                        |
| Batch Number       | 2503058805                                                    |
| Manufacturing Date | 2025-03                                                       |
| Expiration Date    | 2030-02                                                       |

### CERTIFICATE OF CONFORMITY

Ansell certifies that the above product is manufactured in accordance with Ansell product specifications and is in conformity with the following standards or normative documents:

| Standard/Normative Document    | Result   |
|--------------------------------|----------|
| FDA 21 CFR 177-2600            | Conforms |
| Free from BSE/TSE (EMA/410/01) | Conforms |
| ISO 11137-1                    | Conforms |
| PPER (EU) 2016/425             | Conforms |
| Reach Regulation               | Conforms |

### CERTIFICATE OF ANALYSIS

| Property                                                    | Test Method        | Specification  | Result         |
|-------------------------------------------------------------|--------------------|----------------|----------------|
| Freedom from Holes - Final Release                          | EN455-1/ASTM D3577 | G1, AQL 0.65   | Conforms       |
| Liquid Particle Count 0.5-20 µ (particles/cm <sup>2</sup> ) | TEST-RP-CC005.4    | ≤2500          | Conforms       |
| Dimension Test                                              | ASTM D3767         | S2, AQL 4.0    | Conforms       |
| Glove Length (mm)                                           | ASTM D3767         | Min. 295       | Conforms       |
| Palm Thickness (mm)                                         | ASTM D3767         | 0.10 – 0.15    | Conforms       |
| Physical Properties                                         | ASTM D412          | S-2, AQL 4.0   | Conforms       |
| Tensile Strength (MPa)                                      | ASTM D412          | Min. 17        | Conforms       |
| Ultimate Elongation (%)                                     | ASTM D412          | Min. 650       | Conforms       |
| Modulus at 500% elongation (MPa)                            | ASTM D412          | Max. 7.0       | Conforms       |
| Tensile Strength (MPa) after accelerated aging              | ASTM D412          | Min. 12        | Conforms       |
| Ultimate Elongation (%) after accelerated aging             | ASTM D412          | Min. 490       | Conforms       |
| Residual Powder Content (mg/glove)                          | ASTM D6124         | Max. 2.0       | Conforms       |
| Protein Content (µg/g)                                      | EN 455-3           | Not applicable | Not applicable |



Electronically Signed by:

**Amy Jones**

Manager, QA

Date: 30 May 2025

For additional information visit us at [www.ansell.com](http://www.ansell.com), or contact us at:

**Europe, Middle East & Africa Region**

Ansell Healthcare Europe N.V.

Riverside Business Park

Blvd International, 55

B-1070 Brussels,

Belgium

T: +32 (0) 2 528 74 00

F: +32 (0) 2 528 74 01

**Australia & Asia Pacific Region**

678 Victoria St,

Richmond VIC 3121

Australia

Tel: +61 1800 337 041

Fax: +611 800 803578

Email: [anzcustomerservice@ansell.com](mailto:anzcustomerservice@ansell.com)

**Latin America & Caribbean Region**

Ansell Comercial México S.A. de C.V.

Blvd. Bernardo Quintana 7001-C,

Q7001 Torre 2, Suites 1304-1306 Centro Sur.

Querétaro, Qro. México C.P. 76090

Tel: +52 442 296 2050

Email: [cslac@ansell.com](mailto:cslac@ansell.com)

**North America Region**

Ansell Healthcare products LLC

111 S Wood Ave,

Suite 900 Iselin,

NJ 08830,

United States

T: +1 800 800 0444

F: +1 800 800 0445

CA Tel: +1 800 363 8340

Email: [customerserviceus@ansell.com](mailto:customerserviceus@ansell.com)

**Ansell Brazil Ltda.**

Rua das Figueiras, 474

4º andar - Bairro Jardim

Santo André - SP

CEP: 09080-300 – Brasil

Tel: +55 11 3356 3100

Email: [sac@ansell.com](mailto:sac@ansell.com)

Ansell Healthcare Products LLC

2301 Robb Drive,

Reno,

NV 89523,

United States

US Tel: +1 800 800 0444

US Fax: +1 800 800 0445

Email: [customerserviceus@ansell.com](mailto:customerserviceus@ansell.com)