

## CERTIFICATE OF CONFORMITY & CERTIFICATE OF ANALYSIS

Brand	TouchNTuff®
Size(s)	8.5
Material	Neoprene (Polychloroprene)
Style	73-500
Short Description	Sterile Disposable Neoprene (Polychloroprene) Cleanroom Glove
Lot Number	250505
Batch Number	2505050405
Manufacturing Date	2025-05
Expiration Date	2030-04

### CERTIFICATE OF CONFORMITY

Ansell certifies that the above product is manufactured in accordance with Ansell product specifications and is in conformity with the following standards or normative documents:

Standard/Normative Document	Result
FDA 21 CFR 177-2600	Conforms
Free from BSE/TSE (EMA/410/01)	Conforms
ISO 11137-1	Conforms
PPER (EU) 2016/425	Conforms
Reach Regulation	Conforms

### CERTIFICATE OF ANALYSIS

Property	Test Method	Specification	Result
Freedom from Holes - Final Release	EN455-1/ASTM D3577	G1, AQL 0.65	Conforms
Liquid Particle Count 0.5-20 µ (particles/cm <sup>2</sup> )	IEST-RP-CC005.4	<1500	Conforms
Dimension Test	ASTM D3767	S2, AQL 4.0	Conforms
Glove Length (mm)	ASTM D3767	Min. 295	Conforms
Palm Thickness (mm)	ASTM D3767	0.10 – 0.15	Conforms
Physical Properties	ASTM D412	S-2, AQL 4.0	Conforms
Tensile Strength (MPa)	ASTM D412	Min. 17	Conforms
Ultimate Elongation (%)	ASTM D412	Min. 650	Conforms
Modulus at 500% elongation (MPa)	ASTM D412	Max. 7.0	Conforms
Tensile Strength (MPa) after accelerated aging	ASTM D412	Min. 12	Conforms
Ultimate Elongation (%) after accelerated aging	ASTM D412	Min. 490	Conforms
Residual Powder Content (mg/glove)	ASTM D6124	Max. 2.0	Conforms
Protein Content (µg/g)	EN 455-3	Not applicable	Not applicable



Electronically Signed by:

**Amy Jones**

Sr. Manager, QA

Date: 8 July 2025

For additional information visit us at [www.ansell.com](http://www.ansell.com), or contact us at:

**Europe, Middle East & Africa Region**

Ansell Healthcare Europe N.V.

Riverside Business Park

Blvd International, 55

B-1070 Brussels,

Belgium

T: +32 (0) 2 528 74 00

F: +32 (0) 2 528 74 01

**Australia & Asia Pacific Region**

678 Victoria St,

Richmond VIC 3121

Australia

Tel: +61 1800 337 041

Fax: +611 800 803578

Email: [anzcustomerservice@ansell.com](mailto:anzcustomerservice@ansell.com)

**North America Region**

Ansell Healthcare products LLC

111 S Wood Ave,

Suite 900 Iselin,

NJ 08830,

United States

T: +1 800 800 0444

F: +1 800 800 0445

CA Tel: +1 800 363 8340

Email: [customerserviceus@ansell.com](mailto:customerserviceus@ansell.com)

Ansell Healthcare Products LLC

2301 Robb Drive,

Reno,

NV 89523,

United States

US Tel: +1 800 800 0444

US Fax: +1 800 800 0445

Email: [customerserviceus@ansell.com](mailto:customerserviceus@ansell.com)

**Latin America & Caribbean Region**

Ansell Comercial México S.A. de C.V.

Blvd. Bernardo Quintana 7001-C,

Q7001 Torre 2, Suites 1304-1306 Centro Sur.

Querétaro, Qro. México C.P. 76090

Tel: +52 442 296 2050

Email: [cslac@ansell.com](mailto:cslac@ansell.com)

**Ansell Brazil Ltda.**

Rua das Figueiras, 474

4º andar - Bairro Jardim

Santo André - SP

CEP: 09080-300 – Brasil

Tel: +55 11 3356 3100

Email: [sac@ansell.com](mailto:sac@ansell.com)