

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by LRQA. Certificate Number.
10551915

Catalogue Number	022912
Lot Number	II731414
Description	Ethyl acetate, HPLC Grade, 99.5+%
CAS Number	141-78-6
Quality Test/Release Date	25/Apr/2025
Suggested retest date	25/Apr/2030
Country of Origin	Great Britain
Declaration of Origin	Synthetic

Result Name	Units	Specifications	Test Value
Assay (GC)	%	≥99.5%	>99.9
Appearance (Color)		Clear colorless	Clear colourless
Form		Liquid	Liquid
Impurity content		Pesticide Residue Analysis [UK]: Passes Test	Passes Test
Water Content (Karl Fischer Titration)	%	≤0.05% (500ppm) [US] / ≤0.1% (1,000ppm) [UK]	<0.005
Optical Absorbance at	%	255nm: ≤1.00AU [US] / ≥10% transmittance [UK]	>10
Optical Absorbance at	%	260nm: ≥50% transmittance [UK]	>50
Optical Absorbance at	%	265nm: ≥80% transmittance [UK]	>80
Optical Absorbance at	%	270nm: ≥95% transmittance [UK]	>95
Optical Absorbance at	%	310-400nm: ≥99% transmittance [UK]	>99
Residue on Evaporation	ppm	≤3ppm (0.0003%) [US] / ≤2ppm (0.0001%) [UK]	<1



Paul Coleman
Site Quality Manager

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.