

## CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by TUV SUD America Inc.  
 Certificate Number. 951001163

Catalogue Number	041859
Lot Number	T30L717
Description	N,N-Dimethylformamide, HPLC grade, 99.7+%, packaged under Argon in resealable ChemSeal™ bottles
CAS Number	68-12-2
Quality Test/Release Date	29/Jul/2025
Suggested retest date	29/Jul/2030
Country of Origin	United States
Declaration of Origin	Synthetic
BSE/TSE	Not directly derived from or manufactured with any animal byproducts in any way (including but not limited to fermentation or nutrient broth, catalysts, enzymes).

Result Name	Units	Specifications	Test Value
Assay (GC)	%	>/= 99.7%	99.99
Appearance (Color)		Colorless	Colorless
Form		Liquid	Liquid
Water Content (Karl Fischer Titration)	%	0.05%, max	0.004
Residue on Evaporation	ppm	5 ppm, max	4.8
UV/Vis	AU	At 270 nm 1.00 AU, max	0.49
UV/Vis	AU	At 275 nm 0.30 AU, max	0.18
UV/Vis	AU	At 295 nm 0.10 AU, max	0.05
UV/Vis	AU	At 310 nm 0.03 AU, max	0.02
UV/Vis	AU	At 340 nm 0.01 AU, max	0.01



Luis Perez  
 Interim Director Quality, LCD

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.