

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by INTERTEK SAI Global
Certificate Number. QMS42099

Catalogue Number	32573
Lot Number	2545062
Description	Acetonitrile, 99.9 % for HPLC gradient grade ACS meets req. of Reag. Ph. Eur. HPLC for Far UV/gradient analysis
CAS Number	75-05-8
Quality Test/Release Date	15/Jul/2025
Expiry Phrase	Use within 3 years of opening
Country of Origin	China
Declaration of Origin	Synthetic
BSE/TSE	Not directly derived from or manufactured with any animal byproducts in any way (Including but not limited to fermentation or nutrient broth, catalysts, enzymes).

Result Name	Units	Specifications	Test Value
Absorbance @ 190 nm	A.U.	<= 1	0.705
Absorbance @ 195 nm	A.U.	<= 0.1	0.1
Absorbance @ 200 nm	A.U.	<= 0.05	0.04
Absorbance @ 205 nm	A.U.	<= 0.05	0.027
Absorbance @ 210 nm	A.U.	<= 0.02	0.018
Absorbance @ 220 nm	A.U.	<= 0.01	0.009
Absorbance @ 230 nm	A.U.	<= 0.005	0.005
Absorbance @ 240 nm	A.U.	<= 0.005	0.002
Absorbance @ 250 nm	A.U.	<= 0.005	0
Absorbance @ 254 nm	A.U.	<= 0.005	0
Absorbance @ 420 nm	A.U.	<= 0.005	0
Acidity	meq/g	<= 0.0008	0.00002
Alkalinity (meq/g)	meq/g	<= 0.0006	None Detected
Assay (GC)	%	>= 99.85	100.00
Chemical form		Mobile liquid	Mobile liquid
Colour	APHA	<= 10	<5
Density @ 20C (g/ml)	g	>= 0.78 and <= 0.783	0.782
Gradient analysis (max. eluted peak)	A.U.	<= 0.01	None Detected
Gradient analysis Absorbance largest eluted peak	A.U.	<= 0.01	None Detected
LC suitability		Must be 'Pass'	Pass
LC suitability Gradient Elution		Must be 'Pass'	Pass
Refractive index @ 20C, 589nm		>= 1.343 and <= 1.345	1.3438
Residue after evaporation (ppm)	ppm	<= 2	None Detected
Visual colour		Clear colourless	Clear colourless
Water	%	<= 0.01	0.003

Additional Information Filtered through 0.2 micron

A. Ganatra

Ashok Ganatra
Supervisor, QC

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research use or further manufacturing. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.