

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by Intertek Global
Certificate Number: CERT-0120633

Catalogue Number	42458
Lot Number	B0158135
Description	UREA, REAGENT ACS
CAS Number	57-13-6
Quality Test/Release Date	23/Dec/2025
Suggested retest date	19/Nov/2030
Country of Origin	United States
Declaration of Origin	Organic - non animal
BSE/TSE	No animal products are used as starting raw material ingredients, or used in processing, including lubricants, processing aids, or any other material that might migrate to the finished product.

Result Name	Units	Specifications	Test Value
APPEARANCE		REPORT	Colorless to white crystals, prills or crystalline powder
ASSAY	%	Inclusive Between 99.0 - 100.5	99.7
CHLORIDE	ppm	<= 5	<5
HEAVY METALS BY ICP-OES	%	<= 0.001	<0.001
IDENTIFICATION	PASS/FAIL	= PASS TEST	PASS TEST
INSOLUBLE MATTER	%	<= 0.01	<0.01
IRON (Fe)	ppm	<= 10	<0.001
MELTING POINT	DEGREES CELSIUS	Inclusive Between 132 - 135	132
RESIDUE AFTER IGNITION	%	<= 0.01	<0.01
SULFATE (SO4)	ppm	<= 10	<0.001



Harout Sahagian
QC Manager

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research use or further manufacturing. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.