

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by LRQA. Certificate Number. 10551915

Catalogue Number	B20391
Lot Number	10254585
Description	Mercaptoacetic acid, 97+%
CAS Number	68-11-1
Quality Test/Release Date	09/Apr/2025
Suggested retest date	09/Apr/2026
Country of Origin	France
Declaration of Origin	Synthetic

Result Name	Units	Specifications	Test Value
Assay (Aqueous acid-base Titration)	%	≥97.0 to ≤103.0% (non-U.S. sourced material)	99.7
Assay (Silylated GC)	%	≥97.0% (non-U.S. sourced material)	98.5
Appearance (Color)		Clear colorless	Clear colourless
Form		Liquid	Liquid
Identification (FTIR)		Conforms (non-U.S. sourced material)	Conforms
Proton NMR		Conforms to structure (non-U.S. sourced material)	Conforms to structure
Refractive Index		1.5020-1.5070 @ 20°C (non-U.S. sourced material)	1.5050



Paul Coleman
Site Quality Manager

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.