

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by Intertek. Certificate Number. 2317548

Catalogue Number	41006
Lot Number	A0469315
Description	Diethyl ether,99+%,ACS reagent,anhydrous, BHT stab., meets req. of Reag.Ph.Eur.
CAS Number	60-29-7
Quality Test/Release Date	20/Dec/2025
Suggested retest date	20/Dec/2027
Country of Origin	GERMANY
Declaration of Origin	synthetic
BSE/TSE	Not directly derived from or manufactured with any animal byproducts in any way (Including but not limited to fermentation or nutrient broth, catalysts, enzymes).

Result Name	Units	Specifications	Test Value
Appearance (Form)		Clear liquid	Clear liquid
Color scale	APHA	≤10	10
GC	%	≥99.0	99.9
Water	%	≤0.03 (Coulometric)	0.006 (Coulometric)
Density		(20/20°C) 0.713 to 0.715	(20/20°C) 0.715
Boiling point		34°C to 35°C	34°C to 35°C
Peroxides	ppm	≤1 (as H ₂ O ₂)	≤1 (as H ₂ O ₂)
Residue after evaporation	%	≤0.001	≤0.0002
Titration acid	meq/g	≤0.0002	None detected
Carbonyl (as HCHO)	%	≤0.001	≤0.0001
Stabilizer	ppm	≤10 BHT	5 BHT
Ethanol		(limit about 0.05%) Passes test	(limit about 0.05%) Passes test



Geert Torfs
Supervisor, QC

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.