

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by TUV SUD America Inc.
 Certificate Number. 951001163

Catalogue Number	J61472
Lot Number	Y25L033
Description	D-Amygdalin, 98%
CAS Number	29883-15-6
Quality Test/Release Date	25/Nov/2025
Suggested retest date	25/Nov/2030
Country of Origin	China

Result Name	Units	Specifications	Test Value
Assay (unspecified)	cfu/gm	Yeast and Mold: ≤ 10 cfu/gm	<10
Assay (unspecified)	Mesh	Mesh size: 80	80
Assay (unspecified)		E. coli, Salmonella, S. Aureus:	Negative
Assay (unspecified)	cfu/g	Bacterial Endotoxin: ≤ 1000 cfu.gm	<1000
Assay (unspecified)	ppm	Arsenic (As): ≤ 2 ppm; Lead (Pb): ≤ 2 ppm; Mercury (Hg): ≤ 0.3 ppm; Cadmium: ≤ 0.1 ppm	As:;<2;Pb:<2;Hg:<0.3;Cd:<0.1
Assay (HPLC)	%	≥ 98 %	98.41
Form		Crystalline powder	Crystalline powder
Heavy Metals	ppm	≤ 5 ppm	<5
Impurity content	%	Total impurities: ≤ 1.0 %; Other single impurities: ≤ 0.5 %	Total impurities:0.32;Other single impurities:0.19
Loss on Drying	%	≤ 5.0 %	1.91
Optical Rotation	°	- 37 to -41	-37.5



Derek Roy
 Quality Manager, LCD

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.