

## CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by LRQA. Certificate Number. 10551915

Catalogue Number	L13940
Lot Number	10255561
Description	Urea hydrogen peroxide adduct, 97%
CAS Number	124-43-6
Quality Test/Release Date	21/Apr/2026
Suggested retest date	21/Apr/2027
Country of Origin	Germany
Declaration of Origin	Synthetic
BSE/TSE	Not directly derived from or manufactured with any animal byproducts in any way (including but not limited to fermentation or nutrient broth, catalysts, enzymes).

Result Name	Units	Specifications	Test Value
Available Oxygen	%	Available oxygen 16-18%	16.49
Assay (Iodometric Titration)	%	≥96.0%	97.0
Appearance (Color)		White	White
Form		Crystals or crystalline powder or tables	Crystalline powder
Identification (FTIR)		Conforms	Conforms
Free Hydrogen Peroxide	%	Free hydrogen peroxide 34.7% min.	35.05
Melting Point (clear melt)	°C	87-93°C	88.1-91.4



Paul Coleman  
Site Quality Manager

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.