

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by Intertek. Certificate Number. 2317548

Catalogue Number	12190
Lot Number	A0472594
Description	8-Hydroxyquinoline,ACS reagent
CAS Number	148-24-3
Quality Test/Release Date	13/May/2025
Suggested retest date	13/May/2030
Country of Origin	CHINA
Declaration of Origin	synthetic
BSE/TSE	Not directly derived from or manufactured with any animal byproducts in any way (Including but not limited to fermentation or nutrient broth, catalysts, enzymes).

Result Name	Units	Specifications	Test Value
Appearance (Color)		White to light yellow to beige to light brown	light brown
Appearance (Form)		Crystalline powder or crystals or flakes	flakes
Infrared spectrum		Conforms	Conforms
Melting point		72.5°C to 74.0°C	73.2°C
Suitability		(for Mg determination) Passes test	(for Mg determination) Passes test
Insoluble matter	%	=<0.05 (in alcohol)	=<0.05 (in alcohol)
Residue after ignition	%	=<0.05	=<0.05
Sulfate (SO4)	%	=<0.02	0.01

Geert Torfs
Supervisor, QC

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.