

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by LRQA. Certificate Number. 10551915

Catalogue Number	A11489
Lot Number	10260421
Description	Diphenylacetic acid, 99%
CAS Number	117-34-0
Quality Test/Release Date	06/Feb/2026
Suggested retest date	06/Feb/2031
Country of Origin	India
Declaration of Origin	Synthetic
BSE/TSE	Not directly derived from or manufactured with any animal byproducts in any way (including but not limited to fermentation or nutrient broth, catalysts, enzymes).

Result Name	Units	Specifications	Test Value
Assay (Aqueous acid-base Titration)	%	≥98.5 to ≤101.5%	99.2
Assay (HPLC)	%	≥98.5%	99.4
Appearance (Color)		White to cream	White
Form		Crystals or powder or crystalline powder	Crystalline powder
Identification (FTIR)		Conforms	Conforms
Melting Point (clear melt)	°C	144.0-150.0°C	145.8-147.6
Solution Test		10% w/v in Acetonitrile: clear solution	Clear solution



Paul Coleman
Site Quality Manager

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.