

■ Fotoschale


Runde Ecken

■ Tray laboratory

Round corners

■ Cuvettes

Coins ronds




Material	a	A	b	B	C	Artikel Nr.
18/10-STAHL	190	225	140	175	50	8700
18/10-STAHL	250	290	180	220	60	8701
18/10-STAHL	260	290	190	225	50	8702
18/10-STAHL	320	355	260	305	60	8703
18/10-STAHL	350	400	240	280	70	8704
18/10-STAHL	400	450	270	320	80	8705
18/10-STAHL	500	560	330	385	100	8706

■ Verdampfschale mit Rand

■ Evaporating dish with rim

■ Cristallisoirs avec bord




Material	A	B	C	Artikel Nr.
18/10-STAHL	220	155	40	8454
18/10-STAHL	240	160	50	8455
18/10-STAHL	310	200	45	8456
18/10-STAHL	340	210	60	8457
18/10-STAHL	375	270	45	8459

■ Schalen mit 2 Griffen

■ Trays with 2 handles

■ Boîtes rectangulaires avec 2 anses




Material	A	B	C	Artikel Nr.
18/10-STAHL	250	180	70	8735
18/10-STAHL	350	250	70	8736

■ Chemikalienschaufel

■ Chemical scoop

■ Pelle inox




Material	A	a	D	Ltr	Artikel Nr.
18/10-STAHL	190	100	50	0,12	8800
18/10-STAHL	250	145	75	0,45	8801
18/10-STAHL	320	190	105	1,00	8802
18/10-STAHL	350	230	120	1,50	8803
18/10-STAHL	370	250	150	2,00	8804

■ Chemikalienschaufel, schwere Ausführung


■ Chemical scoop, heavy model

■ Pelle inox, modèle massive




Material	A	a	D	Ltr	Artikel Nr.
18/10-STAHL	215	100	40	0,15	8809
18/10-STAHL	310	160	82	0,25	8810
18/10-STAHL	350	200	102	0,5	8811
18/10-STAHL	390	220	120	1,0	8812
18/10-STAHL	450	300	160	2,0	8813

- Chemikalienschaufel Aluminium
- Chemical scoop aluminium
- Pelle aluminium




Material	A	a	D	MI	Artikel Nr.
ALU	65	40	12	5	8814
ALU	85	52	13	10	8815
ALU	135	80	24	50	8816
ALU	155	95	30	65	8817
ALU	185	115	32	90	8818
ALU	210	120	37	160	8819
ALU	250	145	45	240	8820
ALU	290	175	55	400	8821
ALU	310	185	57	480	8822
ALU	350	220	63	900	8823
ALU	400	270	83	1600	8824
ALU	430	300	95	2500	8825
ALU	250	120	35	90	8827
ALU	285	120	35	90	8828
ALU	365	120	35	90	8829

- Wägeschaufel
- Weighing scoop
- Pelle pour balance




Material	A	D	Artikel Nr.
18/10-STAHL	70	32	12800
18/10-STAHL	90	32	12801
18/10-STAHL	105	32	12802
18/10-STAHL	120	32	12803
18/10-STAHL	120	30-65	12804
18/10-STAHL	160	30-75	12805
18/10-STAHL	200	55-100	12806
ALU	70	32	12810
ALU	90	32	12811
ALU	105	32	12812
ALU	120	32	12813

- Schöpfkelle, runder Griff
- Ladle scoop, round handle
- Louche inox, manche rond



Material	A	D	MI	Artikel Nr.
18/10-STAHL	300	60	50	8790
18/10-STAHL	300	70	80	8791
18/10-STAHL	300	80	130	8792
18/10-STAHL	300	90	210	8793
18/10-STAHL	400	100	250	8794
18/10-STAHL	400	120	450	8795
18/10-STAHL	400	140	670	8796
18/10-STAHL	400	160	1000	8797
18/10-STAHL	500	200	2000	8799

- Schöpfkelle, flacher Griff
- Ladle scoop, flat handle
- Louche inox, manche plat



Material	A	D	MI	Artikel Nr.
18/10-STAHL	230	70	50	8740
18/10-STAHL	280	90	125	8741
18/10-STAHL	300	100	250	8742
18/10-STAHL	350	140	750	8743
18/10-STAHL	500	160	1000	8744
18/10-STAHL	500	180	1500	8745