



Ultrasonic Units

fisherbrand easy

The easy way to clean and for sample preparations.

- More power with Pulse function for tough contaminations
- Pulse function for sample preparation
- Easy operation handling
- Versatile ultrasonic unit with high quality and value for money
- Integrated "Sweep" function for intensive ultrasonic cleaning

fisherbrand easy

High performance ultrasonic devices with easy operation

The 9 ElmaSonic EASY cleaning units are ready for typical lab applications like sample preparation as well as for lab cleaning tasks.



Technical Data

	easy 10 / H	easy 20 / H	easy 30 H	easy 40 H	easy 60 H	easy 100 H	easy 120 H	easy 180 H	easy 300 H
Fisher code	16463889 / 16453889	16483889 / 16473889	16493889	16493889	16413899	16423899	16433899	16443899	16453899
Elma code	1071648-C / 1071646-C	1071655-C / 1071652-C	1071656-C	1071664-C	1071666-C	1071669-C	1071671-C	1071673-C	1071675-C
Tank capacity max. (l)	0.8	1.75	2.75	4.25	5.75	9.5	12.75	18.0	28.0
Tank labour capacity (l)	0.7	1.2	1.6	2.9	4.3	6.8	10.0	14.2	22.0
Ultrasonic power effective (W)	30	35	80	140	150	150	200	200	300
Heating power (W)	60	120	200	200	400	400	800	800	1200
Unit ext. dim. W/D/H (mm)	235/135/190	220/190/230	305/190/230	305/190/280	370/230/275	380/320/280	380/320/330	405/380/330	575/380/330
Tank int. dim. W/D/H (mm)	190/65/55	180/135/95	235/135/95	235/135/145	295/145/145	295/235/145	295/235/195	325/295/195	500/395/195
Basket int. dim. W/D/H (mm)	177/73/30	112/103/50	198/106/50	190/105/75	255/115/75	255/200/75	250/190/115	280/250/115	455/250/115
Weight (kg)	2.0	2.1	3.3	4.0	5.1	5.9	7.5	8.5	11.0

Austria: fishersci.at Belgium: fishersci.be Denmark: fishersci.dk
 Germany: fishersci.de Ireland: fishersci.ie Italy: fishersci.it
 Finland: fishersci.fi France: fishersci.fr Netherlands: fishersci.nl
 Norway: fishersci.no Portugal: fishersci.pt Spain: fishersci.es
 Sweden: fishersci.se Switzerland: fishersci.ch UK: fishersci.co.uk

© 2021 Thermo Fisher Scientific Inc. All rights reserved.
 Trademarks used are owned as indicated at fishersci.com/trademarks.

fisher scientific
 part of Thermo Fisher Scientific