


CATALOG NO.	NOMINAL CAPACITY (GAL)				MATERIALS		
					BOTTLE	CLOSURE	GASKET IN CLOSURE
002126	1/4	1/2	1	1 1/4	PPCO	WHITE PP	TPE (KRATON)

SIZE CODE.....:	-1000		-2000		-4000		-5000	
SIZE (NOM VOL L/GAL)	1/ 1/4		2/ 1/2		4/ 1		5/ 1 1/4	
NOM. BRIM CAP. (mL):	940		1995		4200		5370	
NECK FINISH (mm)....:	53B		53B		83B		83B	
THREAD (T.P.I.).....:	4		4		2		2	
NOM. WEIGHT W/CLOSURE (gms).....:	240		440		745		1040	
	INCH	MM	INCH	MM	INCH	MM	INCH	MM
A (NECK I.D.).....:	1.50 ±.04	38.1±1.0	1.50 ±.04	38.1±1.0	2.78 ±.04	70.6 ±1.0	2.50 ±.04	63.5 ±1.0
B (HT. W/CLOSURE)...:	8.93 ±.12	226.8 ±3.0	10.38 ±.12	263.7 ±3.0	13.32 ±.14	338.3 ±3.6	16.30 ±.16	414.0 ±4.1
C (HT. W/O CLOSURE):	8.60 ±.12	218.4 ±3.0	10.00 ±.12	254.0 ±3.0	12.86 ±.14	326.6 ±3.6	15.84 ±.16	402.3 ±4.1
D (DIA).....:	3.62 ±.10	92.0 ±2.5	4.72 ±.10	119.9 ±2.5	6.12 ±.10	155.4 ±2.5	6.15 ±.10	156.2 ±2.5
W.T.(NOM WALL THK.):	.13	3.3	.19	4.8	.19	4.8	.25	6.4

2. This is not a production drawing, but is for informational purposes only,
and is subject to change without notice.
1. All dimensions are nominal and in inches and millimeters unless otherwise noted.



SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE	PB	APP'D	PWC	PSS 00-2126-XXXX-1	REV. 0214
CK'D	KOW		2/17/14		
DESCRIPTION:				HEAVY DUTY ROUND LAB QUALITY BOTTLES	