

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by INTERTEK SAI Global
Certificate Number. QMS42099

Catalogue Number	M/4062
Lot Number	2546556
Description	Methanol LC-MS For LC-MS analysis
CAS Number	67-56-1
Quality Test/Release Date	29/Jul/2025
Expiry Phrase	Use within 3 yrs of opening
Country of Origin	Trinidad and Tobago
Declaration of Origin	Synthetic
BSE/TSE	Not directly derived from or manufactured with any animal byproducts in any way (Including but not limited to fermentation or nutrient broth, catalysts, enzymes).

Result Name	Units	Specifications	Test Value
Absorbance @ 230 nm	A.U.	<= 0.05	0.019
Absorbance @ 260 nm	A.U.	<= 0.005	0.004
Absorbance of the largest eluted peak	mA.U.	<= 0.5	None Detected
Acidity/alkalinity (meq/g)	meq/g	<= 0.0002	0.00003
Aluminium (Al)	ppm	<= 0.2	<0.02
Assay (GC)	%	>= 99.9	100.00
Barium (Ba)	ppm	<= 0.01	<0.005
Cadmium (Cd)	ppm	<= 0.01	<0.005
Calcium (Ca)	ppm	<= 0.05	<0.02
Chemical form		Mobile liquid	Mobile liquid
Chromium (Cr)	ppm	<= 0.01	<0.005
Cobalt (Co)	ppm	<= 0.01	<0.005
Copper (Cu)	ppm	<= 0.01	<0.01
Iron (Fe)	ppm	<= 0.01	<0.01
LC-MS suitability		Must be 'Pass'	Pass
Lead (Pb)	ppm	<= 0.01	<0.005
Magnesium (Mg)	ppm	<= 0.01	<0.01
Manganese (Mn)	ppm	<= 0.01	<0.005
Nickel (Ni)	ppm	<= 0.01	<0.005
Potassium (K)	ppm	<= 0.01	<0.01
Residue after evaporation (ppm)	ppm	<= 5	None Detected
Silver (Ag)	ppm	<= 0.01	<0.005
Sodium (Na)	ppm	<= 0.5	<0.05
Tin (Sn)	ppm	<= 0.01	<0.005
Visual colour		Clear colourless	Clear colourless
Water	%	<= 0.03	0.02
Zinc (Zn)	ppm	<= 0.01	<0.01

Additional Information Filtered to 0.2 micron

A. Ganatra

Ashok Ganatra
Supervisor, QC

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research use or further manufacturing. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.