

AXYGEN SCIENTIFIC – PIPETTE TIPS, PCR, TUBES AND HTS



CORNING

AXYGEN

Austria

Fisher Scientific (Austria) GmbH
Rudolf von Alt-Platz 1
1030 Vienna
Tel.: +43 (0) 800 20 88 40
Fax: +43 (0) 800 20 66 90
Email: info.austria@thermofisher.com
www.at.fishersci.com

Belgium

Fisher Scientific
Clintonpark - Keppekouter
Ninovesteenweg 198
9320 Erembodem Aalst
Tel.: +32 (0) 56 260 260
Fax: +32 (0) 56 260 270
Email: be.fisher@thermofisher.com
www.be.fishersci.com

Czech

Fisher Scientific spol. s.r.o.
Kosmonautu 324
53009 Pardubice
Tel.: +420 (0) 466 798-230
Fax: +420 (0) 466 435-008
Email: info.cz@thermofisher.com
www.thermofisher.cz

Denmark

Fisher Scientific
Postboks 60
Industrivej 3
3550 Slangerup
Tel.: +45 (0) 70 27 99 20
Fax: +45 (0) 70 27 99 29
Email: kundeservice@thermofisher.com
www.fishersci.dk

Finland

Fisher Scientific
Ratastie 2
01620 Vantaa
Tel.: +358 (0) 9 8027 6280
Fax: +358 (0) 9 8027 6235
Email: fisher.fi@thermofisher.com
www.fishersci.fi

France

Fisher Scientific
Parc d'innovation
BP 50111
67403 Illkirch Cedex
Tel.: +33 (0) 388 67 53 20
Fax: +33 (0) 388 67 11 68
Email: fr.commande@thermofisher.com
www.fr.fishersci.com

Germany

Fisher Scientific GmbH
Im Heiligen Feld 17
58239 Schwerte
Tel.: +49 (0) 2304 932 5
Fax: +49 (0) 2304 932 950
Email: info.germany@thermofisher.com
www.de.fishersci.com

Ireland

Fisher Scientific Ireland
Suite 3
Plaza 212
Blanchardstown Corporate Park 2
Ballycoolin
Dublin 15
Tel.: +353 (0)1 885 5854
Fax: +353 (0)1 899 1855
Email: fsie.sales@thermofisher.com
www.ie.fishersci.com

Italy

Fisher Scientific
Tel.: +39 (0)2 953 28 258
Fax: +39 (0)2 953 27 374
Email: it.fisher@thermofisher.com
www.it.fishersci.com

The Netherlands

Fisher Scientific
Scheepsbouwersweg 1b
P.O. Box 4
1120 AA Landsmeer
Tel.: +31 (0) 20 487 70 00
Fax: +31 (0) 20 487 70 70
Email: nl.info@thermofisher.com
www.nl.fishersci.com

Norway

Fisher Scientific
Frysjavaen 33E
0884 Oslo
Tel.: +47 (0) 22 95 59 59
Fax: +47 (0) 22 95 59 40
Email: fisher.no@thermofisher.com
www.fishersci.no

Portugal

Fisher Scientific
Rua Pedro Álvares Cabral, n°24, 3ºD
Edifício Euro - Infantado
2670-391 Loures
Tel.: +351 (0) 21 425 33 50/4
Fax: +351 (0) 21 425 33 51
Email: pt.fisher@thermofisher.com
www.pt.fishersci.com

Slovenia

Fisher Scientific d.o.o
Parmova ulica 53
SI-1000 Ljubljana
Tel.: +386 (0) 598 31 494
Fax: +386 (0) 598 31 495
Email: si.info@thermofisher.com
www.si.fishersci.com

Spain

Fisher Scientific
C/ Luis I, 9
28031 MADRID
Tel.: +34 (0) 902 239 303
Fax: +34 (0) 902 239 404
Email: es.fisher@thermofisher.com
www.es.fishersci.com

Sweden

Fisher Scientific
Box 9193
400 94 Göteborg
Tel.: +46 (0) 31 352 32 00
Fax: +46 (0) 31 352 32 50
Email: fisher.se@thermofisher.com
www.fishersci.se

Switzerland

Fisher Scientific
Wilstrasse 57
BP 1006
5610 Wohlen
Tel.: +41 (0) 56 618 41 11
Fax: +41 (0) 56 618 41 41
Email: info.ch@thermofisher.com
www.ch.fishersci.com

United Kingdom

Fisher Scientific UK
Bishop Meadow Road
Loughborough
Leicestershire
LE11 5RG
Tel.: +44 (0)1509 231166
Fax: +44 (0) 1509 231893
Email: fsuk.sales@thermofisher.com
www.fisher.co.uk

CONTENTS

PIPETTE TIPS

Tips	1
Pipette Tip Compatibility Chart	9

PCR/SEALING PRODUCTS

PCR Plates	15
Sealing Films and Accessories for Sequencing	18
PCR Tubes and Strip Tubes	23
PCR Plate Compatibility Chart	25

MICROTUBES

Microtubes	27
Snap Cap Tubes	28
Screw Cap Tubes	30

HIGH THROUGHPUT SCREENING

Tips for Automation	37
Deepwell Plates and Reservoirs	62

TECHNICAL DATA

Thermoplastics Chemical and Physical Properties	69
Product Certification	71

INDEX

Axygen Catalogue Numbers	73
--------------------------------	----

Axygen Scientific

MAXIMUM Recovery® Ultra Smooth Surfaces

- proteomics • drug discovery • genomics
- high throughput screening

Utilizing a unique manufacturing process, Axxygen Scientific has developed an innovative series of pipette tips, filter tips, PCR products and microcentrifuge tubes that feature ultra smooth surfaces.

- ▶ Exclusive molding technology
- ▶ Reduce sample loss
- ▶ Save costly reagents
- ▶ Maximize accuracy and precision


Surface comparison of polypropylene materials

The images below show a visual comparison of the Axxygen Maxymum Recovery® pipette tip internal surface compared to the surface of both standard polypropylene pipette tips and siliconized pipette tips.

The photographs were taken of the internal surface of sections cut from three styles of pipette tips, via SEM/EDS. Magnification levels ranged from 50x to 5,000x.



Axygen MAXIMUM Recovery® Pipette Tips



Figures 1a (50x), 1b (500x) and 1c (5000x) are images of the Axxygen Maxymum Recovery® surface. Even at the highest magnification level, the ultra-smooth surface is visibly free of occlusions and cavities which can cause sample retention and sample denaturation in standard polypropylene.

Conventional Pipette Tips





Figure 2a (50x), 2b (500x) and 2c (5000x) are images of the internal surface of a standard polypropylene pipette tip. Occlusions and cavities can be seen on the wall surface. At highest magnification, surface strands which cause samples to 'stick', are clearly visible.

Siliconized Pipette Tips



Figure 3a (50x), 3b (500x) and 3c (2000x) are images of a siliconized pipette tip. Here again, notice the lack of smoothness of the walls created by an inconsistent and uneven flow of silicone upon the surface. Sample retention occurs even with siliconized pipette tips.

- ▶ Allows for complete sample retrieval
- ▶ Saves costly reagents by reducing sample loss
- ▶ Greater tip-to-tip precision
- ▶ Optimizes accuracy of pipettor
- ▶ Optimizes transfer of blood plasma
- ▶ Avoid denaturation of nucleic acids¹ and protein samples²



Axygen products are manufactured in a clean, controlled "state of the art" facility and certified RNase-, DNase- and endotoxin-safe on a lot by lot basis.



- No mold-releasing agents used
- Contamination-free
- Reduced sample retention
- Optimized performance
- MAXIMUM RECOVERY – allows complete retrieval of precious samples
- Universal fit tips – compatible with most popular brands of pipettors
- Aerosol barrier tips – prevent aerosol and liquid contamination
- Universal fit & aerosol barrier tips – available in bulk and racked formats
- Optimized tip bevel – reduces sample hang-up; improves pipetting accuracy
- Graduation marks – allow a visual confirmation of pipettor draw volume
- ‘Clean-room’ manufacturing environment – products certified safe from RNase-, DNase- and endotoxin by lot number
- Consistent product quality – every manufacturing lot undergoes rigorous testing
- Pre-sterilized products – e-beam irradiated to prevent product degradation

2: Zhu J., Garcia J., Avila R., Zachoratos J. and Arazani A. 2005. Protein Recovery Studies, Oxygen Research Labs, Union City, California.

Microvolume Tips



Maxymum Recovery® Technology

- allows recovery of costly samples
- improves precision & accuracy

10µl



T-300-L-R-S 10µl microvolume tips

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
T-300-L	0.1-10µl	Clear	Maxymum Recovery	Bulk
T-300-L-R	0.1-10µl	Clear	Maxymum Recovery	Racked
T-300-L-R-S	0.1-10µl	Clear	Maxymum Recovery	Racked, Sterile
TF-300-L-R-S	0.1-10µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
T-300	0.1-10µl	Clear	MicroVolume	Bulk
T-300-R	0.1-10µl	Clear	MicroVolume	Racked
T-300-R-S	0.1-10µl	Clear	MicroVolume	Racked, Sterile
T-300-STK	0.1-10µl	Clear	MicroVolume	Stack Rack
TF-300-R-S	0.1-10µl	Clear	MicroVolume	Filtered, Racked, Sterile



10µl microvolume tips
Extended length

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
TXL-10-L	0.1-10µl	Clear	Maxymum Recovery	Bulk
TXL-10-L-R	0.1-10µl	Clear	Maxymum Recovery	Racked
TXL-10-L-R-S	0.1-10µl	Clear	Maxymum Recovery	Racked, Sterile
TXLF-10-L-R-S	0.1-10µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
TXL-10	0.1-10µl	Clear	MicroVolume	Bulk
TXL-10-R	0.1-10µl	Clear	MicroVolume	Racked
TXL-10-R-S	0.1-10µl	Clear	MicroVolume	Racked, Sterile
TXLF-10-R-S	0.1-10µl	Clear	MicroVolume	Filtered, Racked, Sterile

Packaging Description:

Bulk = 1000 tips/pack, 20 packs/case; Racked = 96 tips/rack, 10 racks/pack, 5 packs/case
Stack Racks = 96 tips/rack, 5 racks/stack, 10 stacks/case

Fits: Pipetman P2/P10 and other popular brands. See Tip Compatibility Table, pages 9-13

20µl



TF-420-L-R-S 20µl microvolume tips

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
T-400-L	0.1-20µl	Clear	Maxymum Recovery	Bulk
T-400-L-R	0.1-20µl	Clear	Maxymum Recovery	Racked
T-400-L-R-S	0.1-20µl	Clear	Maxymum Recovery	Racked, Sterile
TF-410-L-R-S	0.1-10µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile
TF-420-L-R-S	0.1-20µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
T-400	0.1-20µl	Clear	Ultra Micro	Bulk
T-400-R	0.1-20µl	Clear	Ultra Micro	Racked
T-400-R-S	0.1-20µl	Clear	Ultra Micro	Racked, Sterile
TF-410-R-S	0.1-10µl	Clear	Ultra Micro	Filtered, Racked, Sterile
TF-420-R-S	0.1-20µl	Clear	Ultra Micro	Filtered, Racked, Sterile

Packaging Description:

Bulk = 1000 tips/pack, 20 packs/case; Racked = 96 tips/rack, 10 racks/pack, 5 packs/case

Fits: Eppendorf Ultra Micro, Pipetman P2/P10 and other popular brands. See Tip Compatibility Table, pages 9-13

Universal Tips

Fits popular brands of pipettors

200µl, bevelled



200µl, bevelled universal tip

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
T-200-C-L	1-200µl	Clear	Maxymum Recovery	Bulk
T-200-C-L-R	1-200µl	Clear	Maxymum Recovery	Racked
T-200-C-L-R-S	1-200µl	Clear	Maxymum Recovery	Racked, Sterile
T-200-C	1-200µl	Clear	Bevelled	Bulk
T-200-C-R	1-200µl	Clear	Bevelled	Racked
T-200-C-R-S	1-200µl	Clear	Bevelled	Racked, Sterile
T-200-C-STK	1-200µl	Clear	Bevelled	Stack Rack

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
TF-20-L-R-S	1-20µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile
TF-20-R-S	1-20µl	Clear	Bevelled	Filtered, Racked, Sterile



Filter Tips - 20, 50, 100, 150 and 200µl

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
TF-50-L-R-S	1-50µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile
TF-50-R-S	1-50µl	Clear	Bevelled	Filtered, Racked, Sterile

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
TF-100-L-R-S	1-100µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile
TF-100-R-S	1-100µl	Clear	Bevelled	Filtered, Racked, Sterile

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
TF-150-L-R-S	1-150µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile
TF-150-R-S	1-150µl	Clear	Bevelled	Filtered, Racked, Sterile

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
TF-200-L-R-S	1-200µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile
TF-200-R-S	1-200µl	Clear	Bevelled	Filtered, Racked, Sterile

Fits: Universal. See Tip Compatibility Tables, pages 9-13

Packaging Description:

Bulk = 1000 tips/pack, 20 packs/case; Racked = 96 tips/rack, 10 racks/pack, 5 packs/case
Stack Racks = 96 tips/rack, 5 racks/stack, 10 stacks/case

200µl, bevelled, reference



200µl, bevelled reference universal tip. Graduation marks at 10, 50, 100µl

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
TR-222-C-L	1-200µl	Clear	Maxymum Recovery	Bulk
TR-222-C-L-R	1-200µl	Clear	Maxymum Recovery	Racked
TR-222-C-L-R-S	1-200µl	Clear	Maxymum Recovery	Racked, Sterile
TR-222-C	1-200µl	Clear	Bevelled, Reference	Bulk
TR-222-C-R	1-200µl	Clear	Bevelled, Reference	Racked
TR-222-C-R-S	1-200µl	Clear	Bevelled, Reference	Racked, Sterile
TR-222-C-STK	1-200µl	Clear	Bevelled, Reference	Stack Rack

Fits: Universal. See Tip Compatibility Tables, pages 9-13

Packaging Description:

Bulk = 1000 tips/pack, 20 packs/case; Racked = 96 tips/rack, 10 racks/pack, 5 packs/case
Stack Racks = 96 tips/rack, 5 racks/stack, 10 stacks/case

Universal Tips



Fits popular brands of pipettors

200µl, wide bore



200µl, wide bore

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
T-205-WB-C-L	1-200µl	Clear	Maxymum Recovery	Bulk
T-205-WB-C-L-R	1-200µl	Clear	Maxymum Recovery	Racked
T-205-WB-C-L-R-S	1-200µl	Clear	Maxymum Recovery	Racked, Sterile
TF-205-WB-L-R-S	1-200µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile
T-205-WB-C	1-200µl	Clear	Wide Bore	Bulk
T-205-WB-C-R	1-200µl	Clear	Wide Bore	Racked
T-205-WB-C-R-S	1-200µl	Clear	Wide Bore	Racked, Sterile
TF-205-WB-R-S	1-200µl	Clear	Wide Bore	Filtered, Racked, Sterile

Packaging Description:

Bulk = 1000 tips/pack, 20 packs/case; Racked = 96 tips/rack, 10 racks/pack, 5 packs/case

Fits: Universal. See Tip Compatibility Tables, pages 9-13



Wide bore tips are ideal for pipetting viscous materials, genomic DNA or delicate cell cultures

250µl, bevelled, reference


250µl, bevelled, reference
Graduation marks at 10, 50 and 100µl

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
TR-333-C-L	1-250µl	Clear	Maxymum Recovery	Bulk
TR-333-C-L-R	1-250µl	Clear	Maxymum Recovery	Racked
TR-333-C-L-R-S	1-250µl	Clear	Maxymum Recovery	Racked, Sterile
TR-333-C	1-250µl	Clear	Bevelled, Reference	Bulk
TR-333-C-R	1-250µl	Clear	Bevelled, Reference	Racked
TR-333-C-R-S	1-250µl	Clear	Bevelled, Reference	Racked, Sterile

Packaging Description:

Bulk = 1000 tips/pack, 20 packs/case; Racked = 96 tips/rack, 10 racks/pack, 5 packs/case

Fits: Universal. See Tip Compatibility Tables, pages 9-13

300µl, fine-point



300µl, fine-point

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
T-350-C-L	1-300µl	Clear	Maxymum Recovery	Bulk
T-350-C-L-R	1-300µl	Clear	Maxymum Recovery	Racked
T-350-C-L-R-S	1-300µl	Clear	Maxymum Recovery	Racked, Sterile
TF-350-L-R-S	1-300µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile
T-350-C	1-300µl	Clear	Fine-Point	Bulk
T-350-C-R	1-300µl	Clear	Fine-Point	Racked
T-350-C-R-S	1-300µl	Clear	Fine-Point	Racked, Sterile
TF-350-R-S	1-300µl	Clear	Fine-Point	Filtered, Racked, Sterile

Packaging Description:

Bulk = 1000 tips/pack, 10 packs/case; Racked = 96 tips/rack, 10 racks/pack, 5 packs/case

Fits: Universal. See Tip Compatibility Tables, pages 9-13

1000 - 1250µl Tips

1000µl, bevelled



1000µl, bevelled

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
T-1000-C-L	100-1000µl	Clear	Maxymum Recovery	Bulk
T-1000-C-L-R	100-1000µl	Clear	Maxymum Recovery	Racked
T-1000-C-L-R-S	100-1000µl	Clear	Maxymum Recovery	Racked, Sterile
TF-1000-L-R-S	100-1000µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile
T-1000-C	100-1000µl	Clear	Bevelled	Bulk
T-1000-C-R	100-1000µl	Clear	Bevelled	Racked
T-1000-C-R-S	100-1000µl	Clear	Bevelled	Racked, Sterile
TF-1000-R-S	100-1000µl	Clear	Bevelled	Filtered, Racked, Sterile

Packaging Description: Bulk=1000 tips/pack, 5 packs/case; Racked=100 tips/rack, 10 racks/pack, 5 packs/case

Fits: Universal. See Tip Compatibility Tables, pages 9-13

1000µl, wide bore



1000µl, wide bore

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
T-1005-WB-C-L	100-1000µl	Clear	Maxymum Recovery	Bulk
T-1005-WB-C-L-R	100-1000µl	Clear	Maxymum Recovery	Racked
T-1005-WB-C-L-R-S	100-1000µl	Clear	Maxymum Recovery	Racked, Sterile
TF-1005-WB-L-R-S	100-1000µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile
T-1005-WB-C	100-1000µl	Clear	Wide Bore	Bulk
T-1005-WB-C-R	100-1000µl	Clear	Wide Bore	Racked
T-1005-WB-C-R-S	100-1000µl	Clear	Wide Bore	Racked, Sterile
TF-1005-WB-R-S	100-1000µl	Clear	Wide Bore	Filtered, Racked, Sterile

Packaging Description: Bulk = 1000 tips/pack, 5 packs/case; Racked = 100 tips/rack, 10 racks/pack, 5 packs/case

Fits: Universal. See Tip Compatibility Tables, pages 9-13

1200µl, bevelled



1200µl, bevelled

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
T-1200-C	100-1200µl	Clear	Bevelled	Bulk
T-1200-C-R	100-1200µl*	Clear	Bevelled	Racked
T-1200-C-R-S	100-1200µl*	Clear	Bevelled	Racked, Sterile
TF-1200-C-R-S	100-1100µl*	Clear	Bevelled	Filtered, Racked, Sterile

Packaging Description: Bulk = 1000 tips/pack, 5 packs/case; Racked = 96 tips/rack, 12 racks/pack, 3 packs/case

Fits: Universal. See Tip Compatibility Tables, pages 9-13

1250µl, bevelled



1250µl, bevelled

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
MTX-1250-C-L	15-1250µl	Clear	Maxymum Recovery	Bulk
MTX-1250-C-L-R	15-1250µl	Clear	Maxymum Recovery	Racked
MTX-1250-C-L-R-S	15-1250µl	Clear	Maxymum Recovery	Racked, Sterile
MTXF-1250-C-L-R-S	15-1250µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile
MTX-1250-C	15-1250µl	Clear	Matrix-style	Bulk
MTX-1250-C-R	15-1250µl	Clear	Matrix-style	Racked
MTX-1250-C-R-S	15-1250µl	Clear	Matrix-style	Racked, Sterile
MTXF-1250-C-R-S	15-1250µl	Clear	Matrix-style	Filtered, Racked, Sterile

Packaging Description: Bulk = 500 tips/pack, 10 packs/case; Racked = 96 tips/rack, 12 racks/pack, 3 packs/case

Fits: Universal. See Tip Compatibility Tables, pages 9-13

Axypet-16® 384-Format tips

- 16-channel pipettor for 384/1536-well formats
- One-hand volume adjustment and volume locking
- Adapts fully to left and right-handed use
- Autoclavable
- Available in 0.1-2µl, 0.1-10µl, 5-50µl
- Ergonomic handle allows easy operation
- Plunger cap colour coded for ease of identification



volume control



tip ejection



tip holders

Volume Code	Colour ±%	Accuracy ±% (CV)	Precision	Axygen Cat #
0.1 - 2µl	violet	12 - 2.0	6.0 - 1.0	AP-16-2
0.1 - 10µl	white	2.5 - 1.0	1.8 - 0.5	AP-16
5 - 50µl	red	2.5 - 1.0	1.8 - 0.5	AP-16-50

60µl

for 384-well pipetting



for 384-well pipetting

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
T-384-L-R	0.1-60µl	Clear	Maxymum Recovery	Racked
T-384-L-R-S	0.1-60µl	Clear	Maxymum Recovery	Racked, Sterile
T-384-R	0.1-60µl	Clear	Microvolume	Racked
T-384-R-S	0.1-60µl	Clear	Microvolume	Racked, Sterile
TF-384-30-L-R-S	0.1-30µl	Clear	Maxymum Recovery	Filtered, Racked, Sterile
TF-384-30-R-S	0.1-30µl	Clear	Microvolume	Filtered, Racked, Sterile

Packaging Description: Racked = 384 tips/rack, 10 racks/pack, 5 packs/case

30µl

for 1536-well pipetting



for 1536-well pipetting

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
T-1536-L-R	0.5-30µl	Clear	Maxymum Recovery	Racked
T-1536-L-R-S	0.5-30µl	Clear	Maxymum Recovery	Racked, Sterile
T-1536-R	0.5-30µl	Clear	Microvolume	Racked
T-1536-R-S	0.5-30µl	Clear	Microvolume	Racked, Sterile

Packaging Description: Racked = 384 tips/rack, 10 racks/pack, 5 packs/case

50µl

Finnpipette® Focus Multi-channel Plus


Finnpipette® Focus
Multi-channel Plus

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
FPT-384-R	5-50µl	Clear	Microvolume	Racked
FPT-384-R-S	5-50µl	Clear	Microvolume	Racked, Sterile

Packaging Description: Racked = 384 tips/rack, 10 racks/pack, 5 packs/case

See Tip Compatibility Tables, pages 9-13

Macrovolume Tips

5ml



5ml

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
T-5000-C	1000-5000µl	Clear	Macrovolume	Bulk

Fits: Gilson P5000 and MLA pipettor

Packaging Description: Bulk = 250 tips/pack, 10 packs/case

10ml



10ml

Axygen Cat No	Volume	Tip Colour	Tip Type	Packaging
T-10ML-C	1-10ml	Clear	Macrovolume	Bulk

Fits: Gilson P10ML and MLA pipettor

Packaging Description: Bulk = 200 tips/pack, 10 packs/case

Autoclaving Conditions



Temperature: 121°C



Time: 15 minutes



Pressure: 15 psi

Autoclaving Guidelines


To ensure successful steam sterilization of your plastic labware please adhere to the following guideline:

Autoclave all plastic consumables at 121°C for 15 minutes, 15psi/1 atm.

Do not use a dry cycle as this may cause deformation or weakening of the plastic.

Allow temperature within the autoclave to return to at least 80°C before removing product.

Tip Packaging Options



Bulk Packaging

Pipette tips are available in bulk-packaged, re-sealable plastic bags – keeping them safe from contamination.



Hinged Racks

Axygen tip racks in durable polypropylene provide good stability on the lab bench. They feature a hinged lid with a snap fastener. Also available in sterile.



Stack Racks

Axygen inter-locking stack racks offer stability for the tips while saving valuable lab bench space

Pipette Tip Compatibility

Axygen Axytip® (single channel)								(multi-channel)				Axygen Axytip-16®				Biohit Proline (single channel)				(multi-channel)				Biohit e-Line (single channel)				(multi-channel)				Biohit m-Line® (s/ch)				< Pipettor Brand/make	
0.1-2µl	0.5-10µl	2-20µl	5-50µl	10-100µl	20-200µl	50-250µl	100-1000µl	1-10µl	5-50µl	20-200µl	50-300µl	0.2-2µl	0.5-10µl	5-50µl	0.2-10µl	5-100µl	10-250µl	10-500µl	50-1000µl	0.2-10µl	5-100µl	25-250µl	0.2-10µl	5-120µl	10-300µl	50-1000µl	0.2-10µl	5-120µl	10-300µl	0.5-10µl	2-20µl	10-100µl	Page #	< Volume Range			
Non Filter Tips																																Volume/Axygen Tip					
												✓	✓	✓																				7	0.1-60µl, T-384		
												✓	✓	✓																				7	0.1-30µl, T-1536		
✓	✓							✓							✓					✓			✓			✓								3	0.1-10µl, T-300		
✓	✓							✓							✓					✓			✓			✓								3	0.1-10µl, TXL-10		
																																			3	0.1-20µl, T-400	
			✓	✓	✓	✓			✓	✓	✓					✓	✓				✓	✓		✓	✓		✓	✓		✓	✓			4	1-200µl, T-200		
																																			4	1-200µl, TE-204	
			✓	✓	✓	✓			✓	✓	✓					✓	✓				✓	✓		✓	✓		✓	✓		✓	✓			5	1-200µl, T-205-WB		
			✓	✓	✓	✓			✓	✓	✓					✓	✓				✓	✓		✓	✓		✓	✓		✓	✓			4	1-200µl, TR-222		
					✓	✓	✓		✓	✓	✓					✓	✓				✓	✓		✓	✓		✓	✓				✓		5	1-250µl, TR-333		
					✓	✓			✓	✓	✓					✓	✓				✓	✓		✓	✓		✓	✓				✓		5	1-300µl, T-350		
							✓											✓	✓						✓									6	100-1000µl, T-1000		
							✓											✓	✓						✓									6	100-1000µl, T-1005-WB		
							✓											✓	✓						✓									6	100-1200µl, T-1200		
																																			6	15-1250µl, MTX-1250	
Aerosol Barrier Tips																																Volume/Axygen Tip					
												✓	✓	✓																					7	0.1-30µl, TF-384-30	
✓	✓							✓							✓					✓			✓			✓			✓						3	0.1-10µl, TF-300	
✓	✓							✓							✓					✓			✓			✓			✓						3	0.1-10µl, TXLF-10	
																																				3	0.1-10µl, TF-400
																																				3	0.1-20µl, TF-420
			✓																												✓					4	0.5-20µl, TF-20
				✓				✓																												4	0.5-50µl, TF-50
					✓											✓					✓			✓			✓					✓			4	1-100µl, TF-100	
																✓					✓			✓			✓								4	1-150µl, TF-150	
						✓			✓								✓				✓			✓			✓								4	1-200µl, TF-200	
						✓			✓								✓				✓			✓			✓								5	1-200µl, TF-205-WB	
							✓			✓							✓				✓			✓			✓								5	1-300µl, TF-350	
							✓											✓						✓											6	100-1000µl, TF-1000	
								✓											✓						✓										6	100-1000µl, TF-1005-WB	
																			✓							✓									6	100-1100µl, TF-1200	
																																				6	15-1250µl, MTXF-1250

Pipette Tip Compatibility

< Pipettor Brand/make		Biohit m-Line®		BrandTech Transferpette												Capp Aero				384 format	Eppendorf Electronic																	
		single ch	multi-ch	single channel						multi-channel						single/multi-ch				multi-ch																		
< Volume Range	Page #	20-200µl	100-1000µl	0.5-10µl	5-100µl	30-300µl	0.1-1µl	0.5-10µl	2-20µl	Ultra Micro	2-20µl	5-50µl	10-100µl	20-200µl	25-250µl	100-1000µl	0.5-10µl	2-20µl	2.5-25µl	5-50µl	10-100µl	20-200µl	30-300µl	0.2-2µl	0.5-10µl	5-50µl	10-100µl	25-200µl	50-300µl	100-1000µl	0.2-2µl	0.5-10µl	5-50µl	0.5-10µl	5-100µl	2-200µl	50-1000µl	
Volume/Axygen Tip	Non Filter Trips																																					
0.1-60µl, T-384	7																															✓	✓	✓				
0.1-30µl, T-1536	7																															✓	✓	✓				
0.1-10µl, T-300	3			✓			✓	✓											✓					✓	✓											✓		
0.1-10µl, TXL-10	3			✓			✓	✓											✓					✓	✓											✓		
0.1-20µl, T-400	3								✓																													
1-200µl, T-200	4	✓			✓	✓					✓	✓	✓	✓	✓				✓	✓	✓	✓	✓	✓			✓	✓	✓	✓						✓	✓	
1-200µl, T-205-WB	5	✓			✓	✓					✓	✓	✓	✓	✓				✓	✓	✓	✓	✓	✓			✓	✓	✓	✓						✓	✓	
1-200µl, TR-222	4	✓			✓	✓					✓	✓	✓	✓	✓				✓	✓	✓	✓	✓	✓			✓	✓	✓	✓						✓	✓	
1-250µl, TR-333	5	✓			✓	✓								✓	✓	✓						✓	✓	✓			✓	✓	✓							✓	✓	
1-300µl, T-350	5	✓			✓	✓								✓	✓	✓						✓	✓	✓			✓	✓	✓							✓	✓	
100-1000µl, T-1000	6		✓													✓																✓						✓
100-1000µl, T-1005-WB	6		✓													✓																✓						✓
100-1200µl, T-1200	6		✓													✓																✓						✓
15-1250µl, MTX-1250	6																																					
Volume/Axygen Tip	Aerosol Barrier Tips																																					
0.1-30µl, TF-384-30	7																															✓	✓	✓				
0.1-10µl, TF-300	3			✓			✓	✓											✓	✓	✓			✓	✓										✓			
0.1-10µl, TXLF-10	3			✓			✓	✓											✓	✓	✓			✓	✓										✓			
0.1-20µl, TF-420	3								✓																													
0.5-20µl, TF-20	4									✓																												
0.5-50µl, TF-50	4											✓													✓													
1-100µl, TF-100	4				✓								✓													✓										✓		
1-150µl, TF-150	4																																					
1-200µl, TF-200	4	✓				✓								✓	✓								✓				✓	✓									✓	
1-200µl, TF-205-WB	5	✓				✓								✓	✓								✓				✓	✓									✓	
1-300µl, TF-350	5					✓									✓																							
100-1000µl, TF-1000	6		✓													✓							✓										✓					✓
100-1000µl, TF-1005-WB	6		✓													✓							✓										✓					✓
100-1100µl, TF-1200	6		✓													✓							✓															✓
15-1250µl, MTXF-1250	6																																					

Pipette Tip Compatibility

Eppendorf Reference						Eppendorf Research (single channel)						Eppendorf (multi-channel)						ThermoLabsystems Finnpipette (single channel)						(multi- ch)	Gilson Pipetman (single channel)						m/ ch	< Pipettor Brand/make					
0.1-10µl	2-20µl Ultra Micro	2-20µl	10-100µl	20-200µl	100-1000µl	0.1-2.5µl	0.5-10µl	2-20µl	10-100µl	20-200µl	100-1000µl	0.5-10µl	5-100µl	50-100µl	20-300µl	30-300µl	50-1200µl	0.2-10µl	0.5-10µl	5-40µl	40-200µl	100-1000µl	200-1000µl	5-50µl	50-300µl	P2, 0.1-2µl	P10, 0.2-10µl	P20, 2-20µl	P100, 10-100µl	P200, 20-200µl	P1000, 100-1000µl			P200-M8, 20-200µl	Page #	< Volume Range	
Non Filter Tips																																Volume/Axygen Tip					
																																		7	0.1-60µl, T-384		
																																		7	0.1-30µl, T-1536		
✓						✓	✓					✓						✓	✓								✓	✓						3	0.1-10µl, T-300		
✓						✓	✓					✓						✓	✓								✓	✓						3	0.1-10µl, TXL-10		
	✓																																	3	0.1-20µl, T-400		
		✓	✓	✓				✓	✓	✓			✓	✓	✓	✓				✓	✓			✓	✓				✓	✓	✓	✓	✓	4	1-200µl, T-200		
		✓	✓	✓				✓	✓	✓				✓	✓	✓	✓			✓	✓			✓	✓				✓	✓	✓	✓	✓	5	1-200µl, T-205-WB		
		✓	✓	✓				✓	✓	✓				✓	✓	✓	✓			✓	✓			✓	✓				✓	✓	✓	✓	✓	4	1-200µl, TR-222		
			✓	✓				✓	✓					✓	✓	✓	✓				✓			✓					✓	✓			✓	5	1-250µl, TR-333		
			✓	✓				✓	✓					✓	✓	✓	✓				✓			✓					✓	✓			✓	5	1-300µl, T-350		
				✓							✓						✓					✓	✓								✓			6	100-1000µl, T-1000		
				✓							✓						✓					✓	✓								✓			6	100-1000µl, T-1005-WB		
				✓							✓						✓					✓	✓								✓			6	100-1200µl, T-1200		
																					✓	✓												6	15-1250µl, MTX-1250		
Aerosol Barrier Tips																																Volume/Axygen Tip					
																																		7	0.1-30µl, TF-384-30		
✓							✓					✓						✓	✓								✓	✓						3	0.1-10µl, TF-300		
✓						✓	✓					✓						✓	✓								✓	✓						3	0.1-10µl, TXLF-10		
	✓																																		3	0.1-20µl, TF-420	
		✓						✓																					✓						4	0.5-20µl, TF-20	
																			✓						✓										4	0.5-50µl, TF-50	
			✓					✓					✓	✓															✓						4	1-100µl, TF-100	
																			✓					✓											4	1-150µl, TF-150	
				✓						✓				✓	✓				✓					✓							✓			✓	4	1-200µl, TF-200	
				✓						✓				✓	✓					✓				✓							✓			✓	5	1-200µl, TF-205-WB	
														✓	✓									✓											5	1-300µl, TF-350	
				✓							✓										✓	✓										✓			6	100-1000µl, TF-1000	
				✓							✓											✓	✓									✓			6	100-1000µl, TF-1005-WB	
				✓							✓						✓					✓	✓										✓		6	100-1100µl, TF-1200	
																																				6	15-1250µl, MTXF-1250

Pipette Tip Compatibility

< Pipettor Brand/make		Labnet Labpette					Labnet BioPette E					Matrix Impact/ Impact2 (s/mc)	Nichiryo/Oxford Benchmate					Rainin EDP3 (single channel)																	
		single channel			multi-channel		single channel		multi-channel																										
< Volume Range	Page #	0.1-2µl	0.5-10µl	2-20µl	10-100µl	20-200µl	100-1000µl	1-10µl	5-50µl	20-200µl	50-300µl	0.5-10µl	2-20µl	10-200µl	100-1000µl	0.5-10µl	2-20µl	10-200µl	100-1200µl	2-125µl	2-20µl	15-1250µl	0.5-10µl	2-20µl	10-50µl	10-100µl	20-200µl	100-1000µl	E-MC-10, 0.5-10µl	E2-25, 2.5-25µl	E2-100, 10-100µl	E2-250, 25-250µl	E2-100, 100-1000µl		
Volume/Axygen Tip	Non Filter Trips																																		
0.1-60µl, T-384	7																																		
0.1-30µl, T-1536	7																																		
0.1-10µl, T-300	3	✓	✓					✓				✓	✓			✓	✓						✓							✓					
0.1-10µl, TXL-10	3	✓	✓					✓				✓	✓			✓	✓						✓							✓					
0.1-20µl, T-400	3																																		
1-200µl, T-200	4			✓	✓	✓			✓	✓	✓			✓				✓		✓				✓	✓						✓	✓	✓		
1-200µl, T-205-WB	5			✓	✓	✓			✓	✓	✓			✓				✓		✓				✓	✓						✓	✓	✓		
1-200µl, TR-222	4			✓	✓	✓			✓	✓	✓			✓				✓		✓				✓	✓						✓	✓	✓		
1-250µl, TR-333	5				✓	✓				✓	✓			✓				✓			✓											✓	✓		
1-300µl, T-350	5				✓	✓				✓	✓			✓				✓														✓	✓		
100-1000µl, T-1000	6						✓							✓				✓																✓	
100-1000µl, T-1005-WB	6						✓							✓				✓																✓	
100-1200µl, T-1200	6						✓							✓				✓																✓	
15-1250µl, MTX-1250	6																				✓														
Volume/Axygen Tip	Aerosol Barrier Tips																																		
0.1-30µl, TF-384-30	7																																		
0.1-10µl, TF-300	3	✓	✓					✓				✓				✓							✓							✓					
0.1-10µl, TXLF-10	3	✓	✓					✓				✓				✓							✓							✓					
0.1-20µl, TF-420	3												✓			✓																			
0.5-20µl, TF-20	4			✓																			✓								✓				
0.5-50µl, TF-50	4								✓																✓						✓				
1-100µl, TF-100	4				✓																											✓			
1-150µl, TF-150	4																			✓															
1-200µl, TF-200	4					✓				✓	✓			✓				✓		✓												✓			
1-200µl, TF-205-WB	5					✓				✓	✓			✓				✓		✓												✓			
1-300µl, TF-350	5										✓																						✓		
100-1000µl, TF-1000	6						✓																												✓
100-1000µl, TF-1005-WB	6						✓																												✓
100-1100µl, TF-1200	6						✓							✓																					✓
15-1250µl, MTXF-1250	6																				✓														


Pipette Tip Compatibility

Rainin EDP3 (m/ch)		Rainin Latch Mode						Socorex Calibra/Accura										VWR and VWR Signature										Page #	< Pipettor Brand/make					
								(single channel)					(multi-channel)					(single channel)					(multi-channel)											
EP-M8-10, 0.5-10µl	EP-M8-30, 10-30µl	R2, 0.1-2µl	R10, 0.2-10µl	R20, 0.2-20µl	R100, 10-100µl	R200, 20-200µl	R1000, 100-1000µl	0.1-20µl	0.2-20µl	0.5-10µl	1-10µl	2-20µl	10-100µl	20-200µl	100-1000µl	1-10µl	5-50µl	10-100µl	20-200µl	50-200µl	0.1-20µl	0.5-10µl	2-20µl	5-50µl	10-100µl	20-200µl	50-200µl	100-1000µl	1-10µl	5-50µl	20-200µl	50-300µl		
Non Filter Tips																																	Volume/Axygen Tip	
																															7	0.1-60µl, T-384		
																															7	0.1-30µl, T-1536		
✓		✓	✓					✓	✓	✓	✓					✓					✓	✓							✓		3	0.1-10µl, T-300		
✓		✓	✓					✓	✓	✓	✓					✓					✓	✓							✓		3	0.1-10µl, TXL-10		
																															3	0.1-20µl, T-400		
	✓			✓	✓	✓						✓	✓	✓			✓	✓	✓	✓			✓	✓	✓	✓	✓		✓	✓	✓	4	1-200µl, T-200	
	✓			✓	✓	✓						✓	✓	✓			✓	✓	✓	✓			✓	✓	✓	✓	✓		✓	✓	✓	5	1-200µl, T-205-WB	
	✓			✓	✓	✓						✓	✓	✓			✓	✓	✓	✓			✓	✓	✓	✓	✓		✓	✓	✓	4	1-200µl, TR-222	
	✓				✓	✓							✓	✓					✓	✓					✓	✓	✓		✓	✓	✓	5	1-250µl, TR-333	
	✓				✓	✓							✓	✓				✓	✓	✓					✓	✓	✓		✓	✓	✓	5	1-300µl, T-350	
							✓								✓													✓				6	100-1000µl, T-1000	
							✓								✓													✓				6	100-1000µl, T-1005-WB	
							✓								✓													✓				6	100-1200µl, T-1200	
																																6	15-1250µl, MTX-1250	
Aerosol Barrier Tips																																	Volume/Axygen Tip	
																															7	0.1-30µl, TF-384-30		
✓		✓	✓					✓	✓	✓	✓					✓					✓	✓							✓		3	0.1-10µl, TF-300		
✓		✓	✓					✓	✓	✓	✓					✓					✓	✓							✓		3	0.1-10µl, TXLF-10		
																																3	0.1-10µl, TF-400	
																																3	0.1-20µl, TF-420	
				✓								✓										✓										4	0.5-20µl, TF-20	
																✓							✓						✓			4	0.5-50µl, TF-50	
					✓								✓											✓								4	1-100µl, TF-100	
																																4	1-150µl, TF-150	
	✓					✓							✓												✓	✓			✓	✓	4	1-200µl, TF-200		
	✓					✓								✓											✓	✓			✓	✓	5	1-200µl, TF-205-WB		
	✓																									✓				✓	5	1-300µl, TF-350		
														✓														✓				6	100-1000µl, TF-1000	
															✓													✓				6	100-1000µl, TF-1005-WB	
															✓													✓				6	100-1100µl, TF-1200	
																																6	15-1250µl, MTXF-1250	

PCR Products

Axygen PCR Plates

- ▶ Barcoding available on skirted plates
- ▶ Available in a wide variety of sizes, configurations and colours
- ▶ Manufactured from 99.9% pure virgin polypropylene in a clean, controlled 'state of the art' facility
- ▶ Unique cap design prevents sample evaporation
- ▶ Certified to be RNase-, DNase- and Endotoxin safe
- ▶ Quantitative PCR compatible tubes and plates for a wide range of Real Time PCR instruments
- ▶ Ultra-thin and consistent wall thickness allows precise thermal transfer
- ▶ Full PCR multi-well plate compatibility chart on pages 25-26
- ▶ All multi-well plate measurements and dimensions available in PDF format for automation applications



Axygen PCR Tubes

PCR tubes require a thin and consistent wall thickness to reduce the insulating effect of the tube. Axygen PCR tubes are manufactured to the highest quality standards so your results will be consistent every time. Unlike some PCR tubes that have a short cap which may allow for sample evaporation during thermal cycling, Axygen PCR tubes are sealed with a full-length, even insertion cap which ensures a tight fit and eliminates the worry of sample evaporation.



Plate Sealing

Each "well sealer" incorporates a "scored" area for puncturing by a syringe needle. This allows samples to be dispensed and/or aspirated even while the

AxyMat is in place. Each 'well-sealer', once punctured, will reseal itself, ensuring an airtight seal to the well.

PCR Plates and Sealing Mats



AM-96-PCR-RD


96-well Plates and Mats for 0.2ml thermal cycler blocks

No skirt, elevated wells

Axygen Cat No	Volume	Colour	Microplate Type	Packaging
PCR-96-C	200µl	Clear	96-well, No Skirt	Bulk
PCR-96-MB-C	200µl	Clear	96-well, No Skirt, Elevated Wells	Bulk
AM-96-PCR-RD		Natural	Sealing Mat for 96-well PCR Microplates	Bulk

Packaging Description: Plates = 10 plates/pack, 5 packs/case; Mats = 10 mats/pack, 5 packs/case**Application/Compatibility:** Standard thermal cycling; No Skirt Stratagene MX4000; Elevated Wells Megabace sequencer

- 96 Well No-Skirt PCR plate
- Clear, thin wall Well bottom



96-well plates and mats for 0.2ml thermal cycler blocks

- Fits 0.2ml thermal cycler blocks
- 96-well Flat top PCR plate
- Fits ABI PRISM® 3100, 3130, 3730 and 3700 capillary sequencers plus Stratagene MX-3000
- Clear, thin wall well bottom

Volume to Brim of Well
340µl


Working Volume
300µl

Volume with Axymat
250µl

Maximum G-force = 4,000 RCF

Sealing Options

- Axymats
- Heat Sealing
- Adhesive Films and Foils
- Flat & Domed Cap Strips



PCR-96-C

No skirt

Axygen Cat No	Volume	Colour	Microplate Type	Packaging
PCR-96-FLT-C	200µl	Clear	96-well, No Skirt	Bulk
PCR-96-FLT-W	200µl	Clear	96-well, No Skirt, White	Bulk
PCR-96-FLT-BK	200µl	Clear	96-well, No Skirt, Black	Bulk
AM-96-PCR-RD		Natural	Sealing Mat for 96-well PCR Microplates	Bulk

Packaging Description: Plates = 5 plates/sleeve, 5 sleeves/pack, 4 packs/case; Mats = 10 mats/pack, 5 packs/case**Application/Compatibility:** Standard thermal cycling, BioRad qPCR systems, Stratagene MX-3000

Volume to Brim of Well
340µl

Working Volume
300µl

Volume with Axymat
200µl

Maximum G-force = 4,000 RCF

Sealing Options

- Axymats
- Heat Sealing
- Adhesive Films and Foils
- Flat & Domed Cap Strips



PCR Plates and Sealing Mats

96-well Plates and Mats for 0.2ml thermal cycler blocks

No skirt, low profile



96-well plates and mats for 0.2ml thermal cycler blocks

Axygen Cat No	Volume	Colour	Microplate Type	Packaging
PCR-96-LP-FLT-C	100µl	Clear	96-well, No Skirt, Low Profile	Bulk
PCR-96-LP-FLT-BK	100µl	Black	96-well, No Skirt, Low Profile	Bulk
PCR-96-LP-FLT-W	100µl	White	96-well, No Skirt, Low Profile	Bulk
AM-96-PCR-RD		Natural	Sealing Mat for 96-well PCR Microplates	Bulk

Packaging Description:

Plates = 5 plates/sleeve, 5 sleeves/pack, 4 packs/case; Mats = 10 mats/pack, 5 packs/case

Application/Compatibility:

Standard Biometra thermal cyclers, Eppendorf MasterCycler qPCR, MJ Opticon/Chromo4 qPCR



- Suitable for 0.1ml thermal cycler blocks
- 96-well Flat top low profile PCR plate
- Clear, thin wall well bottom
- Also available in black and white

Volume to Brim of Well
220µl


Working Volume
200µl

Volume with Axymat
106µl

Maximum G-force = 4,000 RCF

Sealing Options

- Axymats
- Heat Sealing
- Adhesive Films and Foils
- Flat & Domed Cap Strips



Segmented



96-well plates and mats for 0.2ml thermal cycler blocks

Axygen Cat No	Volume	Colour	Microplate Type	Packaging
PCR-96-SG-C	200µl	Clear	96-well, Segmented	Bulk
AM-96-PCR-RD		Natural	Sealing Mat for 96-well PCR Microplates	Bulk

Packaging Description:

Plates = 10 plates/pack, 5 packs/case; Mats = 10 mats/pack, 5 packs/case

Application/Compatibility:

Standard thermal cycling, Beckman CEQ Sequencers

Volume to Brim of Well
320µl


Working Volume
280µl

Volume with Axymat
240µl

Maximum G-force = 4,000 RCF

Sealing Options

- Axymats
- Heat Sealing
- Adhesive Films and Foils
- Flat & Domed Cap Strips



- 96 Well Segmented PCR plate

PCR Plates and Sealing Mats



96-well Plates and Mats for 0.2ml thermal cycler blocks

Elevated skirt

96-well plates and mats for 0.2ml thermal cycler blocks

Axygen Cat No	Volume	Colour	Microplate Type	Packaging
PCR-96-AB-C	200µl	Clear	96-well, Elevated Skirt	Bulk
AM-96-PCR-RD		Natural	Sealing Mat for 96-well PCR Microplates	Bulk

Packaging Description:

Plates = 10 plates/pack, 5 packs/case; Mats = 10 mats/pack, 5 packs/case

Application/Compatibility:

Standard thermal cycling, ABI Real Time PCR 7300, 7500, 7900, qPCR and ABI Sequencing



Volume to Brim of Well
335µl


Working Volume
300µl

Volume with Axymat
260µl

Maximum G-force = 4,000 RCF

Sealing Options

- Axymats
- Heat Sealing
- Adhesive Films and Foils
- Flat & Domed Cap Strips



- 96 Well Semi-Skirted PCR Plate
- Single Notch Corner
- Designed for ABI Thermal Cyclers

Low profile, half skirt

96-well plates and mats for 0.2ml thermal cycler blocks

Axygen Cat No	Volume	Colour	Microplate Type	Packaging
PCR-96-LP-AB-C	100µl	Clear	96-well Rapid PCR Plate, Low Profile	Bulk
PCR-96-LP-AB-BK	100µl	Black	96-well Rapid PCR Plate, Low Profile	Bulk
PCR-96-LP-AB-W	100µl	White	96-well Rapid PCR Plate, Low Profile	Bulk
AM-96-PCR-RD		Natural	Sealing Mat for 96-well PCR Microplates	Bulk

Packaging Description:

Plates = 5 plates/sleeve, 5 sleeves/pack, 4 packs/case; Mats = 10 mats/pack, 5 packs/case

Application/Compatibility:

ABI Fast PCR 7500, 7900 Fast, 9800, Veriti and StepOne



Volume to Brim of Well
240µl


Working Volume
200µl

Volume with Axymat
140µl

Maximum G-force = 4,000 RCF

Sealing Options

- Axymats
- Heat Sealing
- Adhesive Films and Foils
- Flat & Domed Cap Strips




- 96 Well Semi-Skirted Low Profile PCR Plate
- Optimized for Fast PCR
- Reduced volume minimizes potential evaporation
- Designed for ABI Thermal Cyclers

PCR Plates and Sealing Mats



96-well Plates and Mats for 0.2ml thermal cycler blocks



96-well plates and mats for 0.2ml thermal cycler blocks

Half skirt

Axygen Cat No	Volume	Colour	Microplate Type	Packaging
PCR-96M2-HS-C	200µl	Clear	96-well, Half Skirt	Bulk
AM-96-PCR-RD		Natural	Sealing Mat for 96-well PCR Microplates	Bulk

Packaging Description:

Plates = 10 plates/pack, 5 packs/case; Mats = 10 mats/pack, 5 packs/case

Application/Compatibility:

Standard thermal cycling, plus ABI PCR 2700, 2720, 9700, 9800, 7300, 7500 and 7900 and ABI sequencing units



- 96-well Half skirted PCR plate
- Single Notch Corner
- Clear, thin wall well bottom
- Also available in black and white

Volume to Brim of Well
340µl


Working Volume
300µl

Volume with Axymat
240µl

Maximum G-force = 4,000 RCF

Sealing Options

- Axymats
- Heat Sealing
- Adhesive Films and Foils
- Flat & Domed Cap Strips



Full skirt

Axygen Cat No	Volume	Colour	Microplate Type	Packaging
PCR-96-FS-C	200µl	Clear	96-well, Full Skirt	Bulk
AM-96-PCR-RD		Natural	Sealing Mat for 96-well PCR Microplates	Bulk

Packaging Description:

Plates = 10 plates/pack, 5 packs/case; Mats = 10 mats/pack, 5 packs/case

Application/Compatibility:

Standard thermal cycling, Automation Friendly



- 96-well Full Skirt PCR plate
- Single notch corner
- Clear, thin wall well bottom
- Stackable
- Robotic Friendly full skirt design
- Also available in black and white

Volume to Brim of Well
240µl


Working Volume
200µl

Volume with Axymat
140µl

Maximum G-force = 4,000 RCF

Sealing Options

- Axymats
- Heat Sealing
- Adhesive Films and Foils
- Flat & Domed Cap Strips



New Roche LightCycler® 480 Real-Time PCR



Axygen Cat No	Colour	Description	Sealing	Footprint Film
PCR-96-LC480-W	White	96-Well PCR Microplate for Roche 480 LightCycler®	UC-500 included	SBS
PCR-96-LC480-W-BC	White	96-Well PCR Microplate for Roche 480 LightCycler®, Bar-Coded	UC-500 included	SBS
PCR-96-LC480-W-NF	White	96-Well PCR Microplate for Roche 480 LightCycler®	None	SBS

Packaging Description:


10 Plates /Pack, 5 Pack/Case



Maximum Volume: 45µl
Working Volume: 30µl
Volume with Axymat 6µl

PCR Plates and Sealing Mats

384-well Plates and Mats



New

Roche LightCycler® 480

Axygen Cat No	Colour	Description	Sealing	Footprint Film
PCR-384-LC480-W-BC	White	PCR Plate, 384-well for Roche Lightcycler® 480, Barcoded	UC-500 included	SBS
PCR-384-LC480-W	White	PCR Plate, 384-well for Roche Lightcycler® 480	UC-500 included	SBS
PCR-384-LC480-W-NF	White	PCR Plate, 384-well for Roche Lightcycler® 480	None	SBS

Packaging Description: 10 Plates /Pack; 5 Pack/Case



Maximum Volume: 45µl
Working Volume: 30µl
Volume with Axymat 6µl



384-well plates and mats
Notches on A24 and P24 side

Skirted

Axygen Cat No	Volume	Colour	Microplate Type	Footprint Film
PCR-384-C	50µl	Clear	384-well	Bulk
AM-384-PCR-RD		Natural	Sealing Mat for 384-well PCR Microplates	Bulk
AM-384-PCR-RV		Natural	Volume Reducing Sealing Mat*	Bulk

Packaging Description: Plates = 10 plates/pack, 5 packs/case; Mats = 10 mats/pack, 5 packs/case

Application/Compatibility: Standard thermal cycling



Volume to Brim of Well
50µl

Working Volume
40µl


Volume with Axymat
30µl

Volume with VR Axymat
6.0µl

Maximum G-force = 4,000 RCF

Sealing Options

- Axymats
- Heat Sealing
- Adhesive Films and Foils



- 384-well Double Notch PCR plate
- Robotic Friendly full skirt design
- **Double** notch corner



384-well plates and mats
Notch on A24 side

Skirted

Axygen Cat No	Volume	Colour	Microplate Type	Footprint Film
PCR-384M2-C	55µl	Clear	384-well	Bulk
AM-384-PCR-RD		Natural	Sealing Mat for 384-well PCR Microplates	Bulk
AM-384-PCR-RV		Natural	Volume Reducing Sealing Mat*	Bulk

Packaging Description: Plates = 10 plates/pack, 5 packs/case; Mats = 10 mats/pack, 5 packs/case

Application/Compatibility: Standard thermal cycling, Fully ABI compatible for qPCR and Sequencing



Volume to Brim of Well
55µl

Working Volume
50µl


Volume with Axymat
40µl

Volume with VR Axymat
6.5µl

Maximum G-force = 4,000 RCF

Sealing Options

- Axymats
- Heat Sealing
- Adhesive Films and Foils



- 384-well Single Notch PCR plate
- Robotic Friendly full skirt design
- **Single** notch corner

PCR Plates and Sealing Mats



384-well Plates and Mats

Skirted, rigid



384-well plate
Notch on A24 side

Axygen Cat No	Volume	Colour	Microplate Type	Footprint Film
PCR-384-RGD-C	50µl	Clear	384-well RigiPlate®	Bulk
AM-384-PCR-RD		Natural	Sealing Mat for 384-well PCR Microplates	Bulk
AM-384-PCR-RV		Natural	Volume Reducing Sealing Mat*	Bulk

Packaging Description: Plates = 10 plates/pack, 2 packs/sleeve, 5 sleeves/case; Mats = 10 mats/pack, 5 packs/case


Application/Compatibility: Standard thermal cycling, ABI sequencing, automation applications

Volume to Brim of Well	Working Volume	Volume with Axymat	Volume with VR Axymat
50µl	49.5µl	30µl	6.5µl

Maximum G-force = 4,000 RCF

Sealing Options

- Axymats
- Heat Sealing
- Adhesive Films and Foils



- 384-well RigiPlate® PCR plate
- Robotic friendly rigid plate with full skirt
- Single notch corner



384-well plate
Notch on A24 side

Skirted, elevated wells

Axygen Cat No	Volume	Colour	Microplate Type	Footprint Film
PCR-384-55-C	55µl	Clear	384-well, 55µl	Bulk
AM-384-PCR-RD		Natural	Sealing Mat for 384-well PCR Microplates	Bulk
AM-384-PCR-RV		Natural	Volume Reducing Sealing Mat*	Bulk

Packaging Description: Plates = 10 plates/pack, 5 packs/case; Mats = 10 mats/pack, 5 packs/case


Application/Compatibility: Standard thermal cycling, ABI sequencing, qPCR

Volume to Brim of Well	Working Volume	Volume with Axymat	Volume with VR Axymat
55µl	50µl	45µl	10.5µl

Maximum G-force = 4,000 RCF

Sealing Options

- Axymats
- Heat Sealing
- Adhesive Films and Foils



- 384-well Single Notch PCR plate
- Raised wells allow 55µl volume
- Single notch corner

PCR Plates and Sealing Mats

Sealing Film Options

Real time PCR Accessories

Axygen Cat No	Material	Description	Packaging	App Type
UC-500	Polyester	Ultra Clear Film, Pressure Sensitive	Bulk	
Ultra Clear for Real Time PCR applications				

Packaging Description: Films = 100 films/pack, 5 packs/case



Axygen Cat No	Material	Description	Packaging	App Type
PCR-AS-200	Aluminium	Aluminium Seal, 35µm	Bulk	
PCR-AS-600	Aluminium	Aluminium Seal, 50µm	Bulk	
PCR-TS	Polypropylene	Clear Seal, 60µm	Bulk	
PCR-TS-900	Polypropylene	Clear Seal, 120µm	Bulk	
MF-111	Aluminium/Ethylene/Vinyl	Aluminium Seal, 60µl	Bulk	
MF-300	Litro/Ethylene/Vinyl	Aluminium Seal, paper backed, 85µl	Bulk	
BF-400	Rayon	Breathable film, 50µm	Bulk	
BF-400-S	Rayon	Breathable film sterile, 50µm	Bulk	

 = self adhesive  = heat seal

Packaging Description: * Films = 100 films/pack, 10 packs/case
** 25 per bag, 2 bags per pack, 10 packs per case

Capillary sequencing products

Axygen Cat No	Volume	Colour	Description	Packaging
TUB-310-NC	0.5ml	Clear	Capless Tube for ABI Prism 310 sequencer	Bulk

Packaging Description: 500 tubes/pack, 5 packs/case

Axygen Cat No	Volume	Colour	Description	Packaging
AM-SEPTA-310	-	Grey	Individual SeptaCaps for 0.5ml ABI Prism 310 sequencer tubes	Bulk


Packaging Description: 500 caps/pack, 5 packs/case

Axygen Cat No	Volume	Colour	Description	Packaging
AM-96-SEPTA-3100	-	Grey	Septa Mat for ABI Multi-Capillary Sequencing Instruments	Bulk

Packaging Description: 10 mats/pack, 5 packs/case



Real time PCR Accessories



Capillary sequencing products



PCR Tubes, Flat and Domed

0.2ml and 0.5ml



PCR Tube

Axygen Cat No	Colour	Volume	Tube Type	Packaging
PCR-02-C	MaxyClear	0.2ml	Thin Wall, Flat Cap	Bulk
PCR-02-A	Assorted	0.2ml	Thin Wall, Flat Cap	Bulk
PCR-02-B	Blue	0.2ml	Thin Wall, Flat Cap	Bulk
PCR-02-G	Green	0.2ml	Thin Wall, Flat Cap	Bulk
PCR-02-O	Orange	0.2ml	Thin Wall, Flat Cap	Bulk
PCR-02-R	Red	0.2ml	Thin Wall, Flat Cap	Bulk
PCR-02-V	Violet	0.2ml	Thin Wall, Flat Cap	Bulk
PCR-02-Y	Yellow	0.2ml	Thin Wall, Flat Cap	Bulk
PCR-02-L-C	MaxyClear	0.2ml	Flat Cap, Maxymum Recovery	Bulk

Packaging Description: 1000 tubes/pack, 10 packs/case

0.2ml - domed cap



PCR Tube, domed cap

Axygen Cat No	Colour	Volume	Tube Type	Packaging
PCR-02D-C	MaxyClear	0.2ml	Thin Wall, Domed Cap	Bulk
PCR-02D-A	Assorted	0.2ml	Thin Wall, Domed Cap	Bulk
PCR-02D-B	Blue	0.2ml	Thin Wall, Domed Cap	Bulk
PCR-02D-G	Green	0.2ml	Thin Wall, Domed Cap	Bulk
PCR-02D-O	Orange	0.2ml	Thin Wall, Domed Cap	Bulk
PCR-02D-R	Red	0.2ml	Thin Wall, Domed Cap	Bulk
PCR-02D-V	Violet	0.2ml	Thin Wall, Domed Cap	Bulk
PCR-02D-Y	Yellow	0.2ml	Thin Wall, Domed Cap	Bulk
PCR-02D-L-C	MaxyClear	0.2ml	Domed Cap, Maxymum Recovery	Bulk

Packaging Description: 1000 tubes/pack, 10 packs/case

0.2ml - no cap



PCR Tube, no cap

Axygen Cat No	Colour	Volume	Tube Type	Packaging
PCR-02-NC	MaxyClear	0.2ml	Thin Wall PCR Tubes, No Cap	Bulk

Packaging Description: 1000 tubes/pack, 10 packs/case

0.5ml - flat cap



PCR Tube, flat cap

Axygen Cat No	Colour	Volume	Tube Type	Packaging
PCR-05-C	MaxyClear	0.5ml	Thin Wall, Flat Cap	Bulk
PCR-05-A	Assorted	0.5ml	Thin Wall, Flat Cap	Bulk
PCR-05-B	Blue	0.5ml	Thin Wall, Flat Cap	Bulk
PCR-05-G	Green	0.5ml	Thin Wall, Flat Cap	Bulk
PCR-05-O	Orange	0.5ml	Thin Wall, Flat Cap	Bulk
PCR-05-R	Red	0.5ml	Thin Wall, Flat Cap	Bulk
PCR-05-V	Violet	0.5ml	Thin Wall, Flat Cap	Bulk
PCR-05-Y	Yellow	0.5ml	Thin Wall, Flat Cap	Bulk

Packaging Description: 1000 tubes/pack, 10 packs/case

PCR Tubes, Strips and Racks

0.2ml, flat cap, spectrum pack

Axygen Cat No	Colour	Volume	Tube Type	Packaging
PCR-02-SP	Spectrum 	0.2ml	Thin Wall, Flat Cap, Spectrum Pack Blue, Green, Red, Yellow, Orange	Bulk

Packaging Description: 1000 tubes/pack, 10 packs/case, 2 packs of each colour

Axygen Cat No	Colour	Volume	Tube Type	Packaging
PCR-02D-SP	Spectrum 	0.2ml	Thin Wall, Domed Cap, Spectrum Pack Blue, Green, Red, Yellow, Orange	Bulk

Packaging Description: 1000 tubes/pack, 10 packs/case, 2 packs of each colour

Axygen Cat No	Colour	Volume	Tube Type	Packaging
PCR-0208-C	MaxyClear	0.2ml	Thin Wall PCR Tube, 8 per Strip	Bulk
PCR-02CP-C	MaxyClear	0.2ml	Domed 8 Strip Caps	Bulk
PCR-0208-CP-C	MaxyClear	0.2ml	Thin Wall PCR Tubes and Domed Caps, 8 per Strip	Bulk
New PCR-02-FCP-C	MaxyClear	0.2ml	Flat 8 Strip Caps with writing surface	Bulk
New PCR-0208-FCP-C	MaxyClear	0.2ml	Thin Wall PCR Tubes and Flat Caps, 8 per Strip	Bulk
New PCR-2CP-RT-C	MaxyClear	0.2ml	Thin Wall PCR Caps for qPCR, 8 per Strip	Bulk

Packaging Description: 125 strips/pack, 10 packs/case

Axygen Cat No	Colour	Tube Type	Packaging
R-96-PCR-FP	Fluorescent Pink	PCR Storage Rack	Bulk
R-96-PCR-FB	Fluorescent Blue	PCR Storage Rack	Bulk
R-96-PCR-FG	Fluorescent Green	PCR Storage Rack	Bulk
R-96-PCR-FY	Fluorescent Yellow	PCR Storage Rack	Bulk
R-96-PCR-FO	Fluorescent Orange	PCR Storage Rack	Bulk
R-96-PCR-FSP	5 Fluorescent Colours	PCR Storage Rack, Spectrum Pack	Bulk

Packaging Description: 5 racks/pack, 5 packs/case



PCR tubes, strips and racks

Optical flat cap strips feature ultra-clear upper surfaces, ideal for fluorescent, luminescent and real-time PCR applications. They offer a light transmittance that is 75% higher than with standard strip caps. Made to seal tube strips and 96-well plates.



PCR racks

PCR Plate Compatibility

Axygen Plate		PCR-96-FLT	PCR-96-LP-FLT	PCR-96	PCR-96-MB	PCR-96-SG	PCR-96M2-HS	PCR-96-AB	PCR-96-LP-AB	PCR-96-FS	PCR-384	PCR-384M2	PCR-384-55	PCR-384-RGD
Catalogue page		16	17	16	16	17	19	18	18	19	20	20	21	21
Brand	Model													
Real Time PCR Thermal Cyclers														
Applied Biosystems®	7000	✓					✓	✓						
	7300	✓					✓	✓						
	7500	✓					✓	✓	✓*					
	7700	✓					✓	✓						
	7900HT						✓	✓	✓*			✓		
	StepOne								✓					
BioRad®	iCycler	✓		✓		✓	✓							
	MyiQ	✓		✓										
	iQ5	✓		✓		✓	✓			✓				
Eppendorf	MasterCycler ep Realplex		✓							✓				
MJ Research™	Opticon		✓							✓				
	Opticon 2		✓							✓				
	Chromo4		✓							✓				
Stratagene®	MX-4000		✓	✓										
	MX-3000	✓												
Techne®	Quantica		✓							✓				
PCR Thermal Cyclers														
Applied Biosystems	Veriti	✓		✓		✓	✓	✓	✓*		✓	✓	✓	✓
	9600	✓		✓		✓	✓	✓						
	9700	✓		✓		✓	✓	✓			✓	✓	✓	✓
	9800 FAST								✓					
	2720	✓		✓		✓	✓	✓			✓	✓	✓	✓
Biometra	Uno	✓	✓	✓		✓	✓			✓				
	Uno II	✓	✓	✓			✓				✓	✓	✓	✓
	T1 Thermal Cycler	✓	✓	✓			✓			✓	✓	✓	✓	✓
	Tgradient	✓	✓	✓			✓			✓				
	Trobot	✓	✓	✓			✓			✓	✓	✓	✓	✓
BioRad	iCycler	✓		✓			✓							
	MyCycler	✓		✓			✓							
Corbett Research	PalmCycler 96		✓				✓			✓				
	PalmCycler 384										✓	✓	✓	✓
Eppendorf	Mastercycler	✓	✓	✓			✓			✓				
	Mastercycler ep	✓	✓	✓			✓			✓				
	Mastercycler M384										✓	✓	✓	✓
Flexi	Gene	✓		✓			✓			✓	✓	✓	✓	✓
	Genius	✓		✓			✓			✓				

New: Plates for Roche Lightcycler® - see pages 19-20

*Compatibility with ABI Fast PCR only

PCR-96-FLT	PCR-96-LP-FLT	PCR-96	PCR-96-MB	PCR-96-SG	PCR-96M2-HS	PCR-96-AB	PCR-96-LP-AB	PCR-96-FS	PCR-384	PCR-384M2	PCR-384-55	PCR-384-RGD	Axygen Plate	
16	17	16	16	17	19	18	18	19	20	20	21	21	Catalogue page	
													Model	Brand
PCR Thermal Cyclers														
✓	✓	✓			✓								Single Block	Ericom
✓	✓	✓			✓								TwinBlock	
✓	✓	✓		✓	✓								Deltacycler I	
					✓			✓					PCR Sprint	ThermoHybaid
✓	✓	✓			✓			✓	✓	✓	✓	✓	PCR Express	
✓	✓	✓			✓			✓	✓	✓	✓	✓	Multiblock System	
✓	✓	✓		✓	✓			✓	✓	✓	✓	✓	Touchdown	
✓	✓	✓			✓			✓	✓	✓	✓	✓	Omnigene	
✓	✓	✓			✓			✓					Omn-E	
✓	✓	✓			✓			✓	✓	✓	✓	✓	pxe	
✓	✓	✓			✓			✓	✓	✓	✓	✓	px2	
✓	✓	✓		✓	✓			✓		✓	✓	✓	PTC-100	MJ Research™
✓	✓	✓		✓	✓			✓		✓	✓	✓	PTC-200	
✓	✓	✓		✓	✓			✓		✓	✓	✓	PTC-225 Tetrad	
✓	✓	✓		✓	✓			✓		✓	✓	✓	Dyad/Disciple	
✓	✓	✓		✓	✓			✓					Primus 96	MWG™
									✓	✓	✓	✓	Primus 384	
✓		✓						✓					Robocycler	Stratagene®
								✓					TP240	TaKaRa
✓	✓	✓		✓	✓			✓					TP3000	
✓	✓	✓		✓	✓			✓	✓	✓	✓	✓	Touchgene Gradient (TC512)	Techne®
✓	✓	✓		✓	✓			✓					Genius (TC412)	
✓	✓			✓	✓			✓	✓	✓	✓	✓	Touchgene X	
Sequencers														
✓		✓			✓	✓				✓	✓	✓	3100	Applied Biosystems
✓		✓			✓	✓				✓	✓	✓	3130	
✓		✓			✓	✓			✓	✓	✓	✓	3700	
✓		✓			✓	✓				✓	✓	✓	3730/3730x	
			✓					✓					MegaBACE 500	Amersham
			✓										MegaBACE 1000	
									✓	✓	✓	✓	MegaBACE 4000	
				✓									CEQ	Beckman
								✓					BaseStation	MJ Research
								✓					WAVE System	Transgenomic

Microtubes

MAXYmum Recovery® for the ultimate in sample integrity

Axygen's microcentrifuge tubes are produced from medical grade polypropylene



- Maxymum Recovery & Standard Snaplock tubes – 0.5, 1.5, 1.7 and 2.0ml
- Maxymum Recovery & Standard Screw-cap tubes – 0.5, 1.5 and 2.0ml conical and free-standing
- Durable Plastic Tube Racks – 50, 80 and 81-position
- Aluminum Tube Racks – 48-position for screw cap tubes

MAXYclear SnapLock Microtubes

Axygen 1.5ml, 1.7ml and 2.0ml Snaplock microtubes are engineered to close with a "snap" and stay closed during centrifugation up to 20,000 RCF. The 0.6ml and 1.7ml MAXYclear tubes are manufactured using a copolymer material to offer exceptional strength and chemical resistance. All Axygen SnapLock microtubes have frosted cap surfaces for labelling, frosted panels on the side for writing, a 0.28 mm piercing port in the center of the cap, are tested to 55 psi and are ready for autoclaving.

MAXYclear Screw Cap Microtubes

Axygen screw cap microtubes serve a broad range of laboratory needs including collection, processing, centrifugation, long-term storage and packaging/shipping of restriction enzymes and other reagents. Colour-coded caps provide a syringe port which is easily pierced for radio-isotope labelling and fraction collecting. The threaded 'O' ring design ensures a uniform closure allowing centrifugation up to 20,000 RCF. Ribs are designed to fit racks and facilitate single-handed opening and closing when used with our aluminum AxyRack, found on page 35. See page 70 for information on RCF, or "g-force"



The closure on Axygen Screw Cap Tubes feature an 'O' ring that is formulated and manufactured from a specially selected material that is resistant to many commonly-used laboratory chemicals. The Alignment Orientation Tab (US patent # 5891327) allows the microtube to be aligned with the centrifuge rotor for multiple applications, including desalting. This ensures that the microtube can be re-spun without disturbing the partially pelletized sediment.

- MAXYclear™ for the ultimate in sample visibility - found in all of Axygen's SnapLock tubes
- A wide range of colored tubes for easy sample identification
- SnapLock tubes are guaranteed to stay closed - even during boiling or autoclaving!
- Will withstand up to 20,000 RCF
- SnapLock cap assures efficient seal, yet is still easy to 'flip' open
- Thin membrane in cap center allows easy access to sample by syringe needle
- Certified RNase-, DNase- and endotoxin-safe for total sample integrity
- MAXYmum Recovery - available in most styles for minimal sample retention

* Maxymum Recovery Screw Cap Tubes are available as special order items. please call our customer service department for more information.

Snaplock Microtubes



Maxyclear

- allows recovery of costly samples
- Co-polymer tubes offer exceptional strength and chemical resistance
- Homopolymer tubes are more resistant to autoclaving
- 0.6ml, 1.5ml and 2.0ml microtubes are certified boil proof

0.6ml – Maxyclear



MCT-060-C 0.6ml Microtube

Axygen Cat No	Colour	Volume	Microtube Material	Packaging
MCT-060-C	MaxyClear	0.6ml	Homopolymer	Bulk
MCT-060-A	Assorted*	0.6ml	Homopolymer	Bulk
MCT-060-B	Blue	0.6ml	Homopolymer	Bulk
MCT-060-G	Green	0.6ml	Homopolymer	Bulk
MCT-060-O	Orange	0.6ml	Homopolymer	Bulk
MCT-060-R	Red	0.6ml	Homopolymer	Bulk
MCT-060-V	Violet	0.6ml	Homopolymer	Bulk
MCT-060-X	Amber	0.6ml	Homopolymer	Bulk
MCT-060-Y	Yellow	0.6ml	Homopolymer	Bulk

Packaging Description: 1000 tubes/pack, 10 packs/case**Maximum G-force:** 14,000 RCF

1.7ml – Maxyclear



MCT-175-C 1.7ml Microtube

Axygen Cat No	Colour	Volume	Microtube Material	Packaging
MCT-175-C	MaxyClear	1.7ml	Co-polymer	Bulk
MCT-175-A	Assorted*	1.7ml	Co-polymer	Bulk
MCT-175-B	Blue	1.7ml	Co-polymer	Bulk
MCT-175-G	Green	1.7ml	Co-polymer	Bulk
MCT-175-O	Orange	1.7ml	Co-polymer	Bulk
MCT-175-R	Red	1.7ml	Co-polymer	Bulk
MCT-175-V	Violet	1.7ml	Co-polymer	Bulk
MCT-175-X	Amber	1.7ml	Co-polymer	Bulk
MCT-175-Y	Yellow	1.7ml	Co-polymer	Bulk

Packaging Description: 500 tubes/pack, 10 packs/case**Maximum G-force:** 20,000 RCF

1.5ml – Maxyclear



MCT-150-C 1.5ml Microtube

Axygen Cat No	Colour	Volume	Microtube Material	Packaging
MCT-150-C	MaxyClear	1.5ml	Homopolymer	Bulk
MCT-150-A	Assorted*	1.5ml	Homopolymer	Bulk
MCT-150-B	Blue	1.5ml	Homopolymer	Bulk
MCT-150-G	Green	1.5ml	Homopolymer	Bulk
MCT-150-O	Orange	1.5ml	Homopolymer	Bulk
MCT-150-R	Red	1.5ml	Homopolymer	Bulk
MCT-150-V	Violet	1.5ml	Homopolymer	Bulk
MCT-150-X	Amber	1.5ml	Homopolymer	Bulk
MCT-150-Y	Yellow	1.5ml	Homopolymer	Bulk

Packaging Description: 500 tubes/pack, 10 packs/case**Maximum G-force:** 20,000 RCF

2.0ml – Maxyclear



MCT-200-C 2.0ml Microtube

Axygen Cat No	Colour	Volume	Microtube Material	Packaging
MCT-200-C	MaxyClear	2.0ml	Homopolymer	Bulk
MCT-200-A	Assorted*	2.0ml	Homopolymer	Bulk
MCT-200-B	Blue	2.0ml	Homopolymer	Bulk
MCT-200-G	Green	2.0ml	Homopolymer	Bulk
MCT-200-O	Orange	2.0ml	Homopolymer	Bulk
MCT-200-R	Red	2.0ml	Homopolymer	Bulk
MCT-200-V	Violet	2.0ml	Homopolymer	Bulk
MCT-200-X	Amber	2.0ml	Homopolymer	Bulk
MCT-200-Y	Yellow	2.0ml	Homopolymer	Bulk

Packaging Description: 500 tubes/pack, 10 packs/case**Maximum G-force:** 20,000 RCF

* colors included: blue, green, violet, orange, red and yellow in approximately equal quantities

Snaplock Microtubes



0.6ml

1.5ml

Maxyclear

Axygen Cat No	Colour	Volume	Microtube Materia/Description	Packaging
MCT-060-SP	Spectrum	0.6ml	Homopolymer	Bulk
MCT-150-SP	Spectrum	1.5ml	Homopolymer	Bulk
MCT-175-SP	Spectrum	1.7ml	Co-polymer	Bulk
MCT-200-SP	Spectrum	2.0ml	Homopolymer	Bulk

Packaging Description: 0.6ml = 1000 tubes/pack, 10 packs/case; other sizes = 500 tubes/pack, 10 packs/case.
2 packs of blue, green, orange, red and yellow tubes per case

Maximum G-force: 0.6ml = 14,000 RCF; other size tubes = 20,000 RCF



1.7ml

2.0ml

Maxymum Recovery

Axygen Cat No	Colour	Volume	Microtube Materia/Description	Packaging
MCT-060-L-C	MaxyClear	0.6ml	Homopolymer/Maxymum Recovery	Bulk
MCT-150-L-C	MaxyClear	1.5ml	Homopolymer/Maxymum Recovery	Bulk
MCT-175-L-C	MaxyClear	1.7ml	Co-polymer/Maxymum Recovery	Bulk
MCT-200-L-C	MaxyClear	2.0ml	Homopolymer/Maxymum Recovery	Bulk

Packaging Description: 0.6ml = 500 tubes/pack, 10 packs/case; other sizes = 250 tubes/pack, 10 packs/case.

Maximum G-force: 0.6ml = 14,000 RCF; other size tubes = 20,000 RCF

Pre-Sterilized

Axygen Cat No	Colour	Volume	Microtube Materia/Description	Packaging
MCT-060-C-S	MaxyClear	0.6ml	Homopolymer/Pre-Sterilized	Bulk
MCT-150-C-S	MaxyClear	1.5ml	Homopolymer/Pre-Sterilized	Bulk
MCT-175-C-S	MaxyClear	1.7ml	Co-polymer/Pre-Sterilized	Bulk
MCT-200-C-S	MaxyClear	2.0ml	Homopolymer/Pre-Sterilized	Bulk

Packaging Description: 0.6ml = 1000 tubes/pack, 10 packs/case; other sizes = 500 tubes/pack, 10 packs/case.
2 packs of blue, green, orange, red and yellow tubes per case

Maximum G-force: 0.6ml = 14,000 RCF; other size tubes = 20,000 RCF



1.5ml No Cap

2.0ml No Cap

1.5 and 2.0ml Capless

Axygen Cat No	Colour	Volume	Microtube Materia/Description	Packaging
MCT-150-NC	MaxyClear	1.5ml	Homopolymer/No Cap	Bulk
MCT-200-NC	MaxyClear	2.0ml	Homopolymer/No Cap	Bulk

Packaging Description: 500 tubes/pack, 10 packs/case.

Maximum G-force: 20,000 RCF

**for 1.5 and 2.0ml tubes Tissue Grinder**

Axygen Cat No	Colour	Volume	Microtube Materia/Description	Packaging
PES-15-B-SI	Blue	1.5 & 2.0ml	Pestle/Pre-Sterilized	Individually wrapped

Packaging Description: Individually Wrapped, 100/pack, 4 packs/case

- Durable and inert polypropylene construction
- Designed to fit 1.5ml & 2.0ml centrifuge tubes
- Individually wrapped and pre-sterilized for convenience

Autoclaving Protocol

Autoclave at 121°C/250°F at 15 psi (1 atm.) for 15 minutes. Do not use drying cycle. Remove from autoclave once temperature has reached at least 80°C.

Autoclaving Caution

Excessive exposure to autoclaving heat may cause warping or decreased structural integrity. Do not exceed 121°C / 250°F, 15 psi (1 atm.), 15 minutes.

Screw Cap Tubes



With Caps

0.5ml, conical



0.5ml, conical



ST-45-C

Axygen Cat No	Colour	Volume	Style	Tube Type
SCT-45-C	Clear	0.5ml	Conical	Screw Cap Tubes and Caps
SCT-050-C	Clear	0.5ml	Conical	Screw Cap Tubes and Caps
SCT-050-A	Assorted†	0.5ml	Conical	Screw Cap Tubes and Caps
SCT-050-GR	Grey	0.5ml	Conical	Screw Cap Tubes and Caps
SCT-050-W	White	0.5ml	Conical	Screw Cap Tubes and Caps
SCT-050-P	Pink	0.5ml	Conical	Screw Cap Tubes and Caps
SCT-050-R	Red	0.5ml	Conical	Screw Cap Tubes and Caps
SCT-050-O	Orange	0.5ml	Conical	Screw Cap Tubes and Caps
SCT-050-Y	Yellow	0.5ml	Conical	Screw Cap Tubes and Caps
SCT-050-G	Green	0.5ml	Conical	Screw Cap Tubes and Caps
SCT-050-B	Blue	0.5ml	Conical	Screw Cap Tubes and Caps
SCT-050-V	Violet	0.5ml	Conical	Screw Cap Tubes and Caps
SCT-050-BR	Brown	0.5ml	Conical	Screw Cap Tubes and Caps

Packaging Description: 500 tubes/pack, 8 packs/case; †50/bag, 10 bags/pack, 8 packs/case

Maximum G-force: 20,000 RCF

0.5ml, self-standing



0.5ml, self standing

Axygen Cat No	Colour	Volume	Style	Tube Type
SCT-050-SS-C	Clear	0.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-050-SS-A	Assorted†	0.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-050-SS-GR	Grey	0.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-050-SS-W	White	0.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-050-SS-P	Pink	0.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-050-SS-R	Red	0.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-050-SS-O	Orange	0.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-050-SS-Y	Yellow	0.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-050-SS-G	Green	0.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-050-SS-B	Blue	0.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-050-SS-V	Violet	0.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-050-SS-BR	Brown	0.5ml	Self Standing	Screw Cap Tubes and Caps

Packaging Description: 500 tubes/pack, 8 packs/case; †50/bag, 10 bags/pack, 8 packs/case

Maximum G-force: 20,000 RCF

1.5ml conical



0.5ml, self standing

Axygen Cat No	Colour	Volume	Style	Tube Type
SCT-150-C	Clear	1.5ml	Conical	Screw Cap Tubes and Caps
SCT-150-A	Assorted†	1.5ml	Conical	Screw Cap Tubes and Caps
SCT-150-GR	Grey	1.5ml	Conical	Screw Cap Tubes and Caps
SCT-150-W	White	1.5ml	Conical	Screw Cap Tubes and Caps
SCT-150-P	Pink	1.5ml	Conical	Screw Cap Tubes and Caps
SCT-150-R	Red	1.5ml	Conical	Screw Cap Tubes and Caps
SCT-150-O	Orange	1.5ml	Conical	Screw Cap Tubes and Caps
SCT-150-Y	Yellow	1.5ml	Conical	Screw Cap Tubes and Caps
SCT-150-G	Green	1.5ml	Conical	Screw Cap Tubes and Caps
SCT-150-B	Blue	1.5ml	Conical	Screw Cap Tubes and Caps
SCT-150-V	Violet	1.5ml	Conical	Screw Cap Tubes and Caps
SCT-150-BR	Brown	1.5ml	Conical	Screw Cap Tubes and Caps

Packaging Description: 500 tubes/pack, 8 packs/case; †50/bag, 10 bags/pack, 8 packs/case

Maximum G-force: 20,000 RCF

Screw Cap Tubes

With Caps

1.5ml, self-standing



1.5ml, self-standing

Axygen Cat No	Colour	Volume	Style	Tube Type
SCT-150-SS-C	Clear	1.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-150-SS-A	Assorted†	1.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-150-SS-GR	Grey	1.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-150-SS-W	White	1.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-150-SS-P	Pink	1.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-150-SS-R	Red	1.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-150-SS-O	Orange	1.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-150-SS-Y	Yellow	1.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-150-SS-G	Green	1.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-150-SS-B	Blue	1.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-150-SS-V	Violet	1.5ml	Self Standing	Screw Cap Tubes and Caps
SCT-150-SS-BR	Brown	1.5ml	Self Standing	Screw Cap Tubes and Caps

Packaging Description: 500 tubes/pack, 8 packs/case; †50/bag, 10 bags/pack, 8 packs/case

Maximum G-force: 20,000 RCF

2.0ml, conical



2.0ml, conical

Axygen Cat No	Colour	Volume	Style	Tube Type
SCT-200-C	Clear	2.0ml	Conical	Screw Cap Tubes and Caps
SCT-200-A	Assorted†	2.0ml	Conical	Screw Cap Tubes and Caps
SCT-200-GR	Grey	2.0ml	Conical	Screw Cap Tubes and Caps
SCT-200-W	White	2.0ml	Conical	Screw Cap Tubes and Caps
SCT-200-P	Pink	2.0ml	Conical	Screw Cap Tubes and Caps
SCT-200-R	Red	2.0ml	Conical	Screw Cap Tubes and Caps
SCT-200-O	Orange	2.0ml	Conical	Screw Cap Tubes and Caps
SCT-200-Y	Yellow	2.0ml	Conical	Screw Cap Tubes and Caps
SCT-200-G	Green	2.0ml	Conical	Screw Cap Tubes and Caps
SCT-200-B	Blue	2.0ml	Conical	Screw Cap Tubes and Caps
SCT-200-V	Violet	2.0ml	Conical	Screw Cap Tubes and Caps
SCT-200-BR	Brown	2.0ml	Conical	Screw Cap Tubes and Caps

Packaging Description: 500 tubes/pack, 8 packs/case; †50/bag, 10 bags/pack, 8 packs/case

Maximum G-force: 20,000 RCF

2.0ml, self-standing



2.0ml, self-standing

Axygen Cat No	Colour	Volume	Style	Tube Type
SCT-200-SS-C	Clear	2.0ml	Self Standing	Screw Cap Tubes and Caps
SCT-200-SS-A	Assorted†	2.0ml	Self Standing	Screw Cap Tubes and Caps
SCT-200-SS-GR	Grey	2.0ml	Self Standing	Screw Cap Tubes and Caps
SCT-200-SS-W	White	2.0ml	Self Standing	Screw Cap Tubes and Caps
SCT-200-SS-P	Pink	2.0ml	Self Standing	Screw Cap Tubes and Caps
SCT-200-SS-R	Red	2.0ml	Self Standing	Screw Cap Tubes and Caps
SCT-200-SS-O	Orange	2.0ml	Self Standing	Screw Cap Tubes and Caps
SCT-200-SS-Y	Yellow	2.0ml	Self Standing	Screw Cap Tubes and Caps
SCT-200-SS-G	Green	2.0ml	Self Standing	Screw Cap Tubes and Caps
SCT-200-SS-B	Blue	2.0ml	Self Standing	Screw Cap Tubes and Caps
SCT-200-SS-V	Violet	2.0ml	Self Standing	Screw Cap Tubes and Caps
SCT-200-SS-BR	Brown	2.0ml	Self Standing	Screw Cap Tubes and Caps

Packaging Description: 500 tubes/pack, 8 packs/case; †50/bag, 10 bags/pack, 8 packs/case

Maximum G-force: 20,000 RCF

Screw Cap Tubes



With Caps

Pre-Sterilized



Pre-Sterilized

Axygen Cat No	Colour	Volume	Style	Tube Type
SCT-45-C-S	Clear	0.5ml	Conical	Pre-Sterilized‡
SCT-050-C-S	Clear	0.5ml	Conical	Pre-Sterilized‡
SCT-050-A-S	Assorted†	0.5ml	Conical	Pre-Sterilized‡
SCT-050-SS-C-S	Clear	0.5ml	Self Standing	Pre-Sterilized‡
SCT-050-SS-A-S	Assorted†	0.5ml	Self Standing	Pre-Sterilized‡
SCT-150-C-S	Clear	1.5ml	Conical	Pre-Sterilized‡
SCT-150-A-S	Assorted†	1.5ml	Conical	Pre-Sterilized‡
SCT-150-SS-C-S	Clear	1.5ml	Self Standing	Pre-Sterilized‡
SCT-150-SS-A-S	Assorted†	1.5ml	Self Standing	Pre-Sterilized‡
SCT-200-C-S	Clear	2.0ml	Conical	Pre-Sterilized‡
SCT-200-A-S	Assorted†	2.0ml	Conical	Pre-Sterilized‡
SCT-200-SS-C-S	Clear	2.0ml	Self Standing	Pre-Sterilized‡
SCT-200-SS-A-S	Assorted†	2.0ml	Self Standing	Pre-Sterilized‡

Packaging Description: 500 tubes/pack, 8 packs/case; 150/bag, 10 bags/pack, 8 packs/case

Maximum G-force: 20,000 RCF

Tubes Only



Screw Cap Tubes (Tubes Only)

Amber Screw Cap Tubes (Tubes Only)

Axygen Cat No	Colour	Volume	Style	Tube Type
ST-45	Clear	0.5ml	Conical	Screw Cap Tubes
ST-050	Clear	0.5ml	Conical	Screw Cap Tubes
ST-050-SS	Clear	0.5ml	Self Standing	Screw Cap Tubes
ST-150	Clear	1.5ml	Conical	Screw Cap Tubes
ST-150-SS	Clear	1.5ml	Self Standing	Screw Cap Tubes
ST-200	Clear	2.0ml	Conical	Screw Cap Tubes
ST-200-SS	Clear	2.0ml	Self Standing	Screw Cap Tubes
ST-050-X	Amber	0.5ml	Conical	Screw Cap Tubes
ST-050-SS-X	Amber	0.5ml	Self Standing	Screw Cap Tubes
ST-150-X	Amber	1.5ml	Conical	Screw Cap Tubes
ST-150-SS-X	Amber	1.5ml	Self Standing	Screw Cap Tubes
ST-200-X	Amber	2.0ml	Conical	Screw Cap Tubes
ST-200-SS-X	Amber	2.0ml	Self Standing	Screw Cap Tubes

Packaging Description: 500 tubes/pack, 8 packs/case;

Maximum G-force: 20,000 RCF

‡ Individual Colors Available as Special Order Items.

Caps

Regular and Looped

Caps without 'O' rings



Caps without 'O' rings

Axygen Cat No	Colour	Description
SC-C	Clear	Non-Looped Screw Caps
SC-A	Assorted†	Non-Looped Screw Caps
SC-GR	Grey	Non-Looped Screw Caps
SC-W	White	Non-Looped Screw Caps
SC-P	Pink	Non-Looped Screw Caps
SC-R	Red	Non-Looped Screw Caps
SC-O	Orange	Non-Looped Screw Caps
SC-Y	Yellow	Non-Looped Screw Caps
SC-G	Green	Non-Looped Screw Caps
SC-B	Blue	Non-Looped Screw Caps
SC-V	Violet	Non-Looped Screw Caps
SC-BR	Brown	Non-Looped Screw Caps

Packaging Description: 500 tubes/pack, 8 packs/case; †50/bag, 10 bags/pack, 8 packs/case

Looped Caps without 'O' rings



Looped Caps without 'O' rings

Axygen Cat No	Colour	Description
SC-LP-C	Clear	Looped Screw Caps
SC-LP-A	Assorted†	Looped Screw Caps
SC-LP-GR	Grey	Looped Screw Caps
SC-LP-W	White	Looped Screw Caps
SC-LP-P	Pink	Looped Screw Caps
SC-LP-R	Red	Looped Screw Caps
SC-LP-O	Orange	Looped Screw Caps
SC-LP-Y	Yellow	Looped Screw Caps
SC-LP-G	Green	Looped Screw Caps
SC-LP-B	Blue	Looped Screw Caps
SC-LP-V	Violet	Looped Screw Caps
SC-LP-BR	Brown	Looped Screw Caps

Packaging Description: 500 tubes/pack, 8 packs/case; †50/bag, 10 bags/pack, 8 packs/case

Caps

Regular and Looped



Caps with 'O' rings

Caps with 'O' rings

Axygen Cat No	Colour	Description
SCO-C	Clear	Non-Looped Screw Caps with 'O' rings
SCO-A	Assorted†	Non-Looped Screw Caps with 'O' rings
SCO-GR	Grey	Non-Looped Screw Caps with 'O' rings
SCO-W	White	Non-Looped Screw Caps with 'O' rings
SCO-P	Pink	Non-Looped Screw Caps with 'O' rings
SCO-R	Red	Non-Looped Screw Caps with 'O' rings
SCO-O	Orange	Non-Looped Screw Caps with 'O' rings
SCO-Y	Yellow	Non-Looped Screw Caps with 'O' rings
SCO-G	Green	Non-Looped Screw Caps with 'O' rings
SCO-B	Blue	Non-Looped Screw Caps with 'O' rings
SCO-V	Violet	Non-Looped Screw Caps with 'O' rings
SCO-BR	Brown	Non-Looped Screw Caps with 'O' rings

Packaging Description: 500 tubes/pack, 8 packs/case; †50/bag, 10 bags/pack, 8 packs/case



Looped Caps with 'O' rings

Looped Caps with 'O' rings

Axygen Cat No	Colour	Description
SCO-LP-C	Clear	Looped Screw Caps with 'O' rings
SCO-LP-A	Assorted†	Looped Screw Caps with 'O' rings
SCO-LP-GR	Grey	Looped Screw Caps with 'O' rings
SCO-LP-W	White	Looped Screw Caps with 'O' rings
SCO-LP-P	Pink	Looped Screw Caps with 'O' rings
SCO-LP-R	Red	Looped Screw Caps with 'O' rings
SCO-LP-O	Orange	Looped Screw Caps with 'O' rings
SCO-LP-Y	Yellow	Looped Screw Caps with 'O' rings
SCO-LP-G	Green	Looped Screw Caps with 'O' rings
SCO-LP-B	Blue	Looped Screw Caps with 'O' rings
SCO-LP-V	Violet	Looped Screw Caps with 'O' rings
SCO-LP-BR	Brown	Looped Screw Caps with 'O' rings

Packaging Description: 500 tubes/pack, 8 packs/case; †50/bag, 10 bags/pack, 8 packs/case

Axy Racks

1.5ml and 2.0ml Microtube/Screw-cap tube Racks

80-well Axyracks



80-well Axyracks

Axygen Cat No	Colour	Product
R-80-AF	Assorted Fluorescent	80-well Rack
R-80-BF	Fluorescent Blue	80-well Rack
R-80-GF	Fluorescent Green	80-well Rack
R-80-OF	Fluorescent Orange	80-well Rack
R-80-RF	Fluorescent Red	80-well Rack
R-80-PF	Fluorescent Pink	80-well Rack
R-80-YF	Fluorescent Yellow	80-well Rack

Packaging Description: 25 racks/case

- Holds eighty 1.5/2.0ml micro and screw cap tubes
- Polypropylene; resistant to most lab chemicals and solvents
- Perfect for cryogenic storage of tubes
- Conical bottom wells allow superior stability of conical tubes
- Each well numbered for ease of sample identification
- Frosted side writing panel
- Available in a variety of fluorescent and non-fluorescent colours

50-well Axyracks



50-well Axyracks

Axygen Cat No	Colour	Description
R-50-BK	Black	50-well Rack
R-50-B	Blue	50-well Rack
R-50-G	Green	50-well Rack
R-50-R	Red	50-well Rack
R-50-Y	Yellow	50-well Rack
R-50-A	Assorted	50-well Rack

Packaging Description: 10 racks/pack; 10 packs/case

- Holds fifty 2.0/1.5ml micro and screw cap tubes
- polycarbonate; resistant to most lab chemicals and solvents
- Perfect for cryogenic storage to -80°C and below
- Alpha-numeric grid for easy sample identification

81-well Axyracks



81-well Axyracks

Axygen Cat No	Colour	Description
R-81-G-PC	Green	81-well Rack
R-81-R-PC	Red	81-well Rack
R-81-Y-PC	Yellow	81-well Rack

Packaging Description: 10 racks/pack; 10 packs/case

- Holds eighty-one 2.0/1.5ml micro and screw cap tubes
- Polycarbonate; resistant to most chemical and organic solvents
- Perfect for cryogenic storage to -80°C and below

48-place aluminium Axyracks



48-place aluminium Axyracks

Axygen Cat No	Colour	Description
RA-48	Metallic	Anodized Aluminum Rack

Packaging Description: 4 racks/pack; 4 packs/case

- Holds 48 screw cap tubes of all sizes
- Long lasting aluminum construction
- Unique ribbed-port design allows one-hand operation
- Non-skid benchtop pads for a firm platform
- Center support for added strength and stability

Axyracks, caps and closures

4-sided Tube Rack



4-sided Tube Rack

Axygen Cat No	Colour	Product
R-480-A	Assorted	80 Well 4 Sided Tube Rack

Packaging Description: 5 racks/pack; 4 packs/case

- Holds up to 4x 50ml, 16x 15ml, 13x100 or 12x75, 32x 2.0ml or 1.5ml, and 32x 0.5ml Tubes.
- Assorted pack of Pink, Orange, Yellow, Blue, and Green
- Racks that can be positioned on 4-different sides and interlocked to help manage tubes in your lab.

AxyCap



AxyCap

Axygen Cat No	Colour	Description	Packaging
AC-PE-C	Clear	AxyCap 10-16mm	1000/pack, 10 packs/case
AC-PE-BK	Black	AxyCap 10-16mm	1000/pack, 10 packs/case
AC-PE-B	Blue	AxyCap 10-16mm	1000/pack, 10 packs/case
AC-PE-GR	Grey	AxyCap 10-16mm	1000/pack, 10 packs/case
AC-PE-G	Green	AxyCap 10-16mm	1000/pack, 10 packs/case
AC-PE-L	Lavender	AxyCap 10-16mm	1000/pack, 10 packs/case
AC-PE-R	Red	AxyCap 10-16mm	1000/pack, 10 packs/case
AC-PE-Y	Yellow	AxyCap 10-16mm	1000/pack, 10 packs/case

Uniquely molded, pliable cap designed to fit standard 10mm, 12mm, 13mm and 16mm glass and plastic test tubes. The AxyCap will seal either over the rim on smaller tubes or into the tube on 16mm tubes.



AxyCap

AxySaver

Axygen Cat No	Colour	Description	Packaging
AS-13MM-R	Red	AxySaver Closure 12/13mm	1000/pack, 10 packs/case
AS-13MM-G	Green	AxySaver Closure 12/13mm	1000/pack, 10 packs/case
AS-13MM-L	Lavender	AxySaver Closure 12/13mm	1000/pack, 10 packs/case
AS-13MM-BK	Black	AxySaver Closure 12/13mm	1000/pack, 10 packs/case
AS-13MM-B	Blue	AxySaver Closure 12/13mm	1000/pack, 10 packs/case
AS-13MM-GR	Grey	AxySaver Closure 12/13mm	1000/pack, 10 packs/case
AS-13MM-Y	Yellow	AxySaver Closure 12/13mm	1000/pack, 10 packs/case
AS-13MM-W	White	AxySaver Closure 12/13mm	1000/pack, 10 packs/case
AS-16MM-R	Red	AxySaver Closure 16mm	1000/pack, 10 packs/case
AS-16MM-G	Green	AxySaver Closure 16mm	1000/pack, 10 packs/case
AS-16MM-L	Lavender	AxySaver Closure 16mm	1000/pack, 10 packs/case
AS-16MM-BK	Black	AxySaver Closure 16mm	1000/pack, 10 packs/case
AS-16MM-B	Blue	AxySaver Closure 16mm	1000/pack, 10 packs/case
AS-16MM-GR	Grey	AxySaver Closure 16mm	1000/pack, 10 packs/case
AS-16MM-Y	Yellow	AxySaver Closure 16mm	1000/pack, 10 packs/case
AS-16MM-W	White	AxySaver Closure 16mm	1000/pack, 10 packs/case

The Axygen AxySaver Closure is a soft, pliable secondary closure for use with most 12/13mm and 16mm glass and plastic test tubes. The unique blend of plastic used in these caps is piercable and allows for direct tube sampling.

Since our inception in 1993, Axygen Scientific has grown and developed into a worldwide leader in the development and manufacturing of quality products for the research community.

We continue to set ourselves apart from the rest of the industry by our commitment to doing things the right way, with the right people, the right materials, on-time, every time.

Using only the finest machine tools and molds, coupled with the most skillful toolmakers around, we produce the highest quality precision injection molded plastics available today.

Every year we release an average of 10 to 20 new products – each purpose built and forward-thinking. Through new product innovations we bring new standards to sample handling, delivery, and storage; improving the way research is done. Some examples of this year's innovations are pictured below and throughout this catalog.

Axygen is committed to the complete satisfaction of each and every customer. Whether you are meeting us for the first time, or making a return visit, we welcome the opportunity to serve you.




*Introducing an
expanded selection of
disposable tips for
automation with
Tecan Robotic Systems*



Tecan Robotic Tips
Liquid Level Sensing



Velocity 11
Unique ultra-low volume
5µL tip for optimal
precision



FX-1536
Critical dimensions for
critical applications



Tecan EVO
Tips for the Evolution
platforms



RoboRACK
for PerkinElmer Janus
robotic platforms

Ultra Smooth Surfaces – Maxymum Recovery®

Robotic Tips

With unsurpassed consistency and performance to fit most liquid handling systems.

Utilising a unique manufacturing process, Axygen Scientific has developed an innovative series of pipette tips, filter tips, PCR products and microcentrifuge tubes that feature ultra smooth surfaces.

- ▶ Exclusive molding technology
- ▶ Reduce sample loss
- ▶ Save costly reagents
- ▶ Maximize accuracy and precision

Surface comparison of polypropylene materials

These images show a visual comparison of the Axygen Maxymum Recovery® pipette tip internal surface compared to the surface of both standard polypropylene pipette tips and siliconized pipette tips. The photographs below were taken of the internal surface of sections cut from three styles of pipette tips, via SEM/EDS. Magnification levels ranged from 50x to 5,000x.



Axygen MAXYUM Recovery® Pipette Tips



Figures 1a (50x), 1b (500x) and 1c (5000x) are images of the Axygen Maxymum Recovery® surface. Even at the highest magnification level, the ultra-smooth surface is visibly free of occlusions and cavities which can cause sample retention and sample denaturation in standard polypropylene.

Conventional Pipette Tips




Figure 2a (50x), 2b (500x) and 2c (5000x) are images of the internal surface of a standard polypropylene pipette tip. Occlusions and cavities can be seen on the wall surface. At highest magnification, surface strands which cause samples to 'stick', are clearly visible.

Siliconized Pipette Tips




Figure 3a (50x), 3b (500x) and 3c (2000x) are images of a siliconized pipette tip. Here again, notice the lack of smoothness of the walls created by an inconsistent and uneven flow of silicone upon the surface. Sample retention occurs even with siliconized pipette tips.



Beckman Coulter – Compatible Tips

Tips Compatible with BECKMAN COULTER® BIOMEK® FX, BIOMEK® NX & MULTIMEK™



Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
FX-1536-30FP-R	Non-Filtered	27µl	✓	AP-384	Non-Sterile
FX-1536-30FP-R-S	Non-Filtered	27µl	✓	AP-384	Sterile
FX-384-XL-R	Non-Filtered	50µl	✓	AP-384	Non-Sterile
FX-384-XL-R-S	Non-Filtered	50µl	✓	AP-384	Sterile
FXF-384-XL-R-S	Filtered	30µl	✓	AP-384	Sterile
FX-384-R	Non-Filtered	30µl	✓	AP-384	Non-Sterile
FX-384-R-S	Non-Filtered	30µl	✓	AP-384	Sterile
FXF-384-R-S	Filtered	25µl	✓	AP-384	Sterile

Packaging Description: Quantity = 384 tips/rack, 10 racks/pack, 5 packs/case

Maxym Recovery®

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
FX-384-XL-L-R	Non-Filtered	50µl	✓	AP-384	Non-Sterile
FX-384-XL-L-R-S	Non-Filtered	50µl	✓	AP-384	Sterile
FXF-384-XL-L-R-S	Filtered	30µl	✓	AP-384	Sterile
FX-384-L-R	Non-Filtered	30µl	✓	AP-384	Non-Sterile
FX-384-L-R-S	Non-Filtered	30µl	✓	AP-384	Sterile
FXF-384-L-R-S	Filtered	25µl	✓	AP-384	Sterile

Packaging Description: Quantity = 384 tips/rack, 10 racks/pack, 5 packs/case

FX-1536-30FP-R & FX-1536-30FP-R-S

FX-384-XL-R, FX-384-XL-R-S & FXF-384-XL-R-S

FX-384-R, FX-384-R-S & FXF-384-R-S

FX-384-XL-L-R, FX-384-XL-L-R-S & FXF-384-XL-L-R-S

FX-384-L-R, FX-384-L-R-S & FXF-384-L-R-S

Format:

384-Tip Format

TIP Volume Range

Selection:

25µl - 50µl

Material:


Clear Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile
- Standard or Maxym Recovery®


Certified:

DNase-Free, RNAse-Free, Pyrogen-Safe



Tip Box Format: SBS

Material: Number 5 Polypropylene





FX-10-R & FX-10-R-S



FXF-10-R-S



FX-20-R & FX-20-R-S



FXF-20-R-S



FX-50-R & FX-50-R-S



FXF-50-R-S



FX-250-R & FX-250-R-S



FXF-180-R-S



FX-255-WB-R & FX-255-WB-R-S



FXF-165-WB-R-S

Beckman Coulter – Compatible Tips

Tips Compatible with BECKMAN COULTER® BIOMEK® FX, BIOMEK® NX, BIOMEK® 3000 & MULTIMEK™

Oxygen Cat No.	Type	Max Volume		Compatible Head	Packaging
FX-10-R	Non-Filtered	20µl	✓	AP-96, SPAN-8, MP20	Non-Sterile
FX-10-R-S	Non-Filtered	20µl	✓	AP-96, SPAN-8, MP20	Sterile
FXF-10-R-S	Filtered	5µl	✓	AP-96, SPAN-8, MP20	Sterile
FX-20-R	Non-Filtered	100µl	✓	AP-96, SPAN-8, MP20	Non-Sterile
FX-20-R-S	Non-Filtered	100µl	✓	AP-96, SPAN-8, MP20	Sterile
FXF-20-R-S	Filtered	20µl	✓	AP-96, SPAN-8, MP20	Sterile
FX-50-R	Non-Filtered	50µl	✓	AP-96, SPAN-8, MP20, MP200	Non-Sterile
FX-50-R-S	Non-Filtered	50µl	✓	AP-96, SPAN-8, MP20, MP200	Sterile
FXF-50-R-S	Filtered	30µl	✓	AP-96, SPAN-8, MP20, MP200	Sterile
FX-250-R	Non-Filtered	250µl	✓	AP-96, SPAN-8, MP200	Non-Sterile
FX-250-R-S	Non-Filtered	250µl	✓	AP-96, SPAN-8, MP200	Sterile
FXF-180-R-S	Filtered	165µl	✓	AP-96, SPAN-8, MP200	Sterile
FX-255-WB-R	Wide Bore, Non-Filtered	250µl	✓	AP-96, SPAN-8, MP200	Non-Sterile
FX-255-WB-R-S	Wide Bore, Non-Filtered	250µl	✓	AP-96, SPAN-8, MP200	Sterile
FXF-165-WB-R-S	Wide Bore, Filtered	165µl	✓	AP-96, SPAN-8, MP200	Sterile
FXF-200-R-S	Filtered	200µl	✓	AP-96, SPAN-8, MP200	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case

Maxym Recovery®

Oxygen Cat No.	Type	Max Volume		Compatible Head	Packaging
FX-20-L-R	Non-Filtered	100µl	✓	AP-96, SPAN-8, MP20	Non-Sterile
FX-20-L-R-S	Non-Filtered	100µl	✓	AP-96, SPAN-8, MP20	Sterile
FXF-20-L-R-S	Filtered	20µl	✓	AP-96, SPAN-8, MP20	Sterile
FX-50-L-R	Non-Filtered	50µl	✓	AP-96, SPAN-8, MP20, MP200	Non-Sterile
FX-50-L-R-S	Non-Filtered	50µl	✓	AP-96, SPAN-8, MP20, MP200	Sterile
FXF-50-L-R-S	Filtered	30µl	✓	AP-96, SPAN-8, MP20, MP200	Sterile
FX-250-L-R	Non-Filtered	250µl	✓	AP-96, SPAN-8, MP200	Non-Sterile
FX-250-L-R-S	Non-Filtered	250µl	✓	AP-96, SPAN-8, MP200	Sterile
FXF-180-L-R-S	Filtered	165µl	✓	AP-96, SPAN-8, MP200	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case

Also compatible with Span 8 head when the liquid level sensory function is turned off

Format:
96-Tip Format



TIP Volume Range Selection:
5µl - 250µl

Material:
Clear Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile
- Standard or Maxym Recovery®

Certified:
DNAse-Free, RNAse-Free, Pyrogen-Safe





Beckman Coulter – Compatible Tips

Tips Compatible with BECKMAN COULTER® BIOMEK® FX & BIOMEK® NX with SPAN-8 liquid level sensing head



SPN-20-CBK-R & SPN-20-CBK-R-S



SPNF-20-CBK-R-S



SPN-50-CBK-R & SPN-50-CBK-R-S



SPNF-30-CBK-R-S



SPN-250-CBK-R & SPN-250-CBK-R-S



SPNF-180-CBK-R-S

Format:

96-Tip Format

TIP Volume Range Selection:

20µl - 250µl

Material:

Conductive LLS Black Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile



Certified:

DNase-Free, RNase-Free, Pyrogen-Safe

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
SPN-20-CBK-R	Conductive, Non-Filtered	100µl	✓	SPAN-8	Non-Sterile
SPN-20-CBK-R-S	Conductive, Non-Filtered	100µl	✓	SPAN-8	Sterile
SPNF-20-CBK-R-S	Conductive, Filtered	20µl	✓	SPAN-8	Sterile
SPN-50-CBK-R	Conductive, Non-Filtered	50µl	✓	SPAN-8	Non-Sterile
SPN-50-CBK-R-S	Conductive, Non-Filtered	50µl	✓	SPAN-8	Sterile
SPNF-30-CBK-R-S	Conductive, Filtered	30µl	✓	SPAN-8	Sterile
SPN-250-CBK-R	Conductive, Non-Filtered	250µl	✓	SPAN-8	Non-Sterile
SPN-250-CBK-R-S	Conductive, Non-Filtered	250µl	✓	SPAN-8	Sterile
SPNF-180-CBK-R-S	Conductive, Filtered	165µl	✓	SPAN-8	Sterile

Packaging Description:

Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case






BT-20-R-S



BT-50-R & BT-50-R-S



BT-50-R-S



BT-250-R & BT-250-R-S



BT-180-R-S



BT-255-WB-R & BT-255-WB-R-S



BT-165-WB-R-S



BT-1000-R



BT-1000-R-S

Format:

96-Tip Format
(1ml size are 72 tips/rack)

TIP Volume Range**Selection:**

20µl - 1000µl

Material:

Clear Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile
- Standard or Maxym Recovery®

Certified:

DNase-Free, RNase-Free,
Pyrogen-Safe

Beckman Coulter – Compatible Tips

Tips Compatible with BECKMAN COULTER® BIOMEK® 1000 & BIOMEK® 2000

Axygen Cat No.	Type	Max Volume	Compatible Head	Packaging
BT-20-R	Non-Filtered	100µl	P20, MP20, P200, MP200	Non-Sterile
BT-20-R-S	Non-Filtered	100µl	P20, MP20, P200, MP200	Sterile
BTF-20-R-S	Filtered	20µl	P20, MP20, P200, MP200	Sterile
BT-50-R	Non-Filtered	50µl	P20, MP20, P200, MP200	Non-Sterile
BT-50-R-S	Non-Filtered	50µl	P20, MP20, P200, MP200	Sterile
BTF-50-R-S	Filtered	30µl	P20, MP20, P200, MP200	Sterile
BT-250-R	Non-Filtered	250µl	P200, MP200	Non-Sterile
BT-250-R-S	Non-Filtered	250µl	P200, MP200	Sterile
BTF-180-R-S	Filtered	165µl	P200, MP200	Sterile
BT-255-WB-R	Wide-Bore, Non-Filtered	250µl	P200, MP200	Non-Sterile
BT-255-WB-R-S	Wide-Bore, Non-Filtered	250µl	P200, MP200	Sterile
BTF-165-WB-R-S	Wide-Bore, Filtered	165µl	P200, MP200	Sterile
BT-1000-R*	Non-Filtered	1000µl	P1000	Non-Sterile
BTF-1000-R-S*	Filtered	1000µl	P1000	Sterile

Packaging Description:

Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case



* Quantity = 72 tips/pack, 5 racks/case

Maxym Recovery®

Axygen Cat No.	Type	Max Volume	Compatible Head	Packaging
BT-20-L-R	Non-Filtered	100µl	P20, MP20, P200, MP200	Non-Sterile
BT-20-L-R-S	Non-Filtered	100µl	P20, MP20, P200, MP200	Sterile
BTF-20-L-R-S	Filtered	20µl	P20, MP20, P200, MP200	Sterile
BT-50-L-R	Non-Filtered	50µl	P20, MP20, P200, MP200	Non-Sterile
BT-50-L-R-S	Non-Filtered	50µl	P20, MP20, P200, MP200	Sterile
BTF-50-L-R-S	Filtered	30µl	P20, MP20, P200, MP200	Sterile
BT-250-L-R	Non-Filtered	250µl	P200, MP200	Non-Sterile
BT-250-L-R-S	Non-Filtered	250µl	P200, MP200	Sterile
BTF-180-L-R-S	Filtered	165µl	P200, MP200	Sterile

Packaging Description:


Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case



Tip Box Format: Non-SBS

Material: Number 5 Polypropylene





Beckman Coulter – Compatible Tips



Tips Compatible with BECKMAN COULTER® MULTIMEK™ & SAGIAN MULTIPETTE

Axygen Cat No.	Type	Max Volume	Compatible Head	Packaging
MT-200-R	Non-Filtered	200µl	CCS P50	Non-Sterile
MT-200-R-S	Non-Filtered	200µl	CCS P50	Sterile
MTF-200-R-S	Filtered	180µl	CCS P200	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case



MT-200-R & MT-200-R-S



MTF-200-R-S

Format:

96-Tip Format

TIP Volume Range

Selection:

180µl - 200µl

Material:


Clear Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile
- Standard or Maxymum Recovery®

Certified:

DNase-Free, RNase-Free, Pyrogen-Safe



Tip Box Format: Non-SBS

Material: Number 5 Polypropylene






VT-20-R, VT-20-R-S, VT-20-R-LAB &
VT-20-R-LAB-S



VT-20-R-S



VT-50-R-LAB & VT-50-R-LAB-S



VTF-30-R-LAB-S



VT-250-R, VT-250-R-S, VT-250-R-LAB &
VT-250-R-LAB-S



VTF-165-R-S & VTF-165-R-LAB-S



VT-255-WB-R-S



VTF-165-WB-R-S

Format:

96-Tip Format

TIP Volume Range

Selection:

20µl - 250µl

Material:

Clear Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile

Certified:

DNase-Free, RNase-Free,
Pyrogen-Safe

Velocity11 – Compatible Tips

Tips Compatible with AGILENT/VELOCITY11® VPREP® and BRAVO

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
VT-20-R	Non-Filtered	60µl	✓	96LT & 8LT	Non-Sterile
VT-20-R-S	Non-Filtered	60µl	✓	96LT & 8LT	Sterile
VT-20-R-LAB*	Non-Filtered	60µl	✓	96LT & 8LT	Non-Sterile
VTF-20-R-S	Filtered	20µl	✓	96LT & 8LT	Sterile
VT-20-R-LAB-S*	Non-Filtered	20µl	✓	96LT & 8LT	Sterile
VT-50-R-LAB*	Non-Filtered	50µl	✓	96LT & 8LT	Non-Sterile
VT-50-R-LAB-S*	Non-Filtered	50µl	✓	96LT & 8LT	Sterile
VTF-30-R-LAB-S*	Filtered	30µl	✓	96LT & 8LT	Sterile
VT-250-R	Non-Filtered	250µl	✓	96LT & 8LT	Non-Sterile
VT-250-R-S	Non-Filtered	250µl	✓	96LT & 8LT	Sterile
VT-250-R-LAB*	Non-Filtered	250µl	✓	96LT & 8LT	Non-Sterile
VT-250-R-LAB-S*	Non-Filtered	250µl	✓	96LT & 8LT	Sterile
VTF-165-R-S	Filtered	165µl	✓	96LT & 8LT	Sterile
VTF-165-R-LAB-S*	Filtered	165µl	✓	96LT & 8LT	Sterile
VT-255-WB-R-S	Wide-Bore, Non-Filtered	250µl	✓	96LT & 8LT	Sterile
VTF-165-WB-R-S	Wide-Bore, Filtered	165µl	✓	96LT & 8LT	Sterile



Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case

**Tip box base sealed for best performance in automated up-and-down stacking.*

Maxym Recovery®

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
VT-250-L-R	Non-Filtered	250µl	✓	96LT & 8LT	Non-Sterile
VT-250-L-R-LAB*	Non-Filtered	250µl	✓	96LT & 8LT	Non-Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case





Velocity11 – Compatible Tips



Tips Compatible with AGILENT/VELOCITY11® VPREP® and BRAVO

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
VT-384-5UL-R	Non-Filtered	5µl	✓	384ST, 96ST & 16ST	Non-Sterile
VT-384-5UL-R-S	Non-Filtered	5µl	✓	384ST, 96ST & 16ST	Sterile
VT-384-10UL-R	Non-Filtered	10µl	✓	384ST, 96ST & 16ST	Non-Sterile
VT-384-10UL-R-S	Non-Filtered	10µl	✓	384ST, 96ST & 16ST	Sterile
VT-384-31UL-R	Non-Filtered	30µl	✓	384ST, 96ST & 16ST	Non-Sterile
VT-384-31UL-R-S	Non-Filtered	30µl	✓	384ST, 96ST & 16ST	Sterile
VTF-384-15UL-R-S	Filtered	15µl	✓	384ST, 96ST & 16ST	Sterile
VTF-384-70UL-R	Non-Filtered	70µl	✓	384ST, 96ST & 16ST	Non-Sterile
VTF-384-70UL-R-S	Non-Filtered	70µl	✓	384ST, 96ST & 16ST	Sterile
VTF-384-50UL-R-S	Filtered	50µl	✓	384ST, 96ST & 16ST	Sterile

Packaging Description: Quantity = 384 tips/rack, 10 racks/pack, 5 packs/case



VT-384-5UL-R & VT-384-5UL-R-S



VT-384-10UL-R & VT-384-10UL-R-S



VT-384-31UL-R & VT-384-31UL-R-S



VTF-384-15UL-R-S



VTF-384-70UL-R & VTF-384-70UL-R-S



VTF-384-50UL-R-S

Format:

384-Tip Format

TIP Volume Range

Selection:

5µl - 70µl

Material:

Clear Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile


Certified:

DNase-Free, RNase-Free, Pyrogen-Safe



Tip Box Format: SBS

Material: Number 5 Polypropylene



Tip Box Material:

Conductive polypropylene for static dissipation



TT-20-C-HTR & TT-20-C-HTR-S



TTF-20-C-HTR-S



TT-50-C-HTR & TT-50-C-HTR-S



TTF-50-C-HTR-S



TT-200-C-HTR & TT-200-C-HTR-S



TTF-200-C-HTR-S



TT-1000-C-HTR & TT-1000-C-HTR-S



TTF-1000-C-HTR-S

Format:

96-Tip Format

TIP Volume Range**Selection:**

10µl - 1000µl

Material:

Clear Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile

Certified:


DNAse-Free, RNAse-Free, Pyrogen-Safe

TECAN – Compatible Tips*Tips Compatible with TECAN® GENESIS FREEDOM®, FREEDOM Evo® & MINIPREP with LiHa*

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
TT-20-C-HTR	Non-Filtered	20µl	✓	LiHa-1, -4 & -8	Non-Sterile
TT-20-C-HTR-S	Non-Filtered	20µl	✓	LiHa-1, -4 & -8	Sterile
TTF-20-C-HTR-S	Filtered	10µl	✓	LiHa-1, -4 & -8	Sterile
TT-50-C-HTR	Non-Filtered	50µl	✓	LiHa-1, -4 & -8	Non-Sterile
TT-50-C-HTR-S	Non-Filtered	50µl	✓	LiHa-1, -4 & -8	Sterile
TTF-50-C-HTR-S	Filtered	25µl	✓	LiHa-1, -4 & -8	Sterile
TT-200-C-HTR	Non-Filtered	200µl	✓	LiHa-1, -4 & -8	Non-Sterile
TT-200-C-HTR-S	Non-Filtered	200µl	✓	LiHa-1, -4 & -8	Sterile
TTF-200-C-HTR-S	Filtered	175µl	✓	LiHa-1, -4 & -8	Sterile

Packaging Description: Quantity = 96 tips/rack, 24 racks/case

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
TT-1000-C-HTR	Non-Filtered	1000µl	✓	LiHa-1, -4 & -8	Non-Sterile
TT-1000-C-HTR-S	Non-Filtered	1000µl	✓	LiHa-1, -4 & -8	Sterile
TTF-1000-C-HTR-S	Filtered	1000µl	✓	LiHa-1, -4 & -8	Sterile

Packaging Description: Quantity = 96 tips/rack, 16 racks/case

Tip Box Format: Non-SBS
Material: Number 5 Polypropylene



Tecan – Compatible Tips

Tips Compatible with **TECAN® GENESIS FREEDOM®, FREEDOM Evo® & MINIPREP with LiHa**



Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
TT-20-CBK-HTR	Conductive, Non-Filtered	20µl	✓	LiHa-1, -4 & -8	Non-Sterile
TT-20-CBK-HTR-36*	Conductive, Non-Filtered	20µl	✓	LiHa-1, -4 & -8	Non-Sterile
TT-20-CBK-HTR-S	Conductive, Non-Filtered	20µl	✓	LiHa-1, -4 & -8	Sterile
TTF-20-CBK-HTR-S	Conductive, Filtered	10µl	✓	LiHa-1, -4 & -8	Sterile
TT-50-CBK-HTR	Conductive, Non-Filtered	50µl	✓	LiHa-1, -4 & -8	Non-Sterile
TT-50-CBK-HTR-36*	Conductive, Non-Filtered	50µl	✓	LiHa-1, -4 & -8	Non-Sterile
TT-50-CBK-HTR-S	Conductive, Non-Filtered	50µl	✓	LiHa-1, -4 & -8	Sterile
TTF-50-CBK-HTR-S	Conductive, Filtered	25µl	✓	LiHa-1, -4 & -8	Sterile
TT-200-CBK-HTR	Conductive, Non-Filtered	200µl	✓	LiHa-1, -4 & -8	Non-Sterile
TT-200-CBK-HTR-36*	Conductive, Non-Filtered	200µl	✓	LiHa-1, -4 & -8	Non-Sterile
TT-200-CBK-HTR-S	Conductive, Non-Filtered	200µl	✓	LiHa-1, -4 & -8	Sterile
TTF-200-CBK-HTR-S	Conductive, Filtered	175µl	✓	LiHa-1, -4 & -8	Sterile

Packaging Description:

Quantity = 96 tips/rack, 24 racks/case

*Quantity = 96 tips/wafer, 72 wafers/case. Denotes economy cardboard wrap

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
TT-1000-CBK-HTR	Conductive, Non-Filtered	1000µl	✓	LiHa-1, -4 & -8	Non-Sterile
TT-1000-CBK-HTR-24**	Conductive, Non-Filtered	1000µl	✓	LiHa-1, -4 & -8	Non-Sterile
TT-1000-CBK-HTR-S	Conductive, Non-Filtered	1000µl	✓	LiHa-1, -4 & -8	Sterile
TTF-1000-CBK-HTR-S	Conductive, Filtered	1000µl	✓	LiHa-1, -4 & -8	Sterile

Packaging Description:

Quantity = 96 tips/rack, 16 racks/case

**Quantity = 96 tips/wafer, 48 wafers/case. Denotes economy cardboard wrap



TT-20-CBK-HTR & TT-20-CBK-HTR-36



TTF-50-CBK-HTR-S



TT-50-CBK-HTR & TT-50-CBK-HTR-S



TTF-50-CBK-HTR-S



TT-200-CBK-HTR & TT-200-CBK-HTR-S



TTF-200-CBK-HTR-S



TT-1000-CBK-HTR



TTF-1000-CBK-HTR-S

Format:

96-Tip Format

TIP Volume Range

Selection:

10µl - 1000µl

Material:


Conductive LLS Black Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile

Certified:

DNase-Free, RNase-Free, Pyrogen-Safe



Tip Box Format: Non-SBS
Material: Number 5 Polypropylene



*convenient blister-pack packaging



TECAN – Compatible Tips

Tips Compatible with TECAN® GENESIS FREEDOM®, FREEDOM Evo® & MINIPREP with LiHa

For use on SBS Plate footprint deck carriers.

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
EV-50-R	Non-Filtered	50µl	✓	MCA96	Non-Sterile
EV-50-R-S	Non-Filtered	50µl	✓	MCA96	Sterile
EVF-50-R-S	Filtered	50µl	✓	MCA96	Sterile
EV-100-R	Non-Filtered	100µl	✓	MCA96	Non-Sterile
EV-100-R-S	Non-Filtered	100µl	✓	MCA96	Sterile
EVF-100-R-S	Filtered	80µl	✓	MCA96	Sterile
EV-200-R	Non-Filtered	200µl	✓	MCA96	Non-Sterile
EV-200-R-S	Non-Filtered	200µl	✓	MCA96	Sterile
EVF-180-R-S	Filtered	180µl	✓	MCA96	Sterile
EV-205-WB-R	Wide-Bore, Non-Filtered	200µl	✓	MCA96	Non-Sterile
EV-205-WB-R-S	Wide-Bore, Non-Filtered	200µl	✓	MCA96	Sterile
EVF-205-WB-R-S	Wide-Bore, Filtered	180µl	✓	MCA96	Sterile

Packaging Description:

Quantity = 96 tips/rack, 10 racks/packs, 5 packs/case



EV-50-R & EV-50-R-S



EVF-50-R-S



EV-100-R & EV-100-R-S



EVF-100-R-S



EV-200-R & EV-200-R-S



EVF-180-R-S



EV-205-WB-R & EV-205-WB-R-S



EVF-205-WB-R-S

Format:

96-Tip Format

TIP Volume Range

Selection:

50µl - 200µl

Material:


Clear Polypropylene

Available Options:


- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile

Certified:

DNase-Free, RNase-Free, Pyrogen-Safe



Tip Box Format: SBS
Material: Number 5 Polypropylene





TECAN – Compatible Tips

Tips Compatible with **TECAN® FREEDOM Evo® TEMo & AQUARIUS**

Axygen Cat No.	Type	Max Volume	Compatible Head	Packaging
ZT-50-R	Non-Filtered	50µl	MCA96, TEM096	Non-Sterile
ZT-50-R-S	Non-Filtered	50µl	MCA96, TEM096	Sterile
ZTF-50-R-S	Filtered	50µl	MCA96, TEM096	Sterile
ZT-100-R	Non-Filtered	100µl	MCA96, TEM096	Non-Sterile
ZT-100-R-S	Non-Filtered	100µl	MCA96, TEM096	Sterile
ZTF-100-R-S	Filtered	80µl	MCA96, TEM096	Sterile
ZT-200-R	Non-Filtered	200µl	MCA96, TEM096	Non-Sterile
ZT-200-R-S	Non-Filtered	200µl	MCA96, TEM096	Sterile
ZTF-200-R-S	Filtered	180µl	MCA96, TEM096	Sterile
ZT-205-WB-R	Wide-Bore, Non-Filtered	200µl	MCA96, TEM096	Non-Sterile
ZT-205-WB-R-S	Wide-Bore, Non-Filtered	200µl	MCA96, TEM096	Sterile
ZTF-205-WB-R-S	Wide-Bore, Filtered	180µl	MCA96, TEM096	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case


Maxymum Recovery®

Axygen Cat. No.	Type	Max Volume	Compatible Head	Packaging
ZT-50-L-R	Non-Filtered	50µl	MCA96, TEM096	Non-Sterile
ZT-50-L-R-S	Non-Filtered	50µl	MCA96, TEM096	Sterile
ZTF-50-L-R-S	Filtered	50µl	MCA96, TEM096	Sterile
ZT-100-L-R	Non-Filtered	100µl	MCA96, TEM096	Non-Sterile
ZT-100-L-R-S	Non-Filtered	100µl	MCA96, TEM096	Sterile
ZTF-100-L-R-S	Filtered	80µl	MCA96, TEM096	Sterile
ZT-200-L-R	Non-Filtered	200µl	MCA96, TEM096	Non-Sterile
ZT-200-L-R-S	Non-Filtered	200µl	MCA96, TEM096	Sterile
ZTF-200-L-R-S	Filtered	180µl	MCA96, TEM096	Sterile
ZT-205-WB-L-R	Wide-Bore, Non-Filtered	200µl	MCA96, TEM096	Non-Sterile
ZT-205-WB-L-R-S	Wide-Bore, Non-Filtered	200µl	MCA96, TEM096	Sterile
ZTF-205-WB-L-R-S	Wide-Bore, Filtered	180µl	MCA96, TEM096	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case



ZT-50-R & ZT-50-R-S



ZTF-50-R-S



ZT-100-R & ZT-100-R-S



ZTF-100-R-S



ZT-200-R & ZT-200-R-S



ZTF-200-R-S



ZT-205-WB-R & ZT-205-WB-R-S



ZTF-205-WB-R-S

Format:

96-Tip Format

TIP Volume Range

Selection:

50µl - 200µl

Material:



Clear Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile

Certified:

DNase-Free, RNase-Free, Pyrogen-Safe





TT-50-C-HTR & TT-50-C-HTR-S



TTF-50-C-HTR-S



TT-200-C-HTR & TT-200-C-HTR-S



TTF-200-C-HTR-S



TT-50-CBK-HTR & TT-50-CBK-HTR-S



TTF-50-CBK-HTR-S



TT-200-CBK-HTR & TT-200-CBK-HTR-S



TTF-200-CBK-HTR-S



CTF-199-R-S

Format:

96-Tip Format

TIP Volume Range**Selection:**

25µl - 200µl

Material:

- Clear Polypropylene
- Conductive LLS Black Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile

Certified:

DNAse-Free, RNAse-Free, Pyrogen-Safe

Corbett – Compatible Tips

Tips Compatible with CORBETT CAS-1200™ with LLT and X-TRACTOR GENE


Tips for CAS systems are compatible with Qiagen® QIAgility™. Tips for X-TRACTOR GENE systems are compatible with Qiagen OnCor.

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
TT-50-C-HTR	Non-Filtered	50µl	✓	CAS-1200-Single-Channel-20-150µl/sec	Non-Sterile
TT-50-C-HTR-S	Non-Filtered	50µl	✓	CAS-1200-Single-Channel-20-150µl/sec	Sterile
TTF-50-C-HTR-S	Filtered	25µl	✓	CAS-1200-Single-Channel-20-150µl/sec	Sterile
TT-200-C-HTR	Non-Filtered	200µl	✓	CAS-1200-Single-Channel-20-150µl/sec	Non-Sterile
TT-200-C-HTR-S	Non-Filtered	200µl	✓	CAS-1200-Single-Channel-20-150µl/sec	Sterile
TTF-200-C-HTR-S	Filtered	175µl	✓	CAS-1200-Single-Channel-20-150µl/sec	Sterile
TT-50-CBK-HTR	Conductive, Non-Filtered	50µl	✓	CAS-1200-Single-Channel-20-150µl/sec	Non-Sterile
TT-50-CBK-HTR-S	Conductive, Non-Filtered	50µl	✓	CAS-1200-Single-Channel-20-150µl/sec	Sterile
TTF-50-CBK-HTR-S	Conductive, Filtered	25µl	✓	CAS-1200-Single-Channel-20-150µl/sec	Sterile
TT-200-CBK-HTR	Conductive, Non-Filtered	200µl	✓	CAS-1200-Single-Channel-20-150µl/sec	Non-Sterile
TT-200-CBK-HTR-S	Conductive, Non-Filtered	200µl	✓	CAS-1200-Single-Channel-20-150µl/sec	Sterile
TTF-200-CBK-HTR-S	Conductive, Filtered	175µl	✓	CAS-1200-Single-Channel-20-150µl/sec	Sterile

Packaging Description: Quantity = 96 tips/rack, 24 racks/case

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
CTF-199-R-S	Filtered	200µl	✓	X-tractor Gene 8-Channel	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/packs, 5 packs/case



Tip Box Format: Non-SBS

Material: Number 5 Polypropylene



PerkinElmer – Compatible Tips

Tips Compatible with PERKINELMER® JANUS®, EVOLUTION P³, MINITRAK & PLATETRAK®

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
PK-20-R	Non-Filtered	20µl	✓	MDT-96 P50	Non-Sterile
PK-20-R-S	Non-Filtered	20µl	✓	MDT-96 P50	Sterile
PKF-20-R-S	Filtered	20µl	✓	MDT-96 P50	Sterile
PK-50-R	Non-Filtered	50µl	✓	MDT-96 P50	Non-Sterile
PK-50-R-S	Non-Filtered	50µl	✓	MDT-96 P50	Sterile
PKF-30-R-S	Filtered	30µl	✓	MDT-96 P50	Sterile
PK-200-R	Non-Filtered	235µl	✓	MDT-96 P235	Non-Sterile
PK-200-R-S	Non-Filtered	235µl	✓	MDT-96 P235	Sterile
PKF-180-R	Filtered	180µl	✓	MDT-96 P235	Sterile
PK-205-WB-R	Wide-Bore, Non-Filtered	235µl	✓	MDT-96 P235	Non-Sterile
PK-205-WB-R-S	Wide-Bore, Non-Filtered	235µl	✓	MDT-96 P235	Sterile
PKF-205-WB-R-S	Wide-Bore, Filtered	180µl	✓	MDT-96 P235	Sterile
PK-384-R	Non-Filtered	30µl	✓	MDT-384 30 ul	Non-Sterile
PK-384-R-S	Non-Filtered	30µl	✓	MDT-384 30 ul	Sterile
PKF-384-R-S	Filtered	30µl	✓	MDT-384 30 ul	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case

Maxym Recovery®

Axygen Cat. No.	Type	Max Volume		Compatible Head	Packaging
PK-20-L-R	Non-Filtered	20µl	✓	MDT-96 P50	Non-Sterile
PK-20-L-R-S	Non-Filtered	20µl	✓	MDT-96 P50	Sterile
PKF-20-L-R-S	Filtered	20µl	✓	MDT-96 P50	Sterile
PK-50-L-R	Non-Filtered	50µl	✓	MDT-96 P50	Non-Sterile
PK-50-L-R-S	Non-Filtered	50µl	✓	MDT-96 P50	Sterile
PKF-30-L-R-S	Filtered	30µl	✓	MDT-96 P50	Sterile
PK-200-L-R	Non-Filtered	235µl	✓	MDT-96 P235	Non-Sterile
PK-200-L-R-S	Non-Filtered	235µl	✓	MDT-96 P235	Sterile
PKF-180-L-R-S	Filtered	180µl	✓	MDT-96 P235	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case



PK-20-R & PK-20-R-S



PKF-20-R-S



PK-50-R & PK-50-R-S



PKF-30-R-S



PK-200-R & PK-200-R-S



PKF-180-R-S



PK-205-WB-R & PK-205-WB-R-S



PKF-205-WB-R-S



PK-384-R & PK-384-R-S



PKF-384-R-S

Format:
96-Tip & 384-Tip Format

TIP Volume Range



Selection:
20µl - 235µl

Material:
Clear Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile
- Standard or Maxym Recovery®

Certified:
DNAse-Free, RNAse-Free,
Pyrogen-Safe



Tip Box Format: SBS
Material: Number 5 Polypropylene



New **PerkinElmer – Compatible Tips**

Tips Compatible with PERKINELMER® JANUS®, & MULTIPROBE

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
RRP-20-CBK-R	Conductive, Non-Filtered	20µl	✓	Variospan-1,4,8	Non-Sterile
RRP-20-CBK-R-S	Conductive, Non-Filtered	20µl	✓	Variospan-1,4,8	Sterile
RRP-50-CBK-R	Conductive, Non-Filtered	50µl	✓	Variospan-1,4,8	Non-Sterile
RRP-50-CBK-R-S	Conductive, Non-Filtered	50µl	✓	Variospan-1,4,8	Sterile
RRF-25-CBK-R-S	Conductive, Filtered	25µl	✓	Variospan-1,4,8	Sterile
RRP-200-CBK-R	Conductive, Non-Filtered	200µl	✓	Variospan-1,4,8	Non-Sterile
RRP-200-CBK-R-S	Conductive Non-Filtered	200µl	✓	Variospan-1,4,8	Sterile
RRF-175-CBK-R-S	Conductive, Filtered	175µl	✓	Variospan-1,4,8	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
TT-1000-CBK-HTR	Conductive, Non-Filtered	1000µl	✓	Variospan-1,4,8	Non-Sterile
TT-1000-CBK-HTR-S	Conductive, Non-Filtered	1000µl	✓	Variospan-1,4,8	Sterile
TTF-1000-CBK-HTR-S	Conductive, Filtered	1000µl	✓	Variospan-1,4,8	Sterile

Packaging Description: Quantity = 96 tips/rack, 16 racks/case

RRP-20-CBK-R & RRP-20-CBK-R-S

RRP-50-CBK-R & RRP-50-CBK-R-S

RRF-25-CBK-R-S

RRP-200-CBK-R & RRP-200-CBK-R-S

RRF-175-CBK-R-S

TT-1000-CBK-HTR & TT-1000-CBK-HTR-S

TTF-1000-CBK-HTR-S

Format:

96-Tip Format

TIP Volume Range

Selection:

20µl - 1000µl

Material:



Conductive LLS Black
Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile

Certified:

DNase-Free, RNase-Free,
Pyrogen-Safe





New PerkinElmer – Compatible Tips




Tips Compatible with PERKINELMER® JANUS®, & MULTIPROBE

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
RRP-20-C-R	Non-Filtered	20µl	✓	Variospan-1,4,8	Non-Sterile
RRP-20-C-R-S	Non-Filtered	20µl	✓	Variospan-1,4,8	Sterile
RRP-50-C-R	Non-Filtered	50µl	✓	Variospan-1,4,8	Non-Sterile
RRP-50-C-R-S	Non-Filtered	50µl	✓	Variospan-1,4,8	Sterile
RRF-25-C-R-S	Filtered	25µl	✓	Variospan-1,4,8	Sterile
RRP-200-C-R	Non-Filtered	235µl	✓	Variospan-1,4,8, P235	Non-Sterile
RRP-200-C-R-S	Non-Filtered	235µl	✓	Variospan-1,4,8, P235	Sterile
RRF-175-C-R-S	Filtered	175µl	✓	Variospan-1,4,8, P235	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
TT-1000-C-HTR	Non-Filtered	1000µl	✓	Variospan-1,4,8	Non-Sterile
TT-1000-C-HTR-S	Non-Filtered	1000µl	✓	Variospan-1,4,8	Sterile
TTF-1000-C-HTR-S	Filtered	1000µl	✓	Variospan-1,4,8	Sterile

Packaging Description: Quantity = 96 tips/rack, 16 racks/case



RRP-20-C-R & RRP-20-C-R-S



RRP-50-C-R & RRP-50-C-R-S



RRF-25-C-R-S



RRP-200-C-R & RRP-200-C-R-S



RRF-175-C-R-S



TT-1000-C-HTR & TT-1000-C-HTR-S



TTF-1000-C-HTR-S

Format:

96-Tip Format

TIP Volume Range

Selection:

20µl - 1000µl

Material:


Conductive LLS Black Polypropylene

Available Options:


- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile

Certified:

DNase-Free, RNase-Free, Pyrogen-Safe



Tip Box Format: SBS
Material: Number 5 Polypropylene





Zymark/Caliper – Compatible Tips

Tips Compatible with ZYMARK® / CALIPER RapidPlate® & SciClone®

Tips for these Zymark/Caliper systems are compatible with Corbett CAS-4200.

Oxygen Cat No.	Type	Max Volume		Compatible Head	Packaging
ZT-50-R	Non-Filtered	50µl	-	HV96	Non-Sterile
ZT-50-R-S	Non-Filtered	50µl	-	HV96	Sterile
ZTF-50-R-S	Filtered	50µl	-	HV96	Sterile
ZT-100-R	Non-Filtered	100µl	-	HV96, CAS-4200-1ch-20-150µl/sec	Non-Sterile
ZT-100-R-S	Non-Filtered	100µl	-	HV96, CAS-4200-1ch-20-150µl/sec	Sterile
ZTF-100-R-S	Non-Filtered	80µl	-	HV96, CAS-4200-1ch-20-150µl/sec	Sterile
ZT-200-R	Filtered	200µl	-	HV96, CAS-4200-1ch-20-150µl/sec	Non-Sterile
ZT-200-R-S	Non-Filtered	200µl	-	HV96, CAS-4200-1ch-20-150µl/sec	Sterile
ZTF-200-R-S	Non-Filtered	180µl	-	HV96, CAS-4200-1ch-20-150µl/sec	Sterile
ZT-205-WB-R	Wide-Bore, Non-Filtered	200µl	-	HV96, CAS-4200-1ch-20-150µl/sec	Non-Sterile
ZT-205-WB-R-S	Wide-Bore, Non-Filtered	200µl	-	HV96, CAS-4200-1ch-20-150µl/sec	Sterile
ZTF-205-WB-R-S	Wide-Bore, Filtered	180µl	-	HV96, CAS-4200-1ch-20-150µl/sec	Sterile

New

New

ZT-384-C-R	Non-Filtered	25µl	✓	LV96, LV384	Non-Sterile
ZT-384-C-R-S	Non-Filtered	25µl	✓	LV96, LV384	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case

Maxym Recovery®

Oxygen Cat No.	Type	Max Volume		Compatible Head	Packaging
ZT-50-L-R	Non-Filtered	50µl		HV96	Non-Sterile
ZT-50-L-R-S	Non-Filtered	50µl		HV96	Sterile
ZTF-50-L-R-S	Filtered	50µl		HV96	Sterile
ZT-100-L-R	Non-Filtered	100µl		HV96, CAS-4200-1ch- 20-150µl/sec	Non-Sterile
ZT-100-L-R-S	Non-Filtered	100µl		HV96, CAS-4200-1ch- 20-150µl/sec	Sterile
ZTF-100-L-R-S	Non-Filtered	80µl		HV96, CAS-4200-1ch- 20-150µl/sec	Sterile
ZT-200-L-R	Filtered	200µl		HV96, CAS-4200-1ch- 20-150µl/sec	Non-Sterile
ZT-200-L-R-S	Non-Filtered	200µl		HV96, CAS-4200-1ch- 20-150µl/sec	Sterile
ZTF-200-L-R-S	Non-Filtered	180µl		HV96, CAS-4200-1ch- 20-150µl/sec	Sterile
ZT-205-WB-L-R	Wide-Bore, Non-Filtered	200µl		HV96, CAS-4200-1ch- 20-150µl/sec	Non-Sterile
ZT-205-WB-L-R-S	Wide-Bore, Non-Filtered	200µl		HV96, CAS-4200-1ch- 20-150µl/sec	Sterile
ZTF-205-WB-L-R-S	Wide-Bore, Filtered	180µl		HV96, CAS-4200-1ch- 20-150µl/sec	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case



ZT-50-R & ZT-50-R-S



ZTF-50-R-S



ZT-100-R & ZT-100-R-S



ZTF-100-R-S



ZT-200-R & ZT-200-R-S



ZTF-200-R-S



ZT-205-WB-R & ZT-205-WB-R-S



ZTF-205-WB-R-S



ZT-384-C-R & ZT-384-C-R-S

Format:

96-Tip Format

TIP Volume Range

Selection:

25µl - 200µl

Material:



Clear Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile
- Standard or Maxym Recovery®

Certified:

DNase-Free, RNase-Free, Pyrogen-Safe





Zymark/Caliper - Compatible Tips



Tips Compatible with ZYMARK®/CALIPER RAPIDPLATE®, SciCLONE® & ZEPHYR®

For use on SBS Plate footprint deck carriers.

Oxygen Cat No.	Type	Max Volume		Compatible Head	Packaging
EV-50-R	Non-Filtered	50µl	✓	HV96	Non-Sterile
EV-50-R-S	Non-Filtered	50µl	✓	HV96	Sterile
EVF-50-R-S	Filtered	50µl	✓	HV96	Sterile
EV-100-R	Non-Filtered	100µl	✓	HV96	Non-Sterile
EV-100-R-S	Non-Filtered	100µl	✓	HV96	Sterile
EVF-100-R-S	Filtered	80µl	✓	HV96	Sterile
EV-200-R	Non-Filtered	200µl	✓	HV96	Non-Sterile
EV-200-R-S	Non-Filtered	200µl	✓	HV96	Sterile
EVF-180-R-S	Filtered	180µl	✓	HV96	Sterile
EV-205-WB-R	Wide-Bore, Non-Filtered	200µl	✓	HV96	Non-Sterile
EV-205-WB-R-S	Wide-Bore, Non-Filtered	200µl	✓	HV96	Sterile
EVF-205-WB-R-S	Wide-Bore, Filtered	180µl	✓	HV96	Sterile
ZT-384-C-R	Non-Filtered	25µl	✓	LV96, LV384	Non-Sterile
ZT-384-C-R-S	Non-Filtered	25µl	✓	LV96, LV384	Sterile

Packaging Description:

Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case



EV-50-R & EV-50-R-S



EVF-50-R-S



EV-100-R & EV-100-R-S



EVF-100-R-S



EV-200-R & EV-200-R-S



EVF-180-R-S



EV-205-WB-R & EV-205-WB-R-S



EVF-205-WB-R-S



ZT-384-C-R & ZT-384-C-R-S

Format:

96-Tip Format

TIP Volume Range

Selection:

25µl - 200µl

Material:


Clear Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile


Certified:


DNase-Free, RNase-Free, Pyrogen-Safe



Tip Box Format: SBS

Material: Number 5 Polypropylene





New Qiagen – Compatible Tips

Tips Compatible with QIAGEN® Biorobot® MDx, 3000, 8000, 9600 & 9604

For use on SBS Plate footprint deck carriers.

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
QT-300-R	Non-Filtered	300µl	✓	Biorobot®	Non-Sterile
QT-300-R-S	Non-Filtered	300µl	✓	Biorobot®	Sterile
QTF-300-R-S	Filtered	250µl	✓	Biorobot®	Sterile

Packaging Description: Quantity = 96 tips/rack, 24 racks/case

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
QT-1100-R	Non-Filtered	1100µl	✓	Biorobot®	Non-Sterile
QT-1100-R-S	Non-Filtered	1100µl	✓	Biorobot®	Sterile
QTF-1100-R-S	Filtered	1000µl	✓	Biorobot®	Sterile

Packaging Description: Quantity = 96 tips/rack, 16 racks/case

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
QT-300-CBK-R	Conductive, Non-Filtered	300µl	✓	Biorobot®	Non-Sterile
QT-300-CBK-R-S	Conductive, Non-Filtered	300µl	✓	Biorobot®	Sterile
QTF-300-CBK-R-S	Conductive, Filtered	250µl	✓	Biorobot®	Sterile

Packaging Description: Quantity = 96 tips/rack, 24 racks/case

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
QT-1100-CBK-R	Conductive, Non-Filtered	1100µl	✓	Biorobot®	Non-Sterile
QT-1100-CBK-R-S	Conductive, Non-Filtered	1100µl	✓	Biorobot®	Sterile
QTF-1100-CBK-R-S	Conductive, Filtered	1000µl	✓	Biorobot®	Sterile

Packaging Description: Quantity = 96 tips/rack, 16 racks/case

QT-300-R & QT-300-R-S

QT-300-R-S

QT-1100-R & QT-1100-R-S

QTF-1100-R-S

QT-300-CBK-R & QT-300-CBK-R-S

QTF-300-CBK-R-S

QT-1100-CBK-R & QT-1100-CBK-R-S

QTF-1100-CBK-R-S

Format:

96-Tip Format

TIP Volume Range

Selection:

250µl - 1100µl

Material:


- Clear Polypropylene
- Conductive LLS Black Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile

Certified:

DNAse-Free, RNAse-Free, Pyrogen-Safe





BioTek – Compatible Tips

Tips Compatible with BIOTEK® PRECISION™ and PRECISION™ XS

Oxygen Cat No.	Type	Max Volume		Compatible Head	Packaging
EV-50-R	Non-Filtered	50µl	✓	8 or 12	Non-Sterile
EV-50-R-S	Non-Filtered	50µl	✓	8 or 12	Sterile
EVF-50-R-S	Filtered	50µl	✓	8 or 12	Sterile
EV-100-R	Non-Filtered	100µl	✓	8 or 12	Non-Sterile
EV-100-R-S	Non-Filtered	100µl	✓	8 or 12	Sterile
EVF-100-R-S	Filtered	80µl	✓	8 or 12	Sterile
EV-200-R	Non-Filtered	200µl	✓	8 or 12	Non-Sterile
EV-200-R-S	Non-Filtered	200µl	✓	8 or 12	Sterile
EVF-180-R-S	Filtered	180µl	✓	8 or 12	Sterile
EV-205-WB-R	Wide-Bore, Non-Filtered	200µl	✓	8 or 12	Non-Sterile
EV-205-WB-R-S	Wide-Bore, Non-Filtered	200µl	✓	8 or 12	Sterile
EVF-205-WB-R-S	Wide-Bore, Filtered	180µl	✓	8 or 12	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case



EV-50-R & EV-50-R-S



EVF-50-R-S



EV-100-R & EV-100-R-S



EVF-100-R-S



EV-200-R & EV-200-R-S



EVF-180-R-S



EV-205-WB-R & EV-205-WB-R-S



EVF-205-WB-R-S

Format:

96-Tip Format

TIP Volume Range

Selection:

50µl - 200µl

Material:



Clear Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile

Certified:

DNAse-Free, RNAse-Free, Pyrogen-Safe



Tip Box Format: SBS

Material: Number 5 Polypropylene



Dynamic Devices – Compatible Tips

Tips Compatible with DYNAMIC DEVICES Oasis LM

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
EV-50-R	Non-Filtered	50µl	✓	8/96-Channel-Standard Volume 96-Ch-Low Volume	Non-Sterile
EV-50-R-S	Non-Filtered	50µl	✓	8/96-Channel-Standard Volume 96-Ch-Low Volume	Sterile
EVF-50-R-S	Filtered	50µl	✓	8/96-Channel-Standard Volume 96-Ch-Low Volume	Sterile
EV-100-R	Non-Filtered	100µl	✓	8/96-Channel-Standard Volume	Non-Sterile
EV-100-R-S	Non-Filtered	100µl	✓	8/96-Channel-Standard Volume	Sterile
EVF-100-R-S	Filtered	80µl	✓	8/96-Channel-Standard Volume	Sterile
EV-200-R	Non-Filtered	200µl	✓	8/96-Channel-Standard Volume	Non-Sterile
EV-200-R-S	Non-Filtered	200µl	✓	8/96-Channel-Standard Volume	Sterile
EVF-180-R-S	Filtered	180µl	✓	8/96-Channel-Standard Volume	Sterile
EV-205-WB-R	Non-Filtered	200µl	✓	8/96-Channel-Standard Volume	Non-Sterile
EV-205-WB-R-S	Non-Filtered	200µl	✓	8/96-Channel-Standard Volume	Sterile
EVF-205-WB-R-S	Filtered	180µl	✓	8/96-Channel-Standard Volume	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case

Format:

96-Tip Format

TIP Volume Range**Selection:**

50µl - 200µl

Material:



Clear Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile

Certified:

DNAse-Free, RNAse-Free, Pyrogen-Safe



Dynamic Devices – Compatible Tips



Tips Compatible with DYNAMIC DEVICES Oasis LM

Axygen Cat. No.	Type	Max Volume		Compatible Head	Packaging
FX-384-XL-R	Non-Filtered	50µl	✓	384-Channel-Low Volume	Non-Sterile
FX-384-XL-R-S	Non-Filtered	50µl	✓	384-Channel-Low Volume	Sterile
FXF-384-XL-R-S	Filtered	30µl	✓	384-Channel-Low Volume	Sterile
FX-384-R	Non-Filtered	30µl	✓	384-Channel-Low Volume	Non-Sterile
FX-384-R-S	Non-Filtered	30µl	✓	384-Channel-Low Volume	Sterile
FXF-384-R-S	Filtered	25µl	✓	384-Channel-Low Volume	Sterile

Packaging Description: Quantity = 384 tips/rack, 10 racks/pack, 5 packs/case

Maxymum Recovery®

Axygen Cat. No.	Type	Max Volume		Compatible Head	Packaging
FX-384-XL-L-R	Non-Filtered	50µl	✓	384-Channel-Low Volume	Non-Sterile
FX-384-XL-L-R-S	Non-Filtered	50µl	✓	384-Channel-Low Volume	Sterile
FXF-384-XL-L-R-S	Filtered	30µl	✓	384-Channel-Low Volume	Sterile
FX-384-L-R	Non-Filtered	30µl	✓	384-Channel-Low Volume	Non-Sterile
FX-384-L-R-S	Non-Filtered	30µl	✓	384-Channel-Low Volume	Sterile
FXF-384-L-R-S	Filtered	25µl	✓	384-Channel-Low Volume	Sterile

Packaging Description: Quantity = 384 tips/rack, 10 racks/pack, 5 packs/case



FX-384-XL-R & FX-384-XL-R-S



FXF-384-XL-R-S



FX-384-R & FX-384-R-S



FXF-384-R-S

Format:

384-Tip Format

TIP Volume Range

Selection:
25µl - 50µl

Material:



Clear Polypropylene

Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile

Certified:

DNase-Free, RNase-Free,
Pyrogen-Safe





Hamilton – Compatible Tips

Tips Compatible with HAMILTON® MICROLAB® STAR, STARLET and STARPLUS

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
FX-384-XL-R	Non-Filtered	50µl	✓	384-Channel-Low Volume	Non-Sterile
FX-384-XL-R-S	Non-Filtered	50µl	✓	384-Channel-Low Volume	Sterile
FXF-384-XL-R-S	Filtered	30µl	✓	384-Channel-Low Volume	Sterile
FX-384-R	Non-Filtered	30µl	✓	384-Channel-Low Volume	Non-Sterile
FX-384-R-S	Non-Filtered	30µl	✓	384-Channel-Low Volume	Sterile
FXF-384-R-S	Filtered	25µl	✓	384-Channel-Low Volume	Sterile

Packaging Description: Quantity = 384 tips/rack, 10 racks/pack, 5 packs/case

Maxym Recovery®

Axygen Cat. No.	Type	Max Volume		Compatible Head	Packaging
FX-384-XL-L-R	Non-Filtered	50µl	✓	384-Channel-Low Volume	Non-Sterile
FX-384-XL-L-R-S	Non-Filtered	50µl	✓	384-Channel-Low Volume	Sterile
FXF-384-XL-L-R-S	Filtered	30µl	✓	384-Channel-Low Volume	Sterile
FX-384-L-R	Non-Filtered	30µl	✓	384-Channel-Low Volume	Non-Sterile
FX-384-L-R-S	Non-Filtered	30µl	✓	384-Channel-Low Volume	Sterile
FXF-384-L-R-S	Filtered	25µl	✓	384-Channel-Low Volume	Sterile

Packaging Description: Quantity = 384 tips/rack, 10 racks/pack, 5 packs/case



FX-384-XL-R & FX-384-XL-R-S



FXF-384-XL-R-S



FX-384-R & FX-384-R-S



FXF-384-R-S

Format:

384-Tip Format

TIP Volume Range

Selection:

25µl -50µl

Material:


Clear Polypropylene

Available Options:


- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile

Certified:

DNase-Free, RNase-Free,
Pyrogen-Safe



Tip Box Format: SBS
Material: Number 5 Polypropylene





WellPro – Compatible Tips

Tips Compatible with WELLPRO

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
FX-384-XL-R	Non-Filtered	50µl	✓	16/24 Channel	Non-Sterile
FX-384-XL-R-S	Non-Filtered	50µl	✓	16/24 Channel	Sterile
FXF-384-XL-R-S	Filtered	30µl	✓	16/24 Channel	Sterile

Packaging Description: Quantity = 384 tips/rack, 10 racks/pack, 5 packs/case

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
TWP-200-R	Non-Filtered	200µl	–	8/12 Channel	Non-Sterile
TWP-200-R-S	Non-Filtered	200µl	–	8/12 Channel	Sterile
TWPF-120-R-S	Filtered	120µl	–	8/12 Channel	Sterile

Packaging Description: Quantity = 96 tips/rack, 10 racks/pack, 5 packs/case

Maxymum Recovery®

Axygen Cat No.	Type	Max Volume		Compatible Head	Packaging
FX-384-XL-L-R	Non-Filtered	50µl	✓	16/24 Channel	Non-Sterile
FX-384-XL-L-R-S	Non-Filtered	50µl	✓	16/24 Channel	Sterile
FXF-384-XL-L-R-S	Filtered	30µl	✓	16/24 Channel	Sterile

Packaging Description: Quantity = 384 tips/rack, 10 racks/pack, 5 packs/case



FX-384-XL-R & FX-384-XL-R-S



FXF-384-XL-R-S



TWP-200-R & TWP-200-R-S



TWPF-120-R-S

Format:
96 & 384-Tip Format

TIP Volume Range Selection:
30µl -200µl



Material:
Clear Polypropylene


Available Options:

- With or Without Aerosol-Resistant Filters
- Non-Sterile or Sterile
- Standard or Maxymum Recovery®

Certified:

DNAse-Free, RNAse-Free, Pyrogen-Safe





High Throughput Screening

Axygen's extensive line of HTS products provide researchers with solutions to the challenges in drug discovery

With the ever-growing pressure to find the next blockbuster drug, technicians are faced with the need to screen more targets more efficiently and against a larger library of compounds. Automation has greatly streamlined many standard lab tasks, including liquid handling and sample manipulation.

High throughput screening methods have also increased the need for precisely engineered and consistently manufactured lab consumables. Count on Axygen to be at the forefront of new product R&D and manufacturing improvements, ensuring your complete satisfaction with every item you use.

Deep Well Plates

- ▶ **500µl, 1.1ml, 1.6ml, 2.2ml, 5.0ml and 10.0ml capacities**, in durable polypropylene
- ▶ **1.1ml features an ultra-low profile** for reduced space requirements

Reservoirs

- ▶ **Numerous formats** for almost any manual or automated application
- ▶ **SBS footprint** for compatibility with most robotic systems

Axymats (patented)

- ▶ **Multi-use silicone sealing mats** feature pierceable and self-sealing well covers for easy access
- ▶ **Available in** 96 and 384-well options

ImpermaMats

- ▶ **Chemically resistant silicone sealing mats** resistant to DMSO and other solvents with a high degree of confidence
- ▶ **Contains NO adhesives** - no extractables to contaminate samples



1 Deep Well and Assay Plates



2 Single Well and Multi-well Reservoirs



3 Axymats



4 Chemically Resistant ImpermaMats



1 Deep Well and Assay Plates are used for sample collection, in-vitro growth chambers and long-term storage. Made of virgin polypropylene, they offer excellent chemical resistance and will withstand temperatures down to -80°C.

2 Single Well and Multi-well Reservoirs are a complete line of reagent vessels in numerous formats for automated and manual applications. All are designed with an SBS footprint for compatibility with most robotic systems and are made of virgin polypropylene for excellent chemical resistance.

3 Axymats are patented sealing mats designed for high throughput screening and storage applications. Made of research-grade silicone, they can be autoclaved and following a bleach wash and ethanol rinse protocol, they can also be reused. Axymats are pierceable and self-sealing, ideal for automated processes and can be used in sub-zero environments.

4 Chemically Resistant ImpermaMats (patent pending) are a chemical-resistant line of sealing mats. They are made for use in assays involving strong solvents such as DMSO and similarly harsh solvents. Specifically designed for Axygen deep well and microplates, they contain no extractables to contaminate samples. They feature a tight seal to the plate - no sample evaporation or well-to-well contamination. Usable within wide temperature range - from -80°C up to +121°C. Cost effective - can be re-used.

Deep Well Plates

384-Well Diamond Plates

- Excellent chemical resistance
- Standard SBS footprint
- Centrifugation to 4,000 RCF
- Diamond shaped wells allow complete sample recovery
- Ultra-flat surface ensures proper sealing of heat film

50µl RigiPlate™



Axygen Cat No	Volume to Brim of Well	Working Volume	Volume with Axymat	Colour	Product Descriptions	Packaging
PCR-384-RGD-C	50µl	49.5µl	-	Clear	384-well RigiPlate™	Bulk
AM-384-PCR-RD	-	-	30µl	Natural	Sealing Mat for 384-well PCR Microplates	Bulk
AM-384-PCR-RV	-	-	30µl	Natural	Volume Reducing Sealing Mat	Bulk

Packaging Description: Plates = 10 plates/sleeve, 2 sleeves/pack, 5 packs/case;
Mats = 10 mats/pack, 5 packs/case

Colors available by special order. Contact customer service for details.

120µl Deep Well Plate



Axygen Cat No	Volume to Brim of Well	Working Volume	Volume with Axymat	Colour	Product Descriptions	Packaging
P-384-120SQ-C	130µl	120µl	-	Clear	384-well Deep well Micro Plate	Bulk
AM-384-DW-SQ	-	-	90µl	Natural	Sealing Mat for 384-well MicroPlates with Square Wells	Bulk
AM-384-SQ-IMP	-	-	90µl	Natural	Chemically Resistant Sealing Mat for 384-well MicroPlates with Square Wells	Bulk

Packaging Description: Plates = 5 plates/pack, 10 packs/case;
Mats = 10 mats/pack, 5 packs/case

Black and white plates available by special order.

240µl Deep Well Plate



Axygen Cat No	Volume to Brim of Well	Working Volume	Volume with Axymat	Colour	Product Descriptions	Packaging
P-384-240SQ-C	250µl	240µl	-	Clear	384-well Deep Well Plate	Bulk
AM-384-DW-SQ	-	-	210µl	Natural	Sealing Mat for 384-well Deep Well Plates with Square Wells	Bulk
AM-384-SQ-IMP	-	-	210µl	Natural	Chemically Resistant Sealing Mat for 384 Deep Well Plates with Square Wells	Bulk

Packaging Description: Plates = 5 plates/pack, 10 packs/case;
Mats = 10 mats/pack, 5 packs/case

Black and white plates available by special order.

Deep Well Plates

96-Well Round and Rectangle Bottoms

0.6ml Deep Well Plate

Axygen Cat No	Volume to Brim of Well	Working Volume	Volume with Axymat	Colour	Product Descriptions	Packaging
P-DW-500-C	620µl	560µl	-	Clear	96-well Deep Well Plate, 600µl	Bulk
P-DW-500-C-S	620µl	560µl	-	Clear	96-well Deep Well Plate, 600µl	Bulk Sterile
AM-500UL-RD	-	-	440µl	Natural	Sealing Mat for 600µl 96-well Deep Well Plates	Bulk

Packaging Description: Plates = 5 plates/pack, 10 packs/case;
Mats = 10 mats/pack, 5 packs/case

1.1ml Deep Well Plate

Axygen Cat No	Volume to Brim of Well	Working Volume	Volume with Axymat	Colour	Product Descriptions	Packaging
P-DW-11-C	1.2ml	1.1ml	-	Clear	96-well Deep Well Plate, 1.1ml	Bulk
P-DW-11-C-S	1.2ml	1.1ml	-	Clear	96-well Deep Well Plate, 1.1ml	Bulk Sterile
AM-2ML-RD	-	-	1.0ml	Natural	Sealing Mat for 1.1ml 96-well Deep Well Plates	Bulk
AM-2ML-RD-IMP	-	-	1.0ml	Natural	Chemically Resistant Sealing Mat for 1.1ml 96-well Deep Well Plates	Bulk

Packaging Description: Plates = 5 plates/pack, 10 packs/case;
Mats = 10 mats/pack, 5 packs/case

1.6ml Deep Well Plate – Round Wells

Axygen Cat No	Volume to Brim of Well	Working Volume	Volume with Axymat	Colour	Product Descriptions	Packaging
P-DW-20-C	1.7ml	1.6ml	-	Clear	96-well Deep Well Plate, 2.0ml Round Wells	Bulk
P-DW-20-C-S	1.7ml	1.6ml	-	Clear	96-well Deep Well Plate, 2.0ml Round Wells, Sterile	Bulk
AM-2ML-RD	-	-	1.5ml	Natural	Sealing Mat for 2.0ml 96-well Round Deep Well Plates	Bulk
AM-2ML-RD-IMP	-	-	1.5ml	Natural	Chemically Resistant Sealing Mat for 2.0ml 96-well Deep Well Plates with Round Wells	Bulk

Packaging Description: Plates = 5 plates/pack, 10 packs/case;
Mats = 10 mats/pack, 5 packs/case

1.1ml Deep Well Plate – Square Wells



Axygen Cat No	Volume to Brim of Well	Working Volume	Volume with Axymat	Colour	Product Descriptions	Packaging
P-1ML-SQ-C	1.2ml	1.1ml	-	Clear	96-well Deep Well Plate, 2.0ml Rectangular Wells	Bulk
AM-2ML-SQ	-	-	1.9ml	Natural	Sealing Mat for 2.0ml, 96-well Deep Well Plates with Rectangular Wells	Bulk
AM-2ML-SQ-IMP	-	-	1.9ml	Natural	Chemically Resistant Sealing Mat for 2.0ml 96-well Deep Well Plates with Rectangular Wells	Bulk

Packaging Description: Plates = 5 plates/pack, 10 packs/case;
Mats = 10 mats/pack, 5 packs/case

2.2ml Deep Well Plate – Square Wells

Axygen Cat No	Volume to Brim of Well	Working Volume	Volume with Axymat	Colour	Product Descriptions	Packaging
P-2ML-SQ-C	2.3ml	2.2ml	-	Clear	96-well Deep Well Plate, 2.0ml Rectangular Wells	Bulk
P-2ML-SQ-C-S	2.3ml	2.2ml	-	Clear	96-well Deep Well Plate, 2.0ml Rectangular Wells, Sterile	Bulk
AM-2ML-SQ	-	-	1.9ml	Natural	Sealing Mat for 2.0ml, 96-well Deep Well Plates with Rectangular Wells	Bulk
AM-2ML-SQ-IMP	-	-	1.9ml	Natural	Chemically Resistant Sealing Mat for 2.0ml 96-well Deep Well Plates with Rectangular Wells	Bulk

Packaging Description: Plates = 5 plates/pack, 5 packs/case;
Mats = 10 mats/pack, 5 packs/case



Deep Well/Assay Plates

Round and 'V' Well Options

5.0ml Deep Well Plate – Rectangular Wells

Axygen Cat No	Volume to Brim of Well	Working Volume	Volume with Axymat	Colour	Product Descriptions	Packaging
P-5ML-48-C	4.9ml	4.6ml	-	Clear	48-well Deep Well Plate, 5.0ml	Bulk
P-5ML-48-C-S	4.9ml	4.6ml	-	Clear	48-well Deep Well Plate, 5.0ml Rectangular Wells, Sterile	Bulk
AM-48-IMP	-	-	4.0ml	Natural	Chemically Resistant Sealing Mat for 5.0ml 48 Well Deep Well Plates	Bulk

Packaging Description: Plates = 5 plates/pack; 5 packs/case
Mats = 10 mats/pack, 5 packs/case

10ml Deep Well Plate – Rectangular Wells

Axygen Cat No	Volume to Brim of Well	Working Volume	Volume with Axymat	Colour	Product Descriptions	Packaging
P-DW-10ML-24-C	9.8ml	9.2ml	-	Clear	24-well Deep Well Plate, 10ml	Bulk*

Packaging Description: Plates = 5 plates/pack; 5 packs/case
Mats = 10 mats/pack, 5 packs/case

Round Well Assay Plate

Axygen Cat No	Volume to Brim of Well	Working Volume	Volume with Axymat	Colour	Product Descriptions	Packaging
P-96-450R-C	550µl	550µl	-	Clear	96-well Assay Round Bottom Plate	Bulk
P-96-450R-C-S	550µl	550µl	-	Clear	96-well Assay Round Bottom Plate Sterile	Bulk
AM-2ML-RD	-	-	350µl	Natural	Sealing Mat for 96-well Assay Plates with Round Wells	Bulk
AM-2ML-RD-IMP	-	-	1.0ml	Natural	Chemically Resistant Sealing Mat for 96-well Assay Plates with Round Wells	Bulk

Packaging Description: Plates = 10 plates/pack, 5 packs/case; Mats = 10 mats/pack, 5 packs/case

'V' Well Assay Plate


Axygen Cat No	Volume to Brim of Well	Working Volume	Volume with Axymat	Colour	Product Descriptions	Packaging
P-96-450V-C	520µl	480µl	-	Clear	96-well Assay 'V' Bottom Plate	Bulk
P-96-450V-C-S	520µl	480µl	-	Clear	96-well Assay 'V' Bottom Plate	Bulk
AM-2ML-RD	-	-	300µl	Natural	Sealing Mat for 96-well Assay Plates with 'V' Wells	Bulk
AM-2ML-RD-IMP	-	-	1.5ml	Natural	Chemically Resistant Sealing Mat for 96-well Assay Plates with Round Wells	Bulk

Packaging Description: Plates = 5 plates/pack, 10 packs/case; Mats = 10 mats/pack, 5 packs/case

Centrifuge Adapter for Deep Well Plates

Axygen Cat No	Volume to Brim of Well	Working Volume	Volume with Axymat	Colour	Product Descriptions	Packaging
P-ADAPTER-1	-	-	-	Aluminum	Centrifuge adapter for Deep Well plates	Bulk

Packaging Description: 2 Adapters/Case; (includes one of each of Axgen's popular deep well plates)



Reagent Reservoirs

High and Low Profile

- SBS footprint
- Robot compatible
- Minimizes dead volume
- Durable for multi-use and cost effective for single use
- Various formats for any application

Axygen's Reagent Reservoirs are manufactured in translucent polypropylene. With a standard SBS footprint, they are designed to be robot compatible.

Three design styles are available to fit any liquid handling application:

- **Flat Bottom Series:** single-well, low-profile, guaranteed flatness for a wide variety of applications.
- **Diamond Shaped-well Series:** 96- or 384- collection pools at the bottom surface help minimize dead volume.
- **Trough Series:** Unique "flow troughs" extending the length of the bottom surface are ideal for 8- and 12-channel applications.

Sterile Reservoirs are available upon request..

8 Channel Low Profile



Axygen Cat No	Maximum Volume	Max Vol per well	Colour	Series Style	Product Descriptions	Packaging
RES-MW8-LP	32ml	4.0ml	Clear	Trough	Reservoir, multi well, 8 Channel troughs, low profile	Bulk

12 Channel Low Profile



Axygen Cat No	Maximum Volume	Max Vol per well	Colour	Series Style	Product Descriptions	Packaging
RES-MW12-LP	21ml	1.75ml	Clear	Trough	Reservoir, multi well, 12 Channel troughs, low profile	Bulk

4 Channel High Profile



Axygen Cat No	Maximum Volume	Max Vol per well	Colour	Series Style	Product Descriptions	Packaging
RES-MW4-HP	80ml	19ml	Clear	Trough	Reservoir, multi well, 4 Channel troughs, high profile	Bulk

8 Channel High Profile



Axygen Cat No	Maximum Volume	Max Vol per well	Colour	Series Style	Product Descriptions	Packaging
RES-MW8-HP	80ml	10ml	Clear	Trough	Reservoir, multi well, 8 Channel troughs, high profile	Bulk

12 Channel High Profile



Axygen Cat No	Maximum Volume	Max Vol per well	Colour	Series Style	Product Descriptions	Packaging
RES-MW12-HP	84ml	7.0ml	Clear	Trough	Reservoir, multi well, 12 Channel troughs, high profile	Bulk

Packaging Description: 25 reservoirs/case

Reagent Reservoirs

High and Low Profile

8 Bottom High Profile



Axygen Cat No	Maximum Volume	Max Vol per well	Colour	Series Style	Product Descriptions	Packaging
RES-SW8-HP	290ml	290ml	Clear	Trough	Reservoir, single well, 8 bottom troughs, high profile	Bulk

12 Bottom High Profile



Axygen Cat No	Maximum Volume	Max Vol per well	Colour	Series Style	Product Descriptions	Packaging
RES-SW12-HP	290ml	290ml	Clear	Trough	Reservoir, single well, 12 bottom troughs, high profile	Bulk

96 Bottom High Profile



Axygen Cat No	Maximum Volume	Max Vol per well	Colour	Series Style	Product Descriptions	Packaging
RES-SW96-HP	240ml	240ml	Clear	Diamond Shaped Well	Reservoir, single well, 96 bottom troughs, high profile	Bulk

384 Bottom High Profile



Axygen Cat No	Maximum Volume	Max Vol per well	Colour	Series Style	Product Descriptions	Packaging
RES-SW384-HP	282ml	282ml	Clear	Diamond Shaped Well	Reservoir, single well, 384 bottom troughs, high profile	Bulk

384 Bottom Mid Profile



New

Axygen Cat No	Maximum Volume	Max Vol per well	Colour	Series Style	Product Descriptions	Packaging
RES-SW384-FX	170ml	170ml	Clear	Diamond Shaped Well	Reservoir, single well, 384 bottom troughs, medium profile	Bulk

96 Bottom Low Profile



Axygen Cat No	Maximum Volume	Max Vol per well	Colour	Series Style	Product Descriptions	Packaging
RES-SW96-LP	86ml	86ml	Clear	Diamond Shaped Well	Reservoir, single well, 96 bottom troughs, low profile	Bulk

384 Bottom Low Profile



Axygen Cat No	Maximum Volume	Max Vol per well	Colour	Series Style	Product Descriptions	Packaging
RES-SW384-LP	92ml	92ml	Clear	Diamond Shaped Well	Reservoir, single well, 384 bottom troughs, low profile	Bulk

Single Bottom Low Profile



Axygen Cat No	Maximum Volume	Max Vol per well	Colour	Series Style	Product Descriptions	Packaging
RES-SW1-LP	90ml	90ml	Clear	Flat Bottom	Reservoir, single well, 1 bottom flat, low profile	Bulk

Packaging Description: 25 reservoirs/case



Axygen Cat No	Product Descriptions	Packaging
RES-BAFFLE	Baffle for Reservoir, suitable for single well reservoirs. Creates 9 separate chambers with flow through arches	Bulk

Packaging Description: 10 reservoirs/case

For Compound Library Storage

-

Axygen Cat No	Tube Volume	Product Description	Packaging
MTS-11-C-R	1.1ml	Mini Tube, Single	96/rack, 10 racks/pack, 5 packs/case
MTS-11-C-R-S	1.1ml	Mini Tube, Single*	96/rack, 10 racks/pack, 5 packs/case
MTS-11-C	1.1ml	Mini Tube, Single	960 tubes/bag, 5 bags/case
MTS-11-8-C-R	1.1ml	Mini Tube, 8-strip	12 strips/rack, 10 racks/pack 5 packs/case
MTS-11-8-C-R-S	1.1ml	Mini Tube, 8-strip*	12 strips/rack, 10 racks/pack 5 packs/case
MTS-11-8-C	1.1ml	Mini Tube, 8-strip	120 strips/bag, 5 bags/case
MTS-11-12-C-R	1.1ml	Mini Tube, 12-strip	8 strips/rack, 10 racks/pack 5 packs/case
MTS-11-12-C-R-S	1.1ml	Mini Tube, 12-strip*	8 strips/rack, 10 racks/pack 5 packs/case
MTS-11-12-C	1.1ml	Mini Tube, 12-strip	80 strips/bag, 5 bags/case
MTS-06-C-R	0.65ml	Mini Tube, Single	96/rack, 10 racks/pack, 5 packs/case
MTS-06-C-R-S	0.65ml	Mini Tube, Single*	96/rack, 10 racks/pack, 5 packs/case
MTS-06-C	0.65ml	Mini Tube, Single	960 tubes/bag, 5 bags/case
MTS-8CP-C	-	Mini Tube Cap, 8-strip	120 strips/pack, 5 packs/case
MTS-8CP-C-S	-	Mini Tube Cap, 8-strip	120 strips/pack, 5 packs/case
MTS-12CP-C	-	Mini Tube Cap, 12-strip	80 strips/pack, 5 packs/case
MTS-12CP-C-S	-	Mini Tube Cap, 12-strip*	80 strips/pack, 5 packs/case

Technical drawing of a rectangular container. The top view shows a rectangle with dimensions 1000 mm (width) and 600 mm (depth). The side view shows a cross-section with a height of 100 mm. The drawing includes a grid pattern on the top surface and a cross-section of the container wall.

Thermoplastics Chemical and Physical Properties

Resistance rating on a scale from A (excellent) to D (poor)

Chemical	% Conc.	Resistance at 20°C	Resistance at 60°C	Chemical	% Conc.	Resistance at 20°C	Resistance at 60°C
Acetic acid (glacial)	97	A	B	Dimethyl acetamide	100	A	A
Acetic anhydride		B	B	Dimethylsulfoxide (DMSO)		A	A
Acetaldehyde		B	D	Ethyl acetate		B	C
Acetone	100	A	B	Ethyl alcohol	96	A	B
Acetonitrile		C	D	Ethyl benzene	40	C	D
Acetophenone	100	B	B	Ethyl chloride		B	D
Adipic acid		A	A	Ethylene chloride		C	D
Aluminum chloride		A	A	Ethylene dichloride		B	C
Ammonia (aqueous)	30	A	A	Ethylene glycol	100	B	N/A
Ammonium acetate	satd.	A	A	Formaldehyde	40	A	A
Ammonium carbonate	satd.	A	A	Formic acid	100	A	B
Ammonium chloride	satd.	A	A	Glutaraldehyde	20	A	A
Ammonium fluoride	20	A	A	Hexane		C	C
Ammonium hydroxide	10	A	A	Hydrobromic acid		D	D
Ammonium nitrate	satd.	A	A	Hydrochloric acid	50	B	C
Ammonium sulfate	satd.	A	A	Hydrofluoric acid	40	A	B
Ammonium sulfide	satd.	A	A	Hydrogen peroxide	10	A	A
Amyl acetate	100	C	D	Hydrogen sulfide	3	A	A
Amyl alcohol	100	A	B	Lactic acid		B	C
Amyl chloride	100	D	D	Magnesium chloride	satd.	A	A
Aniline	100	B	B	Magnesium sulfate	satd.	A	A
Aromatic hydrocarbons		D	D	Methyl acetate		D	D
Benzaldehyde		D	D	Methyl alcohol	10	B	C
Benzene		D	D	Methylene chloride	100	D	D
Benzoic acid	100	B	C	Methyl ethyl ketone	100	D	D
Benzl acetate	satd.	A	B	Methyl propyl ketone		B	C
Benzyl alcohol		A	A	Nitric acid	satd.	D	D
Boric acid		A	A	Nitrobenzene		B	C
Bromobenzene		C	D	Perchloroethylene		D	D
Butadiene		C	D	Phenol	95+	B	D
Butyl acetate		C	D	Phosphoric acid	100	C	D
Butyl alcohol	100	C	D	Potassium bromide		A	B
Butyric acid		C	D	Potassium chloride	satd.	A	A
Calcium chloride	satd.	A	A	Potassium fluoride	satd.	A	A
Calcium hypochlorite bleach		A	A	Potassium hydroxide		A	A
Carbon disulfide		A	A	Propionic acid		A	B
Carbon Tetrachloride		D	D	Propyl alcohol		A	B
Carbonic acid	100	C	D	Propylene glycol		A	A
Chloroacetic acid	100	D	D	Silicone oil		A	A
Chlorobenzene		C	D	Sodium acetate	100	A	A
Chloroform	100	D	D	Sodium carbonate	satd.	A	A
Chlorosulfonic acid	100	C	D	Sodium chloride		A	A
Chromic acid	50	D	D	Sodium hydroxide	satd.	A	A
Citric acid		D	D	Sodium hypochlorite	satd.	B	B
Cyclohexane	satd.	D	D	Sulfuric acid	satd.	C	D
Cyclohexanol		C	D	Sulfuric acid	98	C	D
Decalin		C	D	Tetralin	10	C	D
Detergents		A	A	Toluene	100	C	C
Dibutyl phthalate		A	B	Trichloroethane	100	B	C
Dichlorobenzene		C	D	Triethylene glycol		D	D
Dichloroethylene		D	D	Trifluoroacetic acid (TFA) 20%		B	C
Diethyl benzene	100	C	D	Xylene	100	C	D
Diethyl ether		B	C	Zinc chloride		A	A
Diethylene glycol		B	D	Zinc sulfate		A	A

The above chemical resistance chart is meant to be used as a guide only. As temperature, exposure time and functional conditions affect resistance and can vary for each application, Axgyen Scientific highly recommends users to evaluate products under their own conditions prior to use. Axgyen does not warrant (neither expressed or implied) that the information in this chart is accurate or that any material is suitable for any purpose.

Maximum RCF (G-force)

PCR Tubes

PCR-02, PCR-02D, PCR-05, PCR-0208

4,000 RCF

PCR Plates

PCR-24, PCR-32, PCR-48, PCR-96, PCR-96-MB, PCR-96-FLT, PCR-96-LP-FLT,
PCR-96-SG, PCR-96-AB, PCR-96-LP-AB, PCR-96M2-HS, PCR-96-FS, PCR-384,
PCR-384M2, PCR-384-RGD, PCR-384-55

4,000 RCF

Assay & Deep well Plates

P-384-120SQ, P-384-240SQ, P-DW-11, P-DW-20, P-DW-500,
P-2ML-SQ, P-5ML-48, P-96-450R, P-96-450V

4,000 RCF

Microcentrifuge Tubes

MCT-060, MCT-175, MCT-150, MCT-200

14,000* - 20,000 RCF

Screw Cap Tubes

SCT-050, SCT-050-SS, SCT-150, SCT-150-SS,
SCT-200, SCT-200-SS, SCT-45

20,000 RCF

Products filled with distilled water and spun at 20°C for 20 minutes with properly supportive rotor inserts. Your results may vary depending on sample type and volume.

* These products are rated to 14,000 RCF with phenol/chloroform

RPM vs. RCF “What’s the Difference?”

RPM – stands for “Revolutions Per Minute” and is the speed that your rotor spins in your centrifuge. RPM is specific to individual centrifuge brands and rotor sizes.

RCF – stands for “Relative Centrifugal Force” and is better known as g-force. This indicates the actual force resulting from the spinning action in the centrifuge. It is g-force that drives sample separation.

The following equation can be used to convert RPM to RCF for any model centrifuge.

$$\text{RCF} = 0.00001118 \times \text{radius of rotation (cm)} \times \text{RPM}^2$$

Note: radius of rotation is given by the distance of the furthest most point of the tube from the axis of rotation. Please refer to your centrifuge user guide for radius value.

Autoclaving Guideline for Plastics

To ensure successful steam sterilization of your plastic labware please adhere to the following guideline: Autoclave all plastic consumables at 121°C for 15 minutes, 15psi/1 atm. Do not use a dry cycle as this may cause deformation or weakening of the plastic. Allow temperature within the autoclave to return to at least 80°C before removing product.

Light Blocking Ability of Axygen Amber Microtubes

A comparison between the light blocking ability of Axygen’s amber microtubes and an industry competitor’s. Sample tubes were split in half lengthwise to obtain suitable surface area and then placed in a spectrophotometer. Various wavelengths of light were shown through the samples and % transmission of light determined.

Wavelength (nm)	Axygen Amber Microtubes	Competitor Amber Microtubes
1000nm	25.71	90.16
800nm	17.87	83.71
600nm	1.66	48.97
400nm	0.80	44.70
310nm	0.21	42.57

Testing shows significant light blocking ability of the Axygen amber microtubes, thus providing excellent protection for light sensitive samples.

From Engineering to packaging quality in everything we do

Confidence and trust are paramount to the relationship between Axygen and our customers. We believe our manufacturing and quality procedures are second-to-none. We are proud to share these standards and procedures with you to help support this relationship.

Each and every lot of product, regardless of packaging format, both sterile and non-sterile, is tested and certified by Axygen's modern microbiology laboratory. Completely equipped with the latest instruments and technology from the most trusted manufacturers, this facility, was the first of its kind in our industry. This experience, combined with an uncompromising commitment to quality, ensures that Axygen applies the most stringent testing standards to certify products to be safe from RNase, DNase and endotoxin (pyrogens). Axygen maintains a validated sterilization program and certifies sterile products to have an SAL of 10^{-6} .

In addition to being ISO 9001:2000 compliant, our operations also conform to specifications for FDA CFR Title 21-820, ISO-13485:1996 and ISO-17025:1999. Manufacturing utilizes "clean techniques" in sealed, positive over-pressure, clean areas. Axygen products can be used as "raw materials" in the production of or in the manufacture of a GMP class certified product and/or one that qualifies as USP Class IV or VI. Resins used by Axygen Scientific are compliant with FDA CFR Title 21 177.1520, 178.3295, 178.3297 and ISO 10993-3 to ensure that they are not harmful to cells or tissue samples. All resins used by Axygen must pass the requirements outlined in the United States Pharmacopoeia "Heavy Metals as Lead - Physicochemical Testing for Plastics" to demonstrate absence of trace metals, USP Method #3127.

We make available to our customers lot-specific Certificates of Compliance. We also have available, for your perusal, copies of all of our quality standards, procedures, inspection forms and various other documentation, should you wish to see them. We welcome both formal and informal site visits and audits. For more information contact our Customer Service Department at 1.800.4-AXYGEN (US and Canada), +1-510-494-8900 (International) or sales@axxygen.com. Certificates of Compliance can also be downloaded and printed directly from our website, www.axxygen.com.

Competence, compliance, completeness... confidence!

Volume to Brim =
maximum volume of fluid that can be placed in each well without spilling out.

Working Volume =
the comfortable working volume of each well of the plate.

Volume with (VR) Axyamat =
the volume that can be placed in each well, without fluid touching the corresponding Axyamat when sealed.

Plate Brim of Well	Volume to Volume	Working with Axyamat	Volume VR Axyamat	Volume with
PCR-384-C	50µl	40µl	30µl	6.5µl
PCR-384M2-C	55µl	50µl	40µl	6.5µl
PCR-384-RGD-C	50µl	49.5µl	30µl	6.5µl
PCR-384-55-C	55µl	50µl	45µl	10.5µl
PCR-96-C	340µl	300µl	250µl	-
PCR-96-MB-C	340µl	300µl	250µl	-
PCR-96-FLT-C	340µl	300µl	220µl	-
PCR-96-LP-FLT-C	220µl	200µl	106µl	-
PCR-96-SG-C	320µl	280µl	240µl	-
PCR-96-AB-C	335µl	300µl	260µl	-
PCR-96-LP-AB-C	240µl	200µl	140µl	-
PCR-96M2-HS-C	340µl	300µl	240µl	-
PCR-96-F5-C	240µl	200µl	140µl	-
P-384-120SQ	130µl	120µl	90µl	-
P-384-240SQ	250µl	240µl	210µl	-
P-96-450R-C	550µl	500µl	350µl	-
P-96-450V-C	520µl	480µl	300µl	-
P-DW-500	620µl	560µl	440µl	-
P-DW-11	1.17ml	1.09ml	1.01ml	-
P-DW-20	1.74ml	1.64ml	1.56ml	-
P-DW-20-SQ	2.39ml	2.20ml	2.04ml	-
P-5ML-48-C	4.9ml	4.6ml	4.0ml	-

Unit Conversion Reference Table

Unit	Symbol	Equivalent
nanoliter	nl	1 nl = 10^{-9} L
microliter	µl	1 µl = 10^{-6} L
milliliter	ml	1 ml = 10^{-3} L
picogram	pg	1 pg = 10^{-12} g
nanogram	ng	1 ng = 10^{-9} g
microgram	µg	1 µg = 10^{-6} g
milligram	mg	1 mg = 10^{-3} g
kilogram	kg	1 kg = 10^3 g

Fisher Scientific Catalogue Numbers

Axygen Cat No	UK 	Germany 	France 	Spain 	Page No
AC-PE-B	AXY-110-005A	3221245	.997E1	.6801T	36
AC-PE-BK	AXY-110-010H	3221246	.997E2	.6801W	36
AC-PE-C	AXY-110-015U	3221247	.997E3	.6801X	36
AC-PE-G	AXY-110-020E	3221248	.997E4	.6801Y	36
AC-PE-GR	AXY-110-025R	3221249	.997E5	.68020	36
AC-PE-L	AXY-110-030B	3221250	.997E6	.68021	36
AC-PE-R	AXY-110-035X	3221251	.997E7	.68022	36
AC-PE-Y	AXY-110-040V	3221252	.996TN	.68023	36
AM-2ML-RD	AXY-115-005Q	3221253	.995KT	.6768T	64, 65
AM-2ML-RD-IMP	AXY-115-010A	3221254	.995KW	.6771D	64, 65
AM-2ML-SQ	AXY-115-020U	3221256	.995KY	.6771F	64
AM-2ML-SQ-IMP	AXY-115-025K	3221257	.995LO	.6771H	64
AM-384-DW-SQ	AXY-115-040X	3221260	.995L3	.6771L	63
AM-384-PCR-RD	AXY-115-045E	3221261	.995L4	.6771M	20, 21, 63
AM-384-PCR-RV	AXY-115-050L	3221262	.995L5	.6771N	20, 21, 63
AM-384-SQ-IMP	AXY-115-055B	3221263	.995L6	.6771P	63
AM-48-IMP	AXY-115-060Y	3221264	.995L7	.6771R	65
AM-500UL-RD	AXY-115-065V	3221265	.995L8	.6771T	64
AM-96-PCR-RD	AXY-115-080C	3221268	.995LA	.6768W	16, 17, 18, 19
AM-96-SEPTA-3100	AXY-115-085P	3221269	.995LB	.6768X	22
AM-SEPTA-310	AXY-115-090W	3221270	.997AE	.6778F	22
AS-13MM-B	AXY-130-005J	3221291	.997E9	.68024	36
AS-13MM-BK	AXY-130-010Q	3221292	.997EA	.68025	36
AS-13MM-G	AXY-130-015G	3221293	.997EB	.68026	36
AS-13MM-GR	AXY-130-020N	3221294	.997EC	.68027	36
AS-13MM-L	AXY-130-025D	3221295	.997ED	.68028	36
AS-13MM-R	AXY-130-030K	3221296	.997EE	.68029	36
AS-13MM-W	AXY-130-035A	3221297	.997EF	.6802A	36
AS-13MM-Y	AXY-130-040H	3221298	.997EH	.6802B	36
AS-16MM-B	AXY-130-045U	3221299	.997EK	.6802C	36
AS-16MM-BK	AXY-130-050E	3221300	.997EL	.6802D	36
AS-16MM-G	AXY-130-055R	3221301	.997EM	.6802E	36
AS-16MM-GR	AXY-130-060B	3221302	.997EN	.6802F	36
AS-16MM-L	AXY-130-065X	3221303	.997EP	.6802H	36
AS-16MM-R	AXY-130-070V	3221304	.997ER	.6802K	36
AS-16MM-W	AXY-130-075L	3221305	.997ET	.6802L	36
AS-16MM-Y	AXY-130-080S	3221306	.997EW	.6802M	36
BF-400	AXY-135-005C	3221307	.995N3	.6779M	22
BF-400-S	AXY-135-010J	3221308	.995LC	.67783	22
BT-1000-R	AXY-140-005C	3221309	.995MT	.67787	42
BT-20-R	AXY-140-030D	3221314	.996F0	.6789C	42
BT-20-R-S	AXY-140-035Q	3221315	.996F1	.6789D	42
BT-250-R	AXY-140-055K	3221319	.996F4	.6789H	42
BT-250-R-S	AXY-140-060R	3221320	.996F5	.6789K	42
BT-255-WB-R	AXY-140-065H	3221321	.996F6	BT-255-WB-R	42
BT-255-WB-R-S	AXY-140-070X	3221322	.996F7	BT-255-WB-R-S	42
BT-50-R	AXY-140-095V	3221327	.996FA	.6789N	42
BT-50-R-S	AXY-140-100Y	3221328	.996FB	.6789P	42
BTF-1000-R-S	AXY-140-105V	3221329	.995MX	.67789	42
BTF-165-WB-R-S	AXY-140-110F	3221330	.996FC	.6789R	42
BTF-180-R-S	AXY-140-120C	3221332	.996FE	.6789W	42
CTF-199-R-S	AXY-140-140T	3221340	.996FL	CTF-199-R-S	50
EV-100-R	AXY-140-145J	3221341	.996FM	EV-100-R	48, 55, 57, 58
EV-100-R-S	AXY-140-155G	3221343	.996FP	EV-100-R-S	48, 55, 57, 58
EV-200-R	AXY-140-160N	3221344	.996FR	EV-200-R	48, 55, 57, 58
EV-200-R-S	AXY-140-170K	3221346	.996FW	EV-200-R-S	48, 55, 57, 58
EV-205-WB-R	AXY-140-175A	3221347	.996FX	EV-205-WB-R	48, 55, 57, 58

Axygen Cat No	UK 	Germany 	France 	Spain 	Page No
EV-205-WB-R-S	AXY-140-180H	3221348	.996FY	EV-205-WB-R-S	48, 55, 57, 58
EV-50-R	AXY-140-185U	3221349	.996H0	EV-50-R	48, 55, 57, 58
EV-50-R-S	AXY-140-190E	3221350	.996H1	EV-50-R-S	48, 55, 57, 58
EVF-100-R-S	AXY-145-005S	3221351	.996H2	EVF-100-R-S	48, 55, 57, 58
EVF-180-R-S	AXY-145-010C	3221352	.996H3	EVF-180-R-S	48, 55, 57, 58
EVF-205-WB-R-S	AXY-145-015P	3221353	.996H4	EVF-205-WB-R-S	48, 55, 57, 58
EVF-50-R-S	AXY-145-020W	3221354	.996H5	EVF-50-R-S	48, 55, 57, 58
FPT-384-R	AXY-140-200E	3221356	.997AM	.6805F	.7
FPT-384-R-S	AXY-140-205R	3221357	.997AN	.6805H	.7
FX-10-R	AXY-140-210B	3221358	.996H6	.67909	.40
FX-10-R-S	AXY-140-215X	3221359	.996H7	.6790A	.40
FX-1536-30FP-R	AXY-140-220V	3221360	.997AP	.6805K	.39
FX-1536-30FP-R-S	AXY-140-225L	3221361	.997AR	FX-1536-30FP-R-S	.39
FX-20-L-R	AXY-140-230S	3221362	.996H8	.6790B	.40
FX-20-L-R-S	AXY-140-235Y	3221363	.996H9	.6790C	.40
FX-20-R	AXY-140-240P	3221364	.996HA	.6790D	.40
FX-20-R-S	AXY-140-245F	3221365	.996HB	.6790E	.40
FX-250-L-R	AXY-140-250M	3221366	.996HC	.6790F	.40
FX-250-L-R-S	AXY-140-255C	3221367	.996HD	.6790H	.40
FX-250-R	AXY-140-260J	3221368	.996HE	.6790K	.40
FX-250-R-S	AXY-140-265W	3221369	.996HF	.6790L	.40
FX-255-WB-R	AXY-140-270G	3221370	.996HH	.6790M	.40
FX-255-WB-R-S	AXY-140-275T	3221371	.996HK	.6790N	.40
FX-384-L-R	AXY-140-290A	3221374	.997AX	.6805R	.59, 60
FX-384-L-R-S	AXY-140-295N	3221375	.997AY	.6805T	.59, 60
FX-384-R	AXY-140-300A	3221376	.997B0	.6805W	.39, 59, 60
FX-384-R-S	AXY-140-305N	3221377	.997B1	.6805X	.39, 59, 60
FX-384-XL-L-R	AXY-140-310U	3221378	.997B2	.6805Y	.39, 59, 60
FX-384-XL-L-R-S	AXY-140-315K	3221379	.997B3	.68060	.39, 59, 60
FX-384-XL-R	AXY-140-320R	3221380	.997B4	.68061	.39, 59, 60
FX-384-XL-R-S	AXY-140-325H	3221381	.997B5	.68062	.39, 59, 60
FX-50-L-R	AXY-140-330X	3221382	.996HL	.6790P	.40
FX-50-L-R-S	AXY-140-335E	3221383	.996HM	.6790R	.40
FX-50-R	AXY-140-340L	3221384	.996HN	.6790T	.40
FX-50-R-S	AXY-140-345B	3221385	.996HP	.6790W	.40
FXF-10-R-S	AXY-145-025M	3221386	.996HR	.6790X	.40
FXF-165-WB-R-S	AXY-145-030T	3221387	.996HT	FXF-165-WB-R-S	.40
FXF-180-L-R-S	AXY-145-035J	3221388	.996HW	.6790Y	.40
FXF-180-R-S	AXY-145-040Q	3221389	.996HX	.67910	.40
FXF-200-R-S	AXY-145-045G	3221390	.996HY	FXF-200-R-S	.40
FXF-20-L-R-S	AXY-145-050N	3221391	.996K0	.67911	.40
FXF-20-R-S	AXY-145-055D	3221392	.996K1	.67912	.40
FXF-384-L-R-S	AXY-145-065A	3221394	.997B7	.68065	.39, 59, 60
FXF-384-R-S	AXY-145-070H	3221395	.997B8	.68066	.39, 59, 60
FXF-384-XL-L-R-S	AXY-145-075U	3221396	.997B9	.68067	.39, 59, 60
FXF-384-XL-R-S	AXY-145-080E	3221397	.997BA	.68068	.39, 59, 60
FXF-50-L-R-S	AXY-145-085R	3221398	.996K2	.67915	.40
FXF-50-R-S	AXY-145-090B	3221399	.996K3	.6791A	.40
MCT-060-A	AXY-150-005S	3221412	.996TP	.6802Y	.28
MCT-060-B	AXY-150-010C	3221413	.996TR	.68030	.28
MCT-060-C	AXY-150-015P	3221134	.996TT	.6779N	.28
MCT-060-C-S	AXY-150-020W	3221414	.995RY	.6779P	.29
MCT-060-G	AXY-150-025M	3221415	.996TW	.68031	.28
MCT-060-L-C	AXY-150-030T	3221416	.995T0	.6799M	.29
MCT-060-O	AXY-150-035J	3221417	.996TX	.68032	.28
MCT-060-R	AXY-150-040Q	3221418	.996TY	.68033	.28
MCT-060-SP	AXY-150-045G	3221419	.996W0	.68034	.29
MCT-060-V	AXY-150-050N	3221420	.996W1	.68035	.28

Axygen Cat No	UK 	Germany 	France 	Spain 	Page No
MCT-060-X	.AXY-150-055D	3221421	.996W2	.68036	28
MCT-060-Y	.AXY-150-060K	3221422	.996W3	.68037	28
MCT-150-A	.AXY-150-065A	3221423	.995T1	.6778H	28
MCT-150-B	.AXY-150-070H	3221424	.995T2	.6799N	28
MCT-150-C	.AXY-150-075U	3221135	.995T3	.6778K	28
MCT-150-C-S	.AXY-150-080E	3221136	.995RC	.67785	29
MCT-150-G	.AXY-150-085R	3221425	.995T4	.6799P	28
MCT-150-L-C	.AXY-150-090B	3221137	.995RD	.67825	29
MCT-150-NC	.AXY-150-095X	3221426	.995T5	.6778L	29
MCT-150-O	.AXY-150-100B	3221427	.995T6	.6799R	28
MCT-150-R	.AXY-150-105X	3221428	.995T7	.6799T	28
MCT-150-SP	.AXY-150-110V	3221429	.995T8	.6799W	29
MCT-150-V	.AXY-150-115L	3221430	.995T9	.6799X	28
MCT-150-X	.AXY-150-120S	3221431	.995TA	.6799Y	28
MCT-150-Y	.AXY-150-125Y	3221432	.995TB	.68006	28
MCT-175-A	.AXY-150-130P	3221433	.995TC	.68007	28
MCT-175-B	.AXY-150-135F	3221434	.995TD	.68008	28
MCT-175-C	.AXY-150-140M	3221138	.995TE	.6778M	28
MCT-175-C-S	.AXY-150-145C	3221435	.995RE	.67826	29
MCT-175-G	.AXY-150-150J	3221436	.995TF	.68009	28
MCT-175-L-C	.AXY-150-155W	3221139	.995RF	.67827	29
MCT-175-O	.AXY-150-160G	3221437	.995TH	.6800A	28
MCT-175-R	.AXY-150-165T	3221438	.995TK	.6800B	28
MCT-175-SP	.AXY-150-170D	3221439	.995TL	.6800C	29
MCT-175-V	.AXY-150-175Q	3221440	.995TM	.6800D	28
MCT-175-X	.AXY-150-180A	3221441	.995TN	.6800E	28
MCT-175-Y	.AXY-150-185N	3221442	.995TP	.6800F	28
MCT-200-A	.AXY-150-190U	3221443	.995TR	.6800H	28
MCT-200-B	.AXY-150-195K	3221444	.995TT	.6800K	28
MCT-200-C	.AXY-150-200U	3221140	.995TW	.6778N	28
MCT-200-C-S	.AXY-150-205K	3221445	.995RH	.67786	29
MCT-200-G	.AXY-150-210R	3221446	.995TX	.6800L	28
MCT-200-L-C	.AXY-150-215H	3221447	.995RK	.67828	29
MCT-200-NC	.AXY-150-220X	3221448	.995TY	.6800M	29
MCT-200-O	.AXY-150-225E	3221449	.995W0	.6800N	28
MCT-200-R	.AXY-150-230L	3221450	.995W1	.6800P	28
MCT-200-SP	.AXY-150-235B	3221451	.995W2	.6800R	29
MCT-200-V	.AXY-150-240Y	3221452	.995W3	.6800T	28
MCT-200-X	.AXY-150-245V	3221453	.995W4	.6800W	28
MCT-200-Y	.AXY-150-250F	3221454	.995W5	.6800X	28
MF-111	.AXY-115-155U	3221455	.995N4	.6779R	22
MF-300	.AXY-115-160E	3221456	.995N5	.67772	22
MT-200-R	.AXY-140-390J	3221463	.996K7	.6791D	43
MT-200-R-S	.AXY-140-395L	3221464	.996K8	.6791E	43
MTF-200-R-S	.AXY-145-095X	3221469	.996KD	.6791M	43
MTS-06-C	.AXY-155-005L	3221472	.997CM	.6779C	68
MTS-06-C-R	.AXY-155-010S	3221473	.996KH	.6791T	68
MTS-06-C-R-S	.AXY-155-015Y	3221474	.996KK	.6791W	68
MTS-11-12-C	.AXY-155-020P	3221475	.995RM	.6778A	68
MTS-11-12-C-R	.AXY-155-025F	3221476	.995MY	.6778B	68
MTS-11-12-C-R-S	.AXY-155-030M	3221477	.996KL	.6778C	68
MTS-11-8-C	.AXY-155-035C	3221478	.996ER	.67797	68
MTS-11-8-C-R	.AXY-155-040J	3221479	.995P6	.67798	68
MTS-11-8-C-R-S	.AXY-155-045W	3221480	.995P7	.67799	68
MTS-11-C	.AXY-155-050G	3221481	.997CN	.6791X	68
MTS-11-C-R	.AXY-155-055T	3221482	.996KM	.6791Y	68
MTS-11-C-R-S	.AXY-155-060D	3221483	.996KN	.67924	68

Axygen Cat No	UK 	Germany 	France 	Spain 	Page No
MTS-12CP-C	AXY-160-005L	3221485	995RN	6778D	68
MTS-12CP-C-S	AXY-160-010S	3221486	995RP	6778E	68
MTS-8CP-C	AXY-160-015Y	3221487	996ET	6779A	68
MTS-8CP-C-S	AXY-160-020P	3221488	996EW	6779B	68
MTX-1250-C	AXY-140-420N	3221489	997DD	6800Y	6
MTX-1250-C-L	AXY-140-425D	3221490	997DE	68010	6
MTX-1250-C-L-R	AXY-140-430K	3221491	996Y0	6782D	6
MTX-1250-C-L-R-S	AXY-140-435A	3221492	996Y1	6782E	6
MTX-1250-C-R	AXY-140-440H	3221493	996Y2	6782F	6
MTX-1250-C-R-S	AXY-140-445U	3221494	996Y3	6782H	6
MTXF-1250-C-L-R-S	AXY-145-110V	3221495	996Y4	MTXF-1250-C-L-R-S	6
MTXF-1250-C-R-S	AXY-145-115L	3221496	996Y5	6782L	6
P-1ML-SQ-C	AXY-165-005A	3221503	995LK	P-1ML-SQ-C	64
P-2ML-SQ-C	AXY-165-015B	3221505	995F9	6769D	64
P-2ML-SQ-C-S	AXY-165-020Y	3221506	995FA	6769E	64
P-384-120SQ-C	AXY-165-030F	3221508	995LL	67725	63
P-384-240SQ-C	AXY-165-045P	3221511	995LP	6772A	63
P-5ML-48-C	AXY-165-060T	3221514	995FC	6769F	65
P-5ML-48-C-S	AXY-165-065J	3221515	995FD	6769H	65
P-96-450R-C	AXY-170-015B	3221518	995LY	6772H	65
P-96-450R-C-S	AXY-170-025V	3221520	995M0	6772K	65
P-96-450V-C	AXY-170-060T	3221527	995M7	6772W	65
P-ADAPTER-1	AXY-170-095A	3221534	995BT	6768P	65
PCR-0208-C	AXY-175-020B	3221141	995PA	6768R	24
PCR-0208-CP-C	AXY-175-030V	3221142	995PB	6779X	24
PCR-0208-FCP-C	AXY-175-035L	3221539	995PC	68039	24
PCR-02-A	AXY-175-075W	3221547	996W4	6779Y	23
PCR-02-B	AXY-175-080G	3221548	996W5	6803H	23
PCR-02-C	AXY-175-085T	3221143	996W6	67800	23
PCR-02CP-C	AXY-180-015R	3221144	995PN	67801	24
PCR-02D-A	AXY-175-090D	3221556	996W7	6803W	23
PCR-02D-B	AXY-175-095Q	3221557	996W8	6803X	23
PCR-02D-C	AXY-175-100D	3221145	996W9	67802	23
PCR-02D-G	AXY-175-105Q	3221558	996WA	6803Y	23
PCR-02D-L-C	AXY-175-110A	3221559	996WB	68040	23
PCR-02D-O	AXY-175-115N	3221560	996WC	68041	23
PCR-02D-R	AXY-175-120U	3221561	996WD	68042	23
PCR-02D-SP	AXY-175-125K	3221562	996WE	68043	23
PCR-02D-V	AXY-175-130R	3221563	996WF	68044	23
PCR-02D-Y	AXY-175-135H	3221564	996WH	68045	23
PCR-02-FCP-C	AXY-175-140X	3221565	995PY	68046	24
PCR-02-G	AXY-175-145E	3221566	996WK	68047	23
PCR-02-L-C	AXY-175-150L	3221567	996WL	68048	23
PCR-02-NC	AXY-175-160Y	3221569	996WM	67803	23
PCR-02-O	AXY-175-165V	3221570	996WN	68049	23
PCR-02-R	AXY-175-170F	3221571	996WP	6804A	23
PCR-02-SP	AXY-175-175S	3221572	996WR	6804B	24
PCR-02-V	AXY-175-180C	3221573	996WT	6804C	23
PCR-02-Y	AXY-175-185P	3221574	996WW	6804D	23
PCR-05-A	AXY-175-190W	3221575	996WX	6804E	23
PCR-05-B	AXY-175-195M	3221576	996WY	6804F	23
PCR-05-C	AXY-175-200W	3221146	996X0	67804	23
PCR-05-G	AXY-175-205M	3221577	996X1	6804H	23
PCR-05-O	AXY-175-215J	3221579	996X3	6804L	23
PCR-05-R	AXY-175-220Q	3221580	996X4	6804M	23
PCR-05-V	AXY-175-230N	3221582	996X6	6804N	23
PCR-05-Y	AXY-175-240K	3221584	996X8	6804P	23

Axygen Cat No	UK 	Germany 	France 	Spain 	Page No
PCR-2CP-RT-C	.AXY-180-045Y	.3221588	.995R0	.67805	.24
PCR-384-55-C	.AXY-185-020R	.3221590	.995C1	.6773R	.21
PCR-384-C	.AXY-185-035E	.3221593	.995C4	.67744	.20
PCR-384-LC480-W	.AXY-185-050Y	.3221596	.995C7	.PCR-384-LC480-W	.20
PCR-384-LC480-W-BC	.AXY-185-055V	.3221597	.995C8	.PCR-384-LC480-W-BC	.20
PCR-384-LC480-W-NF	.AXY-185-060F	.3221598	.995C9	.PCR-384-LC480-W-NF	.20
PCR-384M2-C	.AXY-185-075P	.3221601	.995CC	.6774A	.20
PCR-384-RGD-C	.AXY-185-135A	.3221613	.995F5	.67775	.21
PCR-96-AB-C	.AXY-185-165X	.3221147	.995D0	.67694	.18
PCR-96-C	.AXY-185-185Y	.3221148	.995D4	.67695	.16
PCR-96-FLT-BK	.AXY-185-255N	.3221635	.995FE	.67778	.16
PCR-96-FLT-C	.AXY-185-260U	.3221149	.995FF	.67779	.16
PCR-96-FLT-W	.AXY-185-265K	.3221636	.995FH	.6777A	.16
PCR-96-FS-C	.AXY-185-285E	.3221150	.995DP	.67696	.19
PCR-96-LC480-W	.AXY-185-330C	.3221648	.995E3	.PCR-96-LC480-W	.19
PCR-96-LC480-W-BC	.AXY-185-335P	.3221151	.995E4	.PCR-96-LC480-W-BC	.19
PCR-96-LC480-W-NF	.AXY-185-340W	.3221649	.995E5	.PCR-96-LC480-W-NF	.19
PCR-96-LP-AB-BK	.AXY-185-345M	.3221650	.995FK	.6777B	.18
PCR-96-LP-AB-C	.AXY-185-350T	.3221651	.995FL	.6777C	.18
PCR-96-LP-AB-W	.AXY-185-355J	.3221652	.995FM	.6777D	.18
PCR-96-LP-FLT-BK	.AXY-185-360Q	.3221653	.995FN	.6777E	.17
PCR-96-LP-FLT-C	.AXY-185-365G	.3221654	.995FP	.6777F	.17
PCR-96-LP-FLT-W	.AXY-185-370N	.3221655	.995FR	.6777H	.17
PCR-96M2-HS-C	.AXY-185-390H	.3221152	.995E9	.67697	.19
PCR-96-MB-C	.AXY-185-430V	.3221666	.995EK	.67761	.16
PCR-96-SG-C	.AXY-185-445Y	.3221153	.995EN	.67698	.17
PCR-AS-200	.AXY-135-015W	.3221671	.995N7	.6777L	.22
PCR-AS-600	.AXY-135-020G	.3221672	.995N8	.67806	.22
PCR-TS	.AXY-135-040A	.3221676	.995NB	.6777R	.22
PCR-TS-900	.AXY-135-045N	.3221677	.995MD	.6778P	.22
P-DW-10ML-24-C	.AXY-165-070Q	.3221678	.995FT	.6769K	.65
P-DW-11-C	.AXY-165-085D	.3221154	.995ME	.6776R	.64
P-DW-11-C-S	.AXY-165-090K	.3221681	.995MF	.6776T	.64
P-DW-20-C	.AXY-165-095A	.3221155	.995MH	.6776W	.64
P-DW-20-C-S	.AXY-165-105A	.3221683	.995ML	.6776X	.64
P-DW-500-C	.AXY-165-115U	.3221685	.995MM	.6776Y	.64
P-DW-500-C-S	.AXY-165-120E	.3221686	.995MN	.67770	.64
PES-15-B-SI	.AXY-165-130B	.3221688	.995NC	.PES-15-B-SI	.29
PK-200-L-R	.AXY-140-480S	.3221689	.996L0	.6792A	.51
PK-200-L-R-S	.AXY-140-485Y	.3221690	.996L1	.6792B	.51
PK-200-R	.AXY-140-490P	.3221691	.996L2	.6792C	.51
PK-200-R-S	.AXY-140-495F	.3221692	.996L3	.6792D	.51
PK-205-WB-R	.AXY-140-500P	.3221693	.996L4	.6792E	.51
PK-205-WB-R-S	.AXY-140-505F	.3221694	.996L5	.6792F	.51
PK-20-L-R	.AXY-140-510M	.3221695	.996L6	.6792H	.51
PK-20-L-R-S	.AXY-140-515C	.3221696	.996L7	.6792K	.51
PK-20-R	.AXY-140-520J	.3221697	.996L8	.6792L	.51
PK-20-R-S	.AXY-140-525W	.3221698	.996L9	.6792M	.51
PK-384-R	.AXY-140-530G	.3221699	.997BE	.6806C	.51
PK-384-R-S	.AXY-140-535T	.3221700	.997BF	.6806D	.51
PK-50-L-R	.AXY-140-540D	.3221701	.996LA	.6792N	.51
PK-50-L-R-S	.AXY-140-545Q	.3221702	.996LB	.6792P	.51
PK-50-R	.AXY-140-550A	.3221703	.996LC	.6792R	.51
PK-50-R-S	.AXY-140-555N	.3221704	.996LD	.6792T	.51
PKF-180-L-R-S	.AXY-145-120S	.3221705	.996LE	.6792W	.51
PKF-180-R-S	.AXY-145-125Y	.3221706	.996LF	.6792X	.51
PKF-205-WB-R-S	.AXY-145-130P	.3221707	.996LH	.6792Y	.51

Axygen Cat No	UK 	Germany 	France 	Spain 	Page No
PKF-20-L-R-S	AXY-145-135F	3221708	.996LK	.67930	.51
PKF-20-R-S	AXY-145-140M	3221709	.996LL	.67932	.51
PKF-30-L-R-S	AXY-145-145C	3221710	.996LM	.67933	.51
PKF-30-R-S	AXY-145-150J	3221711	.996LN	.67934	.51
PKF-384-R-S	AXY-145-155W	3221712	.997BH	PKF-384-R-S	.51
QT-1100-CBK-R	AXY-140-560U	3221718	.996LP	QT-1100-CBK-R	.56
QT-1100-CBK-R-S	AXY-140-565K	3221719	.996LR	QT-1100-CBK-R-S	.56
R-480-A	AXY-150-260C	3221722	.995F7	R-480-A	.36
R-50-A	AXY-150-265P	3221723	.995NL	.6777T	.35
R-50-B	AXY-150-270W	3221724	.995NM	.6777W	.35
R-50-BK	AXY-150-275M	3221725	.995NN	.6777X	.35
R-50-G	AXY-150-280T	3221726	.995NP	.6777Y	.35
R-50-R	AXY-150-285J	3221727	.995NR	.67780	.35
R-50-Y	AXY-150-290Q	3221728	.995NT	.67781	.35
R-80-AF	AXY-150-300Q	3221730	.995H1	.6769N	.35
R-80-BF	AXY-150-310N	3221732	.995H3	.6769R	.35
R-80-GF	AXY-150-330H	3221736	.995H7	.6769Y	.35
R-80-OF	AXY-150-340E	3221738	.995H9	.67703	.35
R-80-PF	AXY-150-345R	3221739	.995HA	.67704	.35
R-80-RF	AXY-150-355X	3221741	.995HC	.67706	.35
R-80-YF	AXY-150-370S	3221744	.995HF	.67709	.35
R-81-G-PC	AXY-150-375Y	3221745	.995EW	.67699	.35
R-81-R-PC	AXY-150-380P	3221746	.995EX	.6769A	.35
R-81-Y-PC	AXY-150-385F	3221747	.995EY	.6769B	.35
R-96-PCR-FB	AXY-200-005W	3221748	.995HH	.6770A	.24
R-96-PCR-FG	AXY-200-010G	3221749	.995HK	.6770B	.24
R-96-PCR-FO	AXY-200-015T	3221750	.995HL	.6770C	.24
R-96-PCR-FP	AXY-200-020D	3221751	.995HM	.6770D	.24
R-96-PCR-FSP	AXY-200-025Q	3221752	.995HN	.6770E	.24
R-96-PCR-FY	AXY-200-030A	3221753	.995HP	.6770F	.24
RA-48	AXY-150-390M	3221754	.995F3	.6769C	.35
RES-BAFFLE	AXY-190-045B	3221758	.995F0	RES-BAFFLE	.67
RES-MW12-HP	AXY-190-050Y	3221759	.995HR	.6770H	.66
RES-MW12-LP	AXY-190-060F	3221761	.995HW	.6770L	.66
RES-MW4-HP	AXY-190-070C	3221763	.995HY	RES-MW4-HP	.66
RES-MW8-HP	AXY-190-075P	3221764	.995K0	.6770N	.66
RES-MW8-LP	AXY-190-085M	3221766	.995K2	.6770R	.66
RES-SW12-HP	AXY-190-095J	3221768	.995K4	.6770W	.67
RES-SW1-LP	AXY-190-105J	3221770	.995K6	.6770Y	.67
RES-SW384-FX	AXY-190-115G	3221772	.995K8	RES-SW384-FX	.67
RES-SW384-HP	AXY-190-125D	3221774	.995KA	.67711	.67
RES-SW384-LP	AXY-190-135A	3221776	.995KC	.67713	.67
RES-SW8-HP	AXY-190-145U	3221778	.995KE	.67715	.67
RES-SW96-HP	AXY-190-160B	3221781	.995KK	.67717	.67
RES-SW96-LP	AXY-190-170V	3221783	.995KM	.67719	.67
RRF-175-CBK-R-S	AXY-145-170D	3221797	.996LW	.6793E	.52
RRF-175-C-R-S	AXY-145-175Q	3221798	.996LX	.6793F	.53
RRF-25-CBK-R-S	AXY-145-180A	3221799	.996LY	.6793H	.52
RRF-25-C-R-S	AXY-145-185N	3221800	.996M0	.6793K	.53
RRP-200-CBK-R	AXY-140-590L	3221801	.996M1	.6793L	.52
RRP-200-CBK-R-S	AXY-140-595B	3221802	.996M2	RRP-200-CBK-R-S	.52
RRP-200-C-R	AXY-140-600L	3221803	.996M3	.6793M	.53
RRP-200-C-R-S	AXY-140-605B	3221804	.996M4	RRP-200-C-R-S	.53
RRP-20-CBK-R	AXY-140-610Y	3221805	.996M5	.6793N	.52
RRP-20-CBK-R-S	AXY-140-615V	3221806	.996M6	RRP-20-CBK-R-S	.52
RRP-20-C-R	AXY-140-620F	3221807	.996M7	.6793P	.53
RRP-20-C-R-S	AXY-140-625S	3221808	.996M8	RRP-20-C-R-S	.53

Axygen Cat No	UK 	Germany 	France 	Spain 	Page No
RRP-50-CBK-R	AXY-140-630C	3221809	996M9	.6793R	52
RRP-50-CBK-R-S	AXY-140-635P	3221810	996MA	RRP-50-CBK-R-S	52
RRP-50-C-R	AXY-140-640W	3221811	996MB	.6793T	53
RRP-50-C-R-S	AXY-140-645M	3221812	996MC	RRP-50-C-R-S	53
SC-A	AXY-180-050P	3221813	995W6	.6782X	33
SC-BR	AXY-180-065C	3221816	995W8	.67830	33
SC-C	AXY-180-070J	3221817	995W9	.67831	33
SC-GR	AXY-180-080G	3221819	995WB	.67833	33
SC-LP-A	AXY-180-085T	3221820	995WC	SC-LP-A	33
SC-LP-B	AXY-180-090D	3221821	995WD	SC-LP-B	33
SC-LP-BR	AXY-180-095Q	3221822	995WE	SC-LP-BR	33
SC-LP-C	AXY-180-100D	3221823	995WF	SC-LP-C	33
SC-LP-G	AXY-180-105Q	3221824	995WH	SC-LP-G	33
SC-LP-GR	AXY-180-110A	3221825	995WK	SC-LP-GR	33
SC-LP-O	AXY-180-115N	3221826	995WL	SC-LP-O	33
SC-LP-P	AXY-180-120U	3221827	995WM	SC-LP-P	33
SC-LP-R	AXY-180-125K	3221828	995WN	SC-LP-R	33
SC-LP-V	AXY-180-130R	3221829	995WP	SC-LP-V	33
SC-LP-W	AXY-180-135H	3221830	995WR	SC-LP-W	33
SC-LP-Y	AXY-180-140X	3221831	995WT	SC-LP-Y	33
SC-O	AXY-180-145E	3221832	995WW	.67834	33
SCO-A	AXY-180-150L	3221833	995WX	.67835	34
SCO-B	AXY-180-160Y	3221835	995X0	.67836	34
SCO-BR	AXY-180-165V	3221836	995X1	.67837	34
SCO-C	AXY-180-180C	3221839	995X4	.6783A	34
SCO-G	AXY-180-190W	3221841	995X6	.6783C	34
SCO-GR	AXY-180-195M	3221842	995X7	.6783D	34
SCO-LP-A	AXY-180-210T	3221845	995XA	.6783H	34
SCO-LP-B	AXY-180-215J	3221846	995XB	.6783K	34
SCO-LP-BR	AXY-180-220Q	3221847	995XC	.6783L	34
SCO-LP-C	AXY-180-225G	3221848	995XD	.6783P	34
SCO-LP-G	AXY-180-235D	3221850	995XF	.6783T	34
SCO-LP-GR	AXY-180-240K	3221851	995XH	.6783W	34
SCO-LP-O	AXY-180-250H	3221853	995XL	.67840	34
SCO-LP-P	AXY-180-255U	3221854	995XM	.67842	34
SCO-LP-R	AXY-180-260E	3221855	995XN	.67844	34
SCO-LP-V	AXY-180-270B	3221857	995XR	.67846	34
SCO-LP-W	AXY-180-275X	3221858	995XT	.67848	34
SCO-LP-Y	AXY-180-280V	3221859	995XW	.6784A	34
SCO-O	AXY-180-285L	3221860	995XX	.6784C	34
SCO-P	AXY-180-295Y	3221862	995Y0	.6784E	34
SCO-R	AXY-180-305Y	3221864	995Y2	.6784H	34
SCO-V	AXY-180-315F	3221866	995Y4	.6784L	34
SCO-W	AXY-180-325C	3221868	995Y6	.6784N	34
SCO-Y	AXY-180-335W	3221870	995Y8	.6784R	34
SC-P	AXY-180-345T	3221872	995YA	.6784W	33
SC-R	AXY-180-350D	3221873	995YB	.6784X	33
SCT-050-A	AXY-210-005P	3221874	995YC	.6784Y	30
SCT-050-A-S	AXY-210-010W	3221875	995YD	.67850	32
SCT-050-B	AXY-210-015M	3221876	995YE	.67851	30
SCT-050-BR	AXY-210-020T	3221877	995YF	.67852	30
SCT-050-C	AXY-210-025J	3221878	995YH	.67855	30
SCT-050-C-S	AXY-210-030Q	3221879	995YK	.67856	32
SCT-050-G	AXY-210-035G	3221880	995YL	.67857	30
SCT-050-GR	AXY-210-040N	3221881	995YM	.67858	30
SCT-050-P	AXY-210-050K	3221883	995YP	.6785D	30
SCT-050-R	AXY-210-055A	3221884	995YR	.6785E	30
SCT-050-SS-A	AXY-210-060H	3221885	995YT	.6785H	30

Axygen Cat No	UK 	Germany 	France 	Spain 	Page No
SCT-050-SS-A-S	AXY-210-065U	3221886	995YW	6785K	32
SCT-050-SS-B	AXY-210-070E	3221887	995YX	6785L	30
SCT-050-SS-BR	AXY-210-075R	3221888	995YY	6785M	30
SCT-050-SS-C	AXY-210-090V	3221891	996A2	6785N	30
SCT-050-SS-C-S	AXY-210-095L	3221892	996A3	6785P	32
SCT-050-SS-G	AXY-210-100V	3221893	996A4	6785R	30
SCT-050-SS-GR	AXY-210-105L	3221894	996A5	6785T	30
SCT-050-SS-O	AXY-210-125F	3221898	996A9	6785W	30
SCT-050-SS-P	AXY-210-130M	3221899	996AA	6785X	30
SCT-050-SS-R	AXY-210-135C	3221900	996AB	6785Y	30
SCT-050-SS-V	AXY-210-145W	3221902	996AD	67860	30
SCT-050-SS-W	AXY-210-155T	3221904	996AF	67861	30
SCT-050-SS-Y	AXY-210-170A	3221907	996AL	67863	30
SCT-050-V	AXY-210-180U	3221909	996AN	67864	30
SCT-050-W	AXY-210-185K	3221910	996AP	67866	30
SCT-050-Y	AXY-210-190R	3221911	996AR	67868	30
SCT-150-A	AXY-210-205H	3221914	996AW	6786A	30
SCT-150-A-S	AXY-210-210X	3221915	996AX	6786B	32
SCT-150-B	AXY-210-215E	3221916	996AY	6786C	30
SCT-150-C	AXY-210-225B	3221918	996B1	6778T	30
SCT-150-C-S	AXY-210-230Y	3221919	996B2	6778W	32
SCT-150-G	AXY-210-235V	3221920	996B3	6786E	30
SCT-150-GR	AXY-210-240F	3221921	996B4	6786F	30
SCT-150-O	AXY-210-255P	3221924	996B7	6786H	30
SCT-150-P	AXY-210-260W	3221925	996B8	6786K	30
SCT-150-R	AXY-210-265M	3221926	996B9	6786L	30
SCT-150-SS-A	AXY-210-270T	3221927	996BA	6786M	31
SCT-150-SS-A-S	AXY-210-275J	3221928	996BB	6786N	32
SCT-150-SS-B	AXY-210-280Q	3221929	996BC	6786P	31
SCT-150-SS-BR	AXY-210-285G	3221930	996BD	6786R	31
SCT-150-SS-C	AXY-210-290N	3221931	996BE	6786T	31
SCT-150-SS-C-S	AXY-210-295D	3221932	996BF	6786W	32
SCT-150-SS-G	AXY-210-300N	3221933	996BH	6786X	31
SCT-150-SS-GR	AXY-210-305D	3221934	996BK	6786Y	31
SCT-150-SS-O	AXY-210-330E	3221939	996BR	67870	30
SCT-150-SS-P	AXY-210-335R	3221940	996BT	67871	31
SCT-150-SS-R	AXY-210-340B	3221941	996BW	67872	30
SCT-150-SS-V	AXY-210-345X	3221942	996BX	67873	31
SCT-150-SS-W	AXY-210-350V	3221943	996BY	67874	31
SCT-150-SS-Y	AXY-210-360S	3221945	996C1	67877	31
SCT-150-V	AXY-210-365Y	3221946	996C2	67878	30
SCT-150-W	AXY-210-370P	3221947	996C3	67879	30
SCT-150-Y	AXY-210-375F	3221948	996C4	6787A	30
SCT-200-A	AXY-210-395W	3221952	996C8	6787B	31
SCT-200-A-S	AXY-210-400J	3221953	996C9	6787C	32
SCT-200-B	AXY-210-405W	3221954	996CA	6787D	31
SCT-200-BR	AXY-210-410G	3221955	996CB	6787E	31
SCT-200-C	AXY-210-415T	3221956	996CC	67791	31
SCT-200-C-S	AXY-210-420D	3221957	996CD	67792	32
SCT-200-G	AXY-210-425Q	3221958	996CE	6787F	31
SCT-200-GR	AXY-210-430A	3221959	996CF	6787H	31
SCT-200-O	AXY-210-440U	3221961	996CK	6787K	31
SCT-200-P	AXY-210-445K	3221962	996CL	6787L	31
SCT-200-R	AXY-210-450R	3221963	996CM	6787M	31
SCT-200-SS-A	AXY-210-455H	3221964	996CN	6787N	31
SCT-200-SS-A-S	AXY-210-460X	3221965	996CP	6787P	32
SCT-200-SS-B	AXY-210-465E	3221966	996CR	6787R	31
SCT-200-SS-BR	AXY-210-470L	3221967	996CT	6787T	31

Axygen Cat No	UK 	Germany 	France 	Spain 	Page No
SCT-200-SS-C	AXY-210-475B	3221968	996CW	6787W	31
SCT-200-SS-C-S	AXY-210-480Y	3221969	996CX	6787X	32
SCT-200-SS-G	AXY-210-485V	3221970	996CY	6787Y	31
SCT-200-SS-GR	AXY-210-490F	3221971	996D0	67880	31
SCT-200-SS-O	AXY-210-505S	3221974	996D3	67881	31
SCT-200-SS-P	AXY-210-510C	3221975	996D4	67882	31
SCT-200-SS-R	AXY-210-515P	3221976	996D5	67883	31
SCT-200-SS-W	AXY-210-525M	3221978	996D7	67885	31
SCT-200-SS-Y	AXY-210-535J	3221980	996D9	67887	31
SCT-200-V	AXY-210-540Q	3221981	996DA	67888	31
SCT-200-W	AXY-210-545G	3221982	996DB	67889	31
SCT-200-Y	AXY-210-550N	3221983	996DC	6788A	31
SCT-45-C	AXY-210-555D	3221984	996DD	SCT-45-C	30
SCT-45-C-S	AXY-210-560K	3221985	996DE	SCT-45-C-S	32
SC-V	AXY-180-355Q	3221994	996DP	6788B	33
SC-W	AXY-180-360A	3221995	996DR	6788C	33
SC-Y	AXY-180-365N	3221996	996DT	6788D	33
SPN-20-CBK-R	AXY-140-650T	3221998	996MD	6793W	41
SPN-20-CBK-R-S	AXY-140-655J	3221999	996ME	6793X	41
SPN-250-CBK-R	AXY-140-660Q	3222000	996MF	6793Y	41
SPN-250-CBK-R-S	AXY-140-665G	3222001	996MH	6794A	41
SPN-50-CBK-R	AXY-140-670N	3222002	996MK	6794B	41
SPN-50-CBK-R-S	AXY-140-675D	3222003	996ML	6794C	41
SPNF-180-CBK-R-S	AXY-145-190U	3222004	996MM	6794D	41
SPNF-20-CBK-R-S	AXY-145-195K	3222005	996MN	6794E	41
SPNF-30-CBK-R-S	AXY-145-200U	3222006	996MP	6794F	41
ST-050	AXY-210-610V	3222007	996DX	6788E	32
ST-050-SS	AXY-210-620S	3222009	996E0	6788H	32
ST-050-SS-X	AXY-210-635F	3222012	996E3	6788K	32
ST-050-X	AXY-210-640M	3222013	996E4	6788L	32
ST-150	AXY-210-650J	3222015	996E5	6788N	32
ST-150-SS	AXY-210-660G	3222017	996E7	6788R	32
ST-150-SS-X	AXY-210-675Q	3222020	996EA	6788W	32
ST-150-X	AXY-210-680A	3222021	996EB	6788X	32
ST-200	AXY-210-685N	3222022	996EC	6788Y	32
ST-200-SS	AXY-210-695K	3222024	996EE	67892	32
ST-200-SS-X	AXY-210-710R	3222027	996EK	67894	32
ST-200-X	AXY-210-715H	3222028	996EL	67895	32
ST-45	AXY-210-720X	3222029	996EM	67896	32
T-1000-C	AXY-140-695U	3222034	997DH	6780A	6
T-1000-C-L	AXY-140-700H	3222035	997DK	68013	6
T-1000-C-L-R	AXY-140-705U	3222036	996XD	6780B	6
T-1000-C-L-R-S	AXY-140-710E	3222037	996XE	68014	6
T-1000-C-R	AXY-140-715R	3222038	996XF	68015	6
T-1000-C-R-S	AXY-140-720B	3222039	996XH	6780C	6
T-1005-WB-C	AXY-140-725X	3222040	997DL	68016	6
T-1005-WB-C-L	AXY-140-730V	3222041	997DM	68017	6
T-1005-WB-C-L-R	AXY-140-735L	3222042	996XK	T-1005-WB-C-L-R	6
T-1005-WB-C-L-R-S	AXY-140-740S	3222043	996XL	T-1005-WB-C-L-R-S	6
T-1005-WB-C-R	AXY-140-745Y	3222044	996XM	68019	6
T-1005-WB-C-R-S	AXY-140-750P	3222045	996XN	6801A	6
T-10ML-C	AXY-140-755F	3222046	996YR	6781D	8
T-1200-C	AXY-140-760M	3222047	997DN	6801B	6
T-1200-C-R	AXY-140-765C	3222048	996Y6	6782B	6
T-1200-C-R-S	AXY-140-770J	3222049	996Y7	6782C	6
T-1536-L-R	AXY-140-775W	3222050	997BK	6806E	7
T-1536-L-R-S	AXY-140-780G	3222051	997BL	6806F	7

Axygen Cat No	UK 	Germany 	France 	Spain 	Page No
T-1536-R	AXY-140-785T	3222052	.997BM	.6806H	.7
T-1536-R-S	AXY-140-790D	3222053	.997BN	.6806K	.7
T-200-C	AXY-140-795Q	3222054	.997FL	.6780K	.4
T-200-C-L	AXY-140-800D	3222055	.997FM	.6806Y	.4
T-200-C-L-R	AXY-140-805Q	3222056	.996MR	.6794H	.4
T-200-C-L-R-S	AXY-140-810A	3222057	.996MT	.6794K	.4
T-200-C-R	AXY-140-825K	3222060	.996MW	.6794N	.4
T-200-C-R-S	AXY-140-830R	3222061	.996MX	.6794P	.4
T-200-C-STK	AXY-140-835H	3222062	.997CX	.6794R	.4
T-205-WB-C	AXY-140-870F	3222066	.997FP	.68070	.5
T-205-WB-C-L	AXY-140-875S	3222067	.997FR	.68071	.5
T-205-WB-C-L-R	AXY-140-880C	3222068	.996N1	.6794Y	.5
T-205-WB-C-L-R-S	AXY-140-885P	3222069	.996N2	.6795A	.5
T-205-WB-C-R	AXY-140-890W	3222070	.996N3	.6795B	.5
T-205-WB-C-R-S	AXY-140-895M	3222071	.996N4	.6795C	.5
T-300	AXY-140-935D	3221162	.997FX	.6780M	.3
T-300-L	AXY-140-940K	3222079	.997FY	.68074	.3
T-300-L-R	AXY-140-945A	3222080	.996N9	.6795F	.3
T-300-L-R-S	AXY-140-950H	3222081	.996NA	.6795H	.3
T-300-R	AXY-140-965R	3221163	.996NB	.6779D	.3
T-300-R-S	AXY-140-970B	3222084	.996NC	.6795M	.3
T-300-STK	AXY-140-975X	3221164	.997D5	.6795N	.3
T-350-C	AXY-140-985L	3222086	.997F3	.6804R	.5
T-350-C-L	AXY-140-990S	3222087	.997F4	.6804T	.5
T-350-C-L-R	AXY-140-995Y	3222088	.996ND	.6795R	.5
T-350-C-L-R-S	AXY-141-005T	3222089	.996NE	.6795T	.5
T-350-C-R	AXY-141-010D	3222090	.996NF	.6795W	.5
T-350-C-R-S	AXY-141-015Q	3222091	.996NH	.6795X	.5
T-384-L-R	AXY-141-020A	3222092	.997BP	.6806L	.7
T-384-L-R-S	AXY-141-025N	3222093	.997BR	.6806M	.7
T-384-R	AXY-141-030U	3222094	.997BT	.6806N	.7
T-384-R-S	AXY-141-035K	3222095	.997BW	.6806P	.7
T-400	AXY-141-040R	3222096	.997H0	.6780N	.3
T-400-L	AXY-141-045H	3222097	.997H1	.68075	.3
T-400-L-R	AXY-141-050X	3222098	.996NK	.6795Y	.3
T-400-L-R-S	AXY-141-055E	3222099	.996NL	.6796A	.3
T-400-R	AXY-141-060L	3222100	.996NM	.6796B	.3
T-400-R-S	AXY-141-065B	3222101	.996NN	.6796C	.3
T-5000-C	AXY-141-070Y	3222102	.997AF	.67829	.8
TF-1000-L-R-S	AXY-145-225E	3221165	.996XP	.6801F	.6
TF-1000-R-S	AXY-145-230L	3221166	.996XR	.6780T	.6
TF-1005-WB-L-R-S	AXY-145-235B	3222117	.996XT	.6801H	.6
TF-1005-WB-R-S	AXY-145-240Y	3222118	.996XW	.6801K	.6
TF-100-L-R-S	AXY-145-245V	3221167	.996NT	.6796K	.4
TF-100-R-S	AXY-145-250F	3221168	.996NW	.6779E	.4
TF-1200-C-R-S	AXY-145-260C	3222120	.996YD	.6782W	.6
TF-150-L-R-S	AXY-145-275M	3222123	.996NY	.6796L	.4
TF-150-R-S	AXY-145-280T	3222124	.996P0	.6796M	.4
TF-200-L-R-S	AXY-145-295G	3221169	.996P1	.6796N	.4
TF-200-R-S	AXY-145-300Q	3221170	.996P2	.6779F	.4
TF-205-WB-L-R-S	AXY-145-305G	3222127	.996P3	.6796P	.5
TF-205-WB-R-S	AXY-145-310N	3222128	.996P4	.6796R	.5
TF-20-L-R-S	AXY-145-315D	3221171	.996P5	.6796T	.4
TF-20-R-S	AXY-145-320K	3221172	.996P6	.6779H	.4
TF-300-L-R-S	AXY-145-330H	3221173	.996P7	.6796W	.3
TF-350-L-R-S	AXY-145-345R	3222131	.996P9	.6796X	.5
TF-350-R-S	AXY-145-350B	3222132	.996PA	.6796Y	.5

Axygen Cat No	UK 	Germany 	France 	Spain 	Page No
TF-384-30-L-R-S	AXY-145-355X	3222133	997BX	6806R	.7
TF-384-30-R-S	AXY-145-360V	3222134	997BY	6806T	.7
TF-420-L-R-S	AXY-145-380P	3222137	996PD	6797B	.3
TF-420-R-S	AXY-145-385F	3222138	996PE	6797C	.3
TF-50-L-R-S	AXY-145-410J	3222143	996PF	6797D	.4
TF-50-R-S	AXY-145-415W	3222144	996PH	6797E	.4
TR-222-C	AXY-141-175R	3222154	997H2	67811	.4
TR-222-C-L	AXY-141-180B	3222155	997H3	68076	.4
TR-222-C-L-R	AXY-141-185X	3221176	996PK	6797F	.4
TR-222-C-L-R-S	AXY-141-190V	3222156	996PL	6797H	.4
TR-222-C-R-S	AXY-141-210S	3222160	996PN	6797N	.4
TR-222-C-STK	AXY-141-215Y	3222161	997D9	6797P	.4
TR-333-C	AXY-141-245W	3222167	997H5	67813	.5
TR-333-C-L	AXY-141-250G	3222168	997H6	68077	.5
TR-333-C-L-R	AXY-141-255T	3222169	996PT	67989	.5
TR-333-C-L-R-S	AXY-141-260D	3222170	996PW	6798A	.5
TR-333-C-R	AXY-141-265Q	3222171	996PX	6798B	.5
TR-333-C-R-S	AXY-141-270A	3222172	996PY	6798C	.5
TT-1000-CBK-HTR	AXY-141-275N	3222173	996YE	67814	.47, 52
TT-1000-CBK-HTR-24	AXY-141-280U	3222174	997CL	TT-1000-CBK-HTR-24	.47
TT-1000-CBK-HTR-S	AXY-141-285K	3222175	996YF	TT-1000-CBK-HTR-S	.47, 52
TT-1000-C-HTR	AXY-141-290R	3222176	996YH	67816	.46, 53
TT-1000-C-HTR-S	AXY-141-295H	3222177	996YK	67817	.46, 53
TT-200-CBK-HTR	AXY-141-300R	3222178	996YT	6781E	.47, 50
TT-200-CBK-HTR-36	AXY-141-305H	3222179	997DX	TT-200-CBK-HTR-36	.47
TT-200-CBK-HTR-S	AXY-141-310X	3222180	996YW	6781F	.47, 50
TT-200-C-HTR	AXY-141-315E	3222181	996YX	6781H	.47, 50
TT-200-C-HTR-S	AXY-141-320L	3222182	996YY	6781K	.47, 50
TT-20-CBK-HTR	AXY-141-325B	3222183	997A0	6781L	.47
TT-20-CBK-HTR-36	AXY-141-330Y	3222184	997DY	6801P	.47
TT-20-CBK-HTR-S	AXY-141-335V	3222185	997A1	6781M	.47
TT-20-C-HTR	AXY-141-340F	3222186	997A2	6781N	.46
TT-20-C-HTR-S	AXY-141-345S	3222187	997A3	6781P	.46
TT-50-CBK-HTR	AXY-141-350C	3222188	997A4	6781R	.47, 50
TT-50-CBK-HTR-36	AXY-141-355P	3222189	997E0	6801R	.47
TT-50-CBK-HTR-S	AXY-141-360W	3222190	997A5	6781T	.47, 50
TT-50-C-HTR	AXY-141-365M	3222191	997A6	6781W	.47, 50
TT-50-C-HTR-S	AXY-141-370T	3222192	997A7	6781X	.47, 50
TTF-1000-CBK-HTR-S	AXY-145-420G	3222193	996YL	TTF-1000-CBK-HTR-S	.47, 52
TTF-1000-C-HTR-S	AXY-145-425T	3222194	996YM	67819	.46, 53
TTF-200-CBK-HTR-S	AXY-145-430D	3222195	997A8	TTF-200-CBK-HTR-S	.47, 50
TTF-200-C-HTR-S	AXY-145-435Q	3222196	997A9	67820	.46, 50
TTF-20-CBK-HTR-S	AXY-145-440A	3222197	997AA	67821	.47
TTF-20-C-HTR-S	AXY-145-445N	3222198	997AB	67822	.46
TTF-50-CBK-HTR-S	AXY-145-450U	3222199	997AC	67823	.47, 50
TTF-50-C-HTR-S	AXY-145-455K	3222200	997AD	67824	.46, 50
TUB-310-NC	AXY-175-250H	3222201	996EP	6782A	.22
TWP-200-R	AXY-141-375J	3222202	996R0	6798D	.61
TWP-200-R-S	AXY-141-380Q	3222203	996R1	6798E	.61
TWPF-120-R-S	AXY-145-460R	3222204	996R2	6798F	.61
TXL-10	AXY-141-385G	3222205	997H7	68078	.3
TXL-10-L	AXY-141-390N	3222206	997H8	68079	.3
TXL-10-L-R	AXY-141-395D	3221177	996R3	6798H	.3
TXL-10-L-R-S	AXY-141-400N	3222207	996R4	6798K	.3
TXL-10-R	AXY-141-405D	3222208	996R5	6798L	.3
TXL-10-R-S	AXY-141-410K	3222209	996R6	6798M	.3
TXLF-10	AXY-141-415A	3222210	997FF	68057	.3

Axygen Cat No	UK 	Germany 	France 	Spain 	Page No
TXLF-10-L-R-S	AXY-145-465H	3221178	.996R7	.6798N	.3
TXLF-10-R-S	AXY-141-420H	3221179	.996R8	.6798P	.3
UC-500	AXY-135-050U	3222211	.995P5	.67782	.22
VT-20-R	AXY-141-425U	3222214	.996R9	VT-20-R	.44
VT-20-R-LAB	AXY-141-430E	3222215	.996RA	VT-20-R-LAB	.44
VT-20-R-LAB-S	AXY-141-435R	3222216	.996RB	VT-20-R-LAB-S	.44
VT-20-R-S	AXY-141-440B	3222217	.996RC	VT-20-R-S	.44
VT-250-L-R	AXY-141-445X	3222218	.996RD	VT-250-L-R	.44
VT-250-L-R-LAB	AXY-141-450V	3222219	.996RE	VT-250-L-R-LAB	.44
VT-250-R	AXY-141-455L	3222220	.996RF	VT-250-R	.44
VT-250-R-LAB	AXY-141-460S	3222221	.996RH	VT-250-R-LAB	.44
VT-250-R-LAB-S	AXY-141-465Y	3222222	.996RK	VT-250-R-LAB-S	.44
VT-250-R-S	AXY-141-470P	3222223	.996RL	VT-250-R-S	.44
VT-384-10UL-R	AXY-141-475F	3222224	.997C0	VT-384-10UL-R	.45
VT-384-10UL-R-S	AXY-141-480M	3222225	.997C1	VT-384-10UL-R-S	.45
VT-384-31UL-R	AXY-141-490J	3222227	.997C3	VT-384-31UL-R	.45
VT-384-31UL-R-S	AXY-141-495W	3222228	.997C4	VT-384-31UL-R-S	.45
VT-384-5UL-R	AXY-141-505W	3222230	.997C6	VT-384-5UL-R	.45
VT-384-5UL-R-S	AXY-141-510G	3222231	.997C7	VT-384-5UL-R-S	.45
VT-384-70UL-R	AXY-141-520D	3222233	.997C9	VT-384-70UL-R	.45
VT-384-70UL-R-S	AXY-141-525Q	3222234	.997CA	VT-384-70UL-R-S	.45
VTF-165-L-R-S	AXY-145-470X	3222236	.996RM	VTF-165-L-R-S	.44
VTF-165-R-LAB-S	AXY-145-475E	3222237	.996RN	VTF-165-R-LAB-S	.44
VTF-165-R-S	AXY-145-480L	3222238	.996RP	VTF-165-R-S	.44
VTF-20-R-LAB-S	AXY-145-485B	3222239	.996RR	VTF-20-R-LAB-S	.44
VTF-20-R-S	AXY-145-490Y	3222240	.996RT	VTF-20-R-S	.44
VTF-384-15UL-R-S	AXY-145-495V	3222241	.997CC	VTF-384-15UL-R-S	.45
VTF-384-50UL-R-S	AXY-145-500Y	3222242	.997CD	VTF-384-50UL-R-S	.45
ZT-100-L-R	AXY-141-540U	3222244	.996RW	.6798R	.53
ZT-100-L-R-S	AXY-141-545K	3222245	.996RX	.6798T	.53
ZT-100-R	AXY-141-550R	3222246	.996RY	.6798W	.49, 53
ZT-100-R-S	AXY-141-555H	3222247	.996T0	.6798X	.49, 53
ZT-200-L-R	AXY-141-565E	3222249	.996T1	.6798Y	.53
ZT-200-L-R-S	AXY-141-570L	3222250	.996T2	.67990	.53
ZT-200-R	AXY-141-575B	3222251	.996T3	.67991	.49, 53
ZT-200-R-S	AXY-141-580Y	3222252	.996T4	.67992	.49, 53
ZT-205-WB-L-R	AXY-141-585V	3222253	.996T5	.67993	.54
ZT-205-WB-R	AXY-141-590F	3222254	.996T6	.67995	.54
ZT-205-WB-R-S	AXY-141-595S	3222255	.996T7	.67996	.49, 54
ZT-384-C-R	AXY-141-600F	3222256	.997CE	ZT-384-C-R	.54
ZT-384-C-R-S	AXY-141-605S	3222257	.997CF	ZT-384-C-R-S	.54
ZT-50-L-R	AXY-141-610C	3222258	.996T8	.67997	.54
ZT-50-L-R-S	AXY-141-615P	3222259	.996T9	.67998	.54
ZT-50-R	AXY-141-620W	3222260	.996TA	.67999	.49, 54
ZT-50-R-S	AXY-141-625M	3222261	.996TB	.6799A	.49, 54
ZTF-100-L-R-S	AXY-145-505V	3222262	.996TC	.6799B	.54
ZTF-100-R-S	AXY-145-510F	3222263	.996TD	.6799C	.49, 54
ZTF-200-L-R-S	AXY-145-515S	3222264	.996TE	.6799D	.54
ZTF-200-R-S	AXY-145-520C	3222265	.996TF	.6799E	.49, 54
ZTF-205-WB-L-R-S	AXY-145-525P	3222266	.996TH	.6799F	.54
ZTF-205-WB-R-S	AXY-145-530W	3222267	.996TK	.6799H	.49, 54
ZTF-50-L-R-S	AXY-145-535M	3222268	.996TL	.6799K	.54
ZTF-50-R-S	AXY-145-540T	3222269	.996TM	.6799L	.49, 54

For up-to-date information
on Axygen Scientific's
comprehensive range of
products and services,
go to your country-specific
Fisher Scientific website.



Austria

Fisher Scientific (Austria) GmbH
Rudolf von Alt-Platz 1
1030 Vienna
Tel.: +43 (0) 800 20 88 40
Fax: +43 (0) 800 20 66 90
Email: info.austria@thermofisher.com
www.at.fishersci.com

Belgium

Fisher Scientific
Clintonpark - Keppekouter
Ninovesteenweg 198
9320 Erembodem Aalst
Tel.: +32 (0) 56 260 260
Fax: +32 (0) 56 260 270
Email: be.fisher@thermofisher.com
www.be.fishersci.com

Czech

Fisher Scientific spol. s.r.o.
Kosmonautu 324
53009 Pardubice
Tel.: +420 (0) 466 798-230
Fax: +420 (0) 466 435-008
Email: info.cz@thermofisher.com
www.thermofisher.cz

Denmark

Fisher Scientific
Postboks 60
Industrivej 3
3550 Slangerup
Tel.: +45 (0) 70 27 99 20
Fax: +45 (0) 70 27 99 29
Email: kundeservice@thermofisher.com
www.fishersci.dk

Finland

Fisher Scientific
Ratastie 2
01620 Vantaa
Tel.: +358 (0) 9 8027 6280
Fax: +358 (0) 9 8027 6235
Email: fisher.fi@thermofisher.com
www.fishersci.fi

France

Fisher Scientific
Parc d'innovation
BP 50111
67403 Illkirch Cedex
Tel.: +33 (0) 388 67 53 20
Fax: +33 (0) 388 67 11 68
Email: fr.commande@thermofisher.com
www.fr.fishersci.com

Germany

Fisher Scientific GmbH
Im Heiligen Feld 17
58239 Schwerte
Tel.: +49 (0) 2304 932 5
Fax: +49 (0) 2304 932 950
Email: info.germany@thermofisher.com
www.de.fishersci.com

Ireland

Fisher Scientific Ireland
Suite 3
Plaza 212
Blanchardstown Corporate Park 2
Ballycoolin
Dublin 15
Tel.: +353 (0)1 885 5854
Fax: +353 (0)1 899 1855
Email: fsie.sales@thermofisher.com
www.ie.fishersci.com

Italy

Fisher Scientific
Tel.: +39 (0)2 953 28 258
Fax: +39 (0)2 953 27 374
Email: it.fisher@thermofisher.com
www.it.fishersci.com

The Netherlands

Fisher Scientific
Scheepsbouwersweg 1b
P.O. Box 4
1120 AA Landsmeer
Tel.: +31 (0) 20 487 70 00
Fax: +31 (0) 20 487 70 70
Email: nl.info@thermofisher.com
www.nl.fishersci.com

Norway

Fisher Scientific
Frysjaeveien 33E
0884 Oslo
Tel.: +47 (0) 22 95 59 59
Fax: +47 (0) 22 95 59 40
Email: fisher.no@thermofisher.com
www.fishersci.no

Portugal

Fisher Scientific
Rua Pedro Álvares Cabral, n°24, 3°D
Edifício Euro - Infantado
2670-391 Loures
Tel.: +351 (0) 21 425 33 50/4
Fax: +351 (0) 21 425 33 51
Email: pt.fisher@thermofisher.com
www.pt.fishersci.com

Slovenia

Fisher Scientific d.o.o
Parmova ulica 53
SI-1000 Ljubljana
Tel.: +386 (0) 598 31 494
Fax: +386 (0) 598 31 495
Email: si.info@thermofisher.com
www.si.fishersci.com

Spain

Fisher Scientific
C/ Luis I, 9
28031 MADRID
Tel.: +34 (0) 902 239 303
Fax: +34 (0) 902 239 404
Email: es.fisher@thermofisher.com
www.es.fishersci.com

Sweden

Fisher Scientific
Box 9193
400 94 Göteborg
Tel.: +46 (0) 31 352 32 00
Fax: +46 (0) 31 352 32 50
Email: fisher.se@thermofisher.com
www.fishersci.se

Switzerland

Fisher Scientific
Wilstrasse 57
BP 1006
5610 Wohlen
Tel.: +41 (0) 56 618 41 11
Fax: +41 (0) 56 618 41 41
Email: info.ch@thermofisher.com
www.ch.fishersci.com

United Kingdom

Fisher Scientific UK
Bishop Meadow Road
Loughborough
Leicestershire
LE11 5RG
Tel.: +44 (0)1509 231166
Fax: +44 (0) 1509 231893
Email: fsuk.sales@thermofisher.com
www.fisher.co.uk