



THE MOST DURABLE FLOOR MARKING TAPE



## **TOUGH**STRIPE® Floor Marking

- SUPERIOR DURABILITY
- EASY APPLICATION
- HIGH VISIBILITY

## Superior Durability

**Spend less time replacing damaged or worn lines for a better-looking, more efficient facility.**

- Withstands forklift traffic without tearing or lifting
- Low-profile design minimizes tears and scratches from skids, pallet jacks, etc.
- Rugged polyester with ultra-aggressive adhesive



**Online Video:**  
[www.BradyID.com/toughstripe](http://www.BradyID.com/toughstripe)

## High Visibility

**Get the same visibility of painted floor markings – and pay less.**

- High-gloss surface shines like new paint
- Low profile minimizes debris buildup along the edges that occurs with thicker (extruded) floor tapes
- Surface resists marks and smudges and cleans up like new
- Available in a variety of high-impact colors
- Custom colors available



## Painless Removal

**Easily remove floor markings without damaging the floor or leaving adhesive residue.**

- Does not chip and flake when being removed – comes off in one piece
- Clean removal without any unsightly adhesive residue or damage to the floor

## Easy Application

**Quickly lay down smooth, straight lines – without the help of coworkers.**

- Can be easily applied by one person working alone
- Stiff polyester with liner prevents tape stretching and reduces wrinkles and wavy, uneven lines
- No special floor preparation required – just clean with common cleansers



**Online Video:**  
[www.BradyID.com/toughstripe](http://www.BradyID.com/toughstripe)

## Diecut Shapes

**Utilize different shapes, colors and sizes for more effective, durable floor markings.**

- Dashes, dots, arrows, footprints, and corner marks (L, T and + shapes)
- Longer lasting markings – Minimizes the risk of damage and facilitates fast repair
- **Select dashes, dots and arrows are pre-spaced on transfer tape, making it incredibly easy to lay down straight, evenly spaced lines**



# Brady B-514 Floor Marking Polyester

ToughStripe® floor marking products are made with Brady's new B-514 polyester. ToughStripe products are ideal for marking aisles, passageways and storage locations, and pointing out important safety equipment and egress paths.

- Exceeds safety standards for clean, dry non-slip surfaces per ANSI A1264.2-2006 and OSHA 1910.22
- 2 mil thickness
- Service temperature range of 0°F – 129°F
- Resists harsh chemicals
- Custom colors available



Floor Marking Tape B-514										
	Black	White	Red	Green	Blue	Orange	Yellow	Black/Yellow 	Red/White 	Black/White 
2" x 100'	104310	104311	104313	104315	104314	104316	104312	104317	104318	104319
3" x 100'	104340	104341	104343	104345	104344	104346	104342	104347	104348	104349
4" x 100'	104370	104371	104373	104375	104374	104376	104372	104377	104378	104379



Dots - 300 / Roll B-514						
	Black	White	Red	Green	Blue	Yellow
3.5" Dia	104404	104405	104400	104401	104402	104403



Arrows 100 / Package B-514						
	Black	White	Red	Green	Blue	Yellow
2" x 5"	104416	104417	104412	104413	104414	104415
3" x 8"	104422	104423	104418	104419	104420	104421
4" x 10"	104428	104429	104424	104425	104426	104427



Foot Prints - 10 / Package (5 Right - 5 Left) B-514						
	Black	White	Red	Green	Blue	Yellow
10' x 3.5"	104410	104411	104406	104407	104408	104409



Corner Marks - "L" 20 / Package B-514						
	Black	White	Red	Green	Blue	Yellow
2" x 5"	104434	104435	104430	104431	104432	104433
3" x 8"	104446	104447	104442	104443	104444	104445
4" x 10"	104458	104459	104454	104455	104456	104457



Divider Marks - "T" 20 / Package B-514						
	Black	White	Red	Green	Blue	Yellow
2" x 5"	104440	104441	104436	104437	104438	104439
3" x 8"	104452	104453	104448	104449	104450	104451
4" x 10"	104464	104465	104460	104461	104462	104463



Center Marks - "+" 20 / Package B-514						
	Black	White	Red	Green	Blue	Yellow
2" x 5"	104470	104471	104466	104467	104468	104469
3" x 8"	104476	104477	104472	104473	104474	104475
4" x 10"	104482	104483	104478	104479	104480	104481



 **Online Video:**  
[www.BradyID.com/toughstripe](http://www.BradyID.com/toughstripe)



Pre-Spaced Shapes (Spaced 18" Apart) B-514						
	Black	White	Red	Green	Blue	Yellow
3.5" x 100' – 55 dots	104525	104522	104521	104520	104524	104523
2" x 5" x 100' – 52 arrows	104554	104555	104526	104527	104528	104529
2" x 8" x 100' – 46 dashes	142178	142177	142179	142181	142180	104556



# ToughStripe® **Print-On-Demand** Floor Labels

**ToughStripe® floor tape is available in printable label cartridges, which can be used to create custom floor labels. The printable labels feature the same durability and performance as ToughStripe floor marking tape, making them an ideal solution for identifying designated storage locations and providing visual instructions on the shop floor.**

- Easy 3-step process: print desired label from a select Brady printer, position on floor, apply included overlamine

## **ToughStripe Floor Label Cartridges for GlobalMark® 2 Sign and Label Printer**

Catalog No.	Size	Color	Description
142155	1.125" x 100'	White	ToughStripe Tape w/ Overlam
142159	1.125" x 100'	Black	ToughStripe Tape w/ Overlam
142162	1.125" x 100'	Yellow	ToughStripe Tape w/ Overlam
142166	1.125" x 100'	Red	ToughStripe Tape w/ Overlam
142169	1.125" x 100'	Blue	ToughStripe Tape w/ Overlam
142172	1.125" x 100'	Green	ToughStripe Tape w/ Overlam
142175	1.125" x 100'	Orange	ToughStripe Tape w/ Overlam
142154	2.25" x 100'	White	ToughStripe Tape w/ Overlam
142158	2.25" x 100'	Black	ToughStripe Tape w/ Overlam
142161	2.25" x 100'	Yellow	ToughStripe Tape w/ Overlam
142165	2.25" x 100'	Red	ToughStripe Tape w/ Overlam
142168	2.25" x 100'	Blue	ToughStripe Tape w/ Overlam
142171	2.25" x 100'	Green	ToughStripe Tape w/ Overlam
142174	2.25" x 100'	Orange	ToughStripe Tape w/ Overlam
142156	3" x 100'	White	ToughStripe Tape w/ Overlam
142163	3" x 100'	Yellow	ToughStripe Tape w/ Overlam
142157	4" x 100'	White	ToughStripe Tape w/ Overlam
142160	4" x 100'	Black	ToughStripe Tape w/ Overlam
142164	4" x 100'	Yellow	ToughStripe Tape w/ Overlam
142167	4" x 100'	Red	ToughStripe Tape w/ Overlam
142170	4" x 100'	Blue	ToughStripe Tape w/ Overlam
142173	4" x 100'	Green	ToughStripe Tape w/ Overlam
142176	4" x 100'	Orange	ToughStripe Tape w/ Overlam

\* Specialty black ribbon catalog #96089 required to print on ToughStripe floor tape. Use standard white ribbon catalog #76741 for white text.



**!** For more information on GlobalMark® 2 Printer visit [www.BradyID.com/globalmark](http://www.BradyID.com/globalmark)



## **ToughStripe Floor Label Cartridges for BMP®71 Label Printer**

Catalog No.	Size	Color	Description
142140	1" x 50'	White	ToughStripe Tape w/ Overlam
142142	1" x 50'	Black	ToughStripe Tape w/ Overlam
142144	1" x 50'	Yellow	ToughStripe Tape w/ Overlam
142146	1" x 50'	Red	ToughStripe Tape w/ Overlam
142148	1" x 50'	Blue	ToughStripe Tape w/ Overlam
142150	1" x 50'	Green	ToughStripe Tape w/ Overlam
142152	1" x 50'	Orange	ToughStripe Tape w/ Overlam
142141	2" x 50'	White	ToughStripe Tape w/ Overlam
142143	2" x 50'	Black	ToughStripe Tape w/ Overlam
142145	2" x 50'	Yellow	ToughStripe Tape w/ Overlam
142147	2" x 50'	Red	ToughStripe Tape w/ Overlam
142149	2" x 50'	Blue	ToughStripe Tape w/ Overlam
142151	2" x 50'	Green	ToughStripe Tape w/ Overlam
142153	2" x 50'	Orange	ToughStripe Tape w/ Overlam

\* Specialty black ribbon catalog #M71-R6000 required to print on ToughStripe floor tape. Use standard white ribbon catalog #M71-R4400-WT for white text.



















**!** For more information on BMP®71 Printer visit [www.BradyID.com/bmp71](http://www.BradyID.com/bmp71)

# Brady B-534 Floor Marking Signs with Anti-Skid Tread

Brady B-534 ToughStripe® floor signs are made with Brady's new B-534 polyester. They are specifically designed to alert workers of potential dangers and enforce protective equipment requirements.

- Exceeds safety standards for clean, dry non-slip surfaces per ANSI A1264.2-2006 and OSHA 1910.22
- 3 mil thickness
- Service temperature range of 0°F – 129°F
- Resists harsh chemicals
- Black areas of signs are coated with anti-skid tread

	Catalog No.	Description	Size
	104486	First Aid with Arrow	17" dial
	104487	Safety Shower	17" dial
	104489	Arrow Symbol	17" dial
	104490	Exit Arrow with Symbol	17" dial
	104492	Fire Extinguisher with Symbol	17" dial
	104493	Fire Alarm with Symbol	17" dial
	104494	Fire Hose with Symbol	17" dial
	104495	Emergency Exit with Symbol	17" dial
	104496	Emergency Stairs with Symbol	17" dial
	104501	Watch Out For Fork Lift	17" dial
	104507	Eye Wash with Symbol	17" dial
	104508	Keep Aisles Clear	17" dial
	104509	Pedestrian Traffic Only	17" dial
	104511	Stop with Symbol	17" dial

	Catalog No.	Description	Size
	104512	Warning Forklift Traffic	17" dial
	104513	Production Area	17" dial
	104488	Radiation Area	14" x 18"
	104491	First Aid with Symbol	14" x 18"
	104497	Do Not Enter	14" x 18"
	104498	Chemical Storage	14" x 18"
	104499	Watch Your Step	14" x 18"
	104500	No Smoking with Symbol	14" x 18"
	104502	Ear Protection Area	14" x 18"
	104503	Eye Protection Area	14" x 18"
	104504	Hard Hat Area with Symbol	14" x 18"
	104505	Safety Goggles Required	14" x 18"
	104506	Biohazard with Symbol	14" x 18"
	104510	Safety Glasses Required	14" x 18"

# Premium 5S Marking Kits

Brady's Premium 5S Marking Kits provide everything you need to 5S your facility, enhancing workplace organization & efficiency.

## Kit includes:

ToughStripe® floor marking tapes

- 4 Rolls of 2" floor tape (yellow, red, blue, green)
- 4 Packages of 2" L-shaped corner marks (yellow, red, blue, green)

Toolboard / workbench marking tapes (1 roll of black, red, blue, green)

- 4 Rolls of 12" shadow vinyl (black, red, blue, green)
- 4 Rolls of ½" border tape (black, red, blue, green)
- 4 Rolls of ½" L-shaped corner marks (black, red, blue, green)

## Kit with IDXPRT™ Printer

### All Contents of Premium 5S Marking Kit, plus:

- IDXPRT™ Continuous Only Label Printer
- AC adaptor
- 3 Black on white tape cartridges (½", 1", 1½")
- 1 Black on yellow tape cartridge (1½")
- 1 Red on white tape cartridge (1½")

## Kit with BMP®71 Label Printer

### All Contents of Premium 5S Marking Kit, plus:

- BMP®71 Printer with hard carrying case
- Charger/AC power adaptor
- 3 White vinyl tape cartridges (½", 1", 2")
- 1 Yellow vinyl tape cartridge (2")
- 2 Ribbon cartridges (black, red)

Catalog No.	Description
1242871	Premium Kit
1242902	Premium Kit with IDXPRT™ Printer
1242903	Premium Kit with BMP®71 Printer



\* Not all Kit contents shown

Visit [www.BradyID.com/ToughStripe](http://www.BradyID.com/ToughStripe) to find more information on ToughStripe® Floor Marking, including:

- Application Video and Instruction Sheet
- 5S Floor Marking Color Standard
- Product Testing Video
- Sample Packs
- And more!



Y1244471 MS1244471

USA  
1-888-272-3946  
[www.BradyID.com](http://www.BradyID.com)

Canada  
1-800-263-6179  
[www.BradyCanada.ca](http://www.BradyCanada.ca)

Mexico  
1-800-262-7777  
[www.BradyLatinAmerica.com](http://www.BradyLatinAmerica.com)