




Captair® Flow 321



Assembly Instructions Notice de Montage Montage Beschreibung Instrucciones de Montaje Istruzioni per il Montaggio








www.erlab.com
sales@erlab.net

Europe



-  +33 (0)2 32 09 55 80
-  +44 (0) 1722 341 940
-  (0) 800 330 47 31
-  +34 93 673 24 74
-  +39 (0) 2 89 00 771

North America

-  +1 (800) 964 4434



Asia

-  + 86 (0) 512 5781 4085
-  +60 (0)7 3 555 724




- A** Work surface I / Plan de travail I / Arbeitsplatte Nr I /
Superficie de trabajo I / Piano di Lavoro I
- B** Back panel / Panneau arrière / Rückwand / Panel trasero /
Pannello posteriore
- C** Side panel / Panneau latéral / Seitenwand / Panel lateral /
Pannello laterale
- CI**
- D** Ceiling and control panel / Plafond et panneau de contrôle /
Kontrollanzeige / Techo y panel de control / Soffito e pannello
di controllo
- E** Acrylic front panel / Façade acrylique / Acrylfassade / Panel
frontal acrílico / Facciata in acrilico


- F** Casing / Carter / Gehäuse / Cártel / Coperchio
- G** Filters / Filtres / Filter / Filtrós / Filtri
- H** Fan module / Boîtier de ventilation / Ventilatorengehäuse /
Módulo ventilador / Cassone di ventilazione
- K** Air flow meter / Balance à air / Luftstrommesser / Medidor
de flujo de aire / Anemometro meccanico
- L** Pre-filter / Pré-filtre / Vorfilter / Prefiltro / Pre-filtro
- M** FLEXTM Technology / Technologie FLEXTM /
FLEXTM Technologie / Tecnologia FLEXTM / Tecnología FLEXTM
- N** Laminar flux




D x 1




H x 1




E x 1




F x 2




C1 x 1




C x 1




B x 1




N x 1




L IP







I x 15




P x 2



J x 1




K x 1




M

**FLEX™ Technology / Technologie FLEX™ /
FLEX™ Technologie / Tecnologia FLEX™ / Tecnología FLEX™**


Patent Pending




**Molecular filter
Filtre moléculaire
Molekularfilter
Filtro Molecular
Filtro Molecolare**



**HEPA H14 filter
Filtre HEPA H14
HEPA H14 Filter
Filtro HEPA H 14
Filtro HEPA H 14**




321	IP		x1
	IPIC	x1	x1



Options - Optionen - Opciones - Opzioni


A1

Work surface in phenolic resin
Plan de travail En résine phénolique
Arbeitsplatte aus phenolischem Harz
Superficie de trabajo En resina fenólica
Piano di Lavoro In Resina Fenolica




A2


Work surface in stainless steel 304 L
Plan de travail en Inox 304 L
Arbeitsplatte aus Edelstahl 304 L
Superficie de trabajo en Acero inoxidable 304 L
Piano di lavoro in Inox 304 L



B2


Transparent back panel
Panneau arrière transparent
Durchsichtige Rückwand
Panel trasero transparente
Pannello posteriore trasparente






1

A1



A2




2

A

C1



x 1




3

B1 / B2

x 3






4

C




x 4




5

D

x 4







6


N

P x 2




7


7-1




7-2




7-3




7-4




7-5






8




9


E

x 3





10



11



M

**FLEX[™] Technology / Technologie FLEX[™] /
FLEX[™] Technologie / Tecnología FLEX[™] / Tecnología FLEX[™]**



Patent Pending


**Molecular filter
Filtre moléculaire
Molekularfilter
Filtro Molecular
Filtro Molecolare**

**HEPA H14 filter
Filtre HEPA H14
HEPA H14 Filter
Filtro HEPA H 14
Filtro HEPA H 14**




32l	IP		x1
	IPIC	x1	x1







12

M







13




14








15

J



16





EUROPE

France & DOMTOM, Monaco



Erlab D.F.S. S.A.S.

Parc d'Affaires des Portes BP 403
27104 Val de Reuil Cedex
France
Tel. : +33 (0)2 32 09 55 80
Fax. : +33 (0)2 32 09 55 90

Ventes@erlab.net

Spain, Andorra, Portugal



Erlab S.L.

Pol. Ind. Sur-Passaje Newton 3A
08754 El Papiol-Barcelona
Spain
Tel. : +34 93 673 24 74
Fax. : +34 93 673 24 76

Ventas@erlab.net
sales@erlab.net

United Kingdom, Belgium Netherland, Irlanda, Norway, Sweden Finland, Denmark



Erlab D.F.S. S.A.S.

Tel. : +44 (0)1722 341 940
Fax. : +44 (0)1722 341 950

SalesUK@erlab.net
sales@erlab.net

Germany, Switzerland Austria, Liechtenstein



Erlab D.F.S. S.A.S.

from Deutschland:
Tel.: 0800 330 47 31
Fax: 0800 330 47 32
from Schweiz or Österreich:
Tel. : +33 (0)2 32 09 55 80
Fax. : +33 (0)2 32 09 55 90

Verkauf@erlab.net
sales@erlab.net

Italy, Vatican, Poland Romania, Hungary Czech Republic, Slovakia



Erlab D.F.S. S.A.S.

Tel. : +39 (0)2 89 00 771
Fax. : +39 (0)2 72 097 812

Vendite@erlab.net
sales@erlab.net

North AMERICA

U.S.A., Canada



Erlab inc.

388 Newburyport Turnpike
Rowley, MA 01969
Tel : +1 (800) 964-4434
Fax : +1 (978) 948-3354

captairsales@erlab.com

ASIA

China



Kunshan Erlab D.F.S. co Ltd.

100 Liu Shi Jing, road
Kunshan Development Zone
Jiangsu Province
Penglang - P.R. China 215333
Tel. : +86 (0) 512 5781 4085
Fax. : +86 (0) 512 5781 4082

Sales.china@erlab.com.cn

Malaysia



Erlab asia sdn bhd

25 Jalan Firma - /I Kawasan Perindustrian
Tebrau - 81 100 Johor Bahru,
Johor State
Tel. : +60 (0)7 3 555 724
Fax. : +60 (0)7 3 552 810

Erlab@tm.net.my

Other country?
Contact us: **sales@erlab.net**

www.erlab.com