



## PRODUCT INFORMATION

# HinfI

**#ER0803** 10000 U

**Lot:** \_\_\_\_ **Expiry Date:** \_\_

5'...**G↓A** N T C...3'  
3'...**C T N A↑G**...5'

Concentration: 50 U/μL  
Source: *Haemophilus influenzae* Rf  
Supplied with: 2 x 1 mL of 10X Buffer R  
1 mL of 10X Buffer Tango

**Store at -20°C**



In total 4 vials.

BSA included

[www.thermoscientific.com/onebio](http://www.thermoscientific.com/onebio)

## RECOMMENDATIONS

**1X Buffer R** (for 100% HinfI digestion)

10 mM Tris-HCl (pH 8.5), 10 mM MgCl<sub>2</sub>, 100 mM KCl,  
0.1 mg/mL BSA.

**Incubation temperature**

37°C.

**Unit Definition**

One unit is defined as the amount of HinfI required to digest 1 μg lambda DNA in 1 hour at 37°C in 50 μL of recommended reaction buffer.

**Dilution**

Dilute with Dilution Buffer (#B19): 10 mM Tris-HCl (pH 7.4 at 25°C), 100 mM KCl, 1 mM EDTA, 1 mM DTT, 0.2 mg/mL BSA and 50% glycerol.

**Double Digests**

Thermo Scientific Tango Buffer is provided to simplify buffer selection for double digests. 98% of Thermo Scientific restriction enzymes are active in a 1X or 2X concentration of Tango™ Buffer. Please refer to [www.thermoscientific.com/doubledigest](http://www.thermoscientific.com/doubledigest) to choose the best buffer for your experiments.

1X Tango Buffer: 33 mM Tris-acetate (pH 7.9 at 37°C), 10 mM magnesium acetate, 66 mM potassium acetate, 0.1 mg/mL BSA.

Rev.10



53

## Storage Buffer

Hinfl is supplied in: 10 mM Tris-HCl (pH 7.4 at 25°C), 100 mM KCl, 1 mM DTT, 1 mM EDTA, 0.2 mg/mL BSA and 50% glycerol.

## Recommended Protocol for Digestion

- Add:  
nuclease-free water      16 µL  
10X Buffer R                2 µL  
DNA (0.5-1 µg/µL)        1 µL  
Hinfl                         0.5-2 µL\*
- Mix gently and spin down for a few seconds.
- Incubate at 37°C for 1-16 hours.

The digestion reaction may be scaled either up or down.

## Recommended Protocol for Digestion of PCR Products Directly after Amplification

- Add:  
PCR reaction mixture      10 µL (~0.1-0.5 µg of DNA)  
nuclease-free water        18 µL  
10X Buffer R                2 µL  
Hinfl                         1-2 µL\*
- Mix gently and spin down for a few seconds.
- Incubate at 37°C for 1-16 hours.

\* This volume of the enzyme is recommended for preparations of standard concentrations (10 U/µL), whereas HC enzymes (50 U/µL) should be diluted with the Dilution Buffer to obtain 10 U/µL concentration.

## Thermal Inactivation

Hinfl is inactivated by incubation at 65°C for 20 min.

## ENZYME PROPERTIES

### Enzyme Activity in Thermo Scientific REase Buffers, %

B	G	O	R	Tango	2X Tango
0-20	20-50	50-100	100	50-100	50-100

## Methylation Effects on Digestion

Dam: never overlaps – no effect.  
Dcm: never overlaps – no effect.  
CpG: may overlap – cleavage impaired.  
EcoKI: never overlaps – no effect.  
EcoBI: may overlap – blocked.

## Stability during Prolonged Incubation

A minimum of 0.1 units of the enzyme is required for complete digestion of 1 µg of lambda DNA in 16 hours at 37°C.

## Compatible Ends

G↓A(A/T)TC – PfiI.

## Number of Recognition Sites in DNA

λ	ΦX174	pBR322	pUC57	pUC18/19	pTZ19R/U	M13mp18/19
148	21	10	5	6	9	27

For **CERTIFICATE OF ANALYSIS** see back page

# CERTIFICATE OF ANALYSIS

## Overdigestion Assay

No detectable change in the specific fragmentation pattern is observed after a 160-fold overdigestion with HinfI (10 U/μg lambda DNA x 16 hours).

## Ligation and Recleavage (L/R) Assay

The ligation and recleavage assay was replaced with LO test after validating experiments showed LO test ability to trace nuclease and phosphatase activities with sensitivity that is higher than L/R by a factor of 100.

## Labeled Oligonucleotide (LO) Assay

No detectable degradation of single-stranded or double-stranded labeled oligonucleotides occurred during incubation with 10 units of HinfI for 4 hours.

Quality authorized by:

 Jurgita Zilinskiene

## **PRODUCT USE LIMITATION**

This product is developed, designed and sold exclusively *for research purposes and in vitro use only*. The product was not tested for use in diagnostics or for drug development, nor is it suitable for administration to humans or animals.

Please refer to [www.thermoscientific.com/onebio](http://www.thermoscientific.com/onebio) for Material Safety Data Sheet of the product.

© 2012 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries.

