

eBioscience™ Anti-Human Foxp3 Staining Set APC

Catalog Number: 77-5774

Also known as: Forkhead Box P3, Scurfin, JM2

RUO: For Research Use Only. Not for use in diagnostic procedures.

Product Information

Contents: eBioscience™ Anti-Human Foxp3 Staining Set APC

Catalog Number: 77-5774

Clone: 236A/E7 Set

Host/Isotype: Mouse IgG1



Temperature Limitation: Store at 2-8°C. Light-sensitive material. Use within 6 months of opening or by date indicated on the bottle.



Batch Code: Refer to vial



Use By: Refer to vial



Contains sodium azide and formaldehyde

Description

This Anti-Human Foxp3 Staining Set contains the buffers and monoclonal antibody necessary to successfully stain and identify Foxp3+ cells. The 236A/E7 monoclonal antibody reacts with human Foxp3, also known as FORKHEAD BOX P3, SCURFIN, and JM2. Foxp3 is a 49-55 kDa protein and a member of the forkhead/winged-helix family of transcription factors. It was identified as the gene responsible for the X-linked lymphoproliferative disease observed in scurfy (sf) mice and in the human disorder, X-linked autoimmunity-allergic dysregulation syndrome (XLAAD). Constitutive expression of Foxp3 mRNA has been shown in CD4+CD25+ regulatory T cells (Treg), and ectopic expression of Foxp3 in CD4+CD25- cells imparts a Treg phenotype in these cells.

The 236A/E7 antibody has been shown to crossreact with rhesus macaque, sooty mangabey, and cynomolgus Foxp3. 236A/E7 recognizes a different epitope of Foxp3 than PCH101 and 150D/E4.

Components

Fixation/Permeabilization Concentrate (4X) (cat. 00-5123): 30 mL, store at 2-8°C. Avoid agitation.

Fixation/Permeabilization Diluent (cat. 00-5223): 100 mL, store at 2-8°C.

Permeabilization Buffer (10X) (cat. 00-8333): 100 mL, store at 2-8°C. *Note: The 10X Permeabilization Buffer has a natural tendency to precipitate, however, its function is not affected by this. To clarify, the solution can be filtered after dilution to 1x working solution.*

Normal Mouse Serum (cat. 24-5544): 100 µL, store at 2-8°C.

Anti-Human Foxp3 APC (clone 236A/E7, cat. 17-4777): 25 tests, store at 2-8°C. Light-sensitive material.

Applications Reported

This Anti-Human Foxp3 Staining Set has been reported for use in intracellular staining followed by flow cytometric analysis.

Applications Tested

This Anti-Human Foxp3 Staining Set has been pre-titrated and tested by intracellular staining and flow cytometric analysis of normal human peripheral blood cells according to the protocol below. The 236A/E7 antibody can be used at 20 µL (0.125 µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test.

References

Green AM, Mattila JT, Bigbee CL, Bongers KS, Lin PL, Flynn JL. CD4(+) regulatory T cells in a cynomolgus macaque model of Mycobacterium tuberculosis infection. J Infect Dis. 2010 Aug 15;202(4):533-41. (236A/E7, IHC-paraffin, crossreactivity to cynomolgus and sooty mangabey, PubMed)

Estes JD, Gordon SN, Zeng M, Chahroudi AM, Dunham RM, Staprans SI, Reilly CS, Silvestri G, Haase AT. Early resolution of acute immune activation and induction of PD-1 in SIV-infected sooty mangabeys distinguishes nonpathogenic from pathogenic infection in rhesus macaques. J Immunol. 2008 May 15;180(10):6798-807. (236A/E7, IHC-paraffin, crossreactivity to rhesus, PubMed)

Lim, H.W., P. Hillsamer, A.H. Banham, and C.H. Kim. Cutting Edge: Direct Suppression of B cells by CD4+CD25+

Not for further distribution without written consent.

Copyright © 2016 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified.

Tel: 888.999.1371 or 858.642.2058 • Fax: 858.642.2046 • thermofisher.com/ebioscience • info@ebioscience.com

eBioscience™ Anti-Human Foxp3 Staining Set APC

Catalog Number: 77-5774

Also known as: Forkhead Box P3, Scurfin, JM2

RUO: For Research Use Only. Not for use in diagnostic procedures.

Regulatory T cells. J Immunol. 2005 Oct 1;175(7):4180-3. **(236A/E7)**, IHC-frozen, PubMed)

Roncador G, Brown PJ, Maestre L, Hue S, Martinez-Torrecuadrada JL, Ling KL, Pratap S, Toms C, Fox BC, Cerundolo V, Powrie F, Banham AH. Analysis of FOXP3 protein expression in human CD4+CD25+ regulatory T cells at the single-cell level. Eur J Immunol. 2005 Jun;35(6):1681-91. **(236A/E7)**, IC Flow, IHC-paraffin, PubMed)

Related Products

00-5523 eBioscience™ Foxp3 / Transcription Factor Staining Buffer Set

11-0049 eBioscience™ Anti-Human CD4 FITC (RPA-T4)

12-0259 eBioscience™ Anti-Human CD25 PE (BC96)

17-4714 eBioscience™ Mouse IgG1 K Isotype Control APC (P3.6.2.8.1)

72-5774 eBioscience™ Anti-Human Foxp3 Staining Set PE (236A/E7 Set)

Not for further distribution without written consent.

Copyright © 2016 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified.

Tel: 888.999.1371 or 858.642.2058 • Fax: 858.642.2046 • thermofisher.com/ebioscience • info@ebioscience.com

Foxp3 Staining Protocol

Introduction

The following protocol allows the simultaneous analysis of cell surface molecules and intracellular antigens, including nuclear antigens such as Foxp3, at the single-cell level. This protocol combines fixation and permeabilization into a single step. This protocol is recommended for the detection of nuclear antigens such as transcription factors but is also useful for the detection of many cytokines. For compatibility of the Foxp3/Transcription Factor Staining Buffer Set (Cat. No. 00-5523) with cytokine antibodies, please see our Buffer Compatibility chart online: [Intracellular Buffer Selection](#).

Protocol

Materials needed

- 12x75 mm round bottom test tubes or 96-well V- or U-bottom plates
- Flow Cytometry Staining Buffer (Cat. No. 00-4222)
- [Optional] Fixable Viability Dyes
 - Fixable Viability Dye eFluor™ 455UV (Cat. No. 65-0868)
 - Fixable Viability Dye eFluor™ 450 (Cat. No. 65-0863)
 - Fixable Viability Dye eFluor™ 506 (Cat. No. 65-0866)
 - Fixable Viability Dye eFluor™ 520 (Cat. No. 65-0867)
 - Fixable Viability Dye eFluor™ 660 (Cat. No. 65-0864)
 - Fixable Viability Dye eFluor™ 780 (Cat. No. 65-0865)

Buffers and solution preparation

- Prepare fresh Fixation/Permeabilization working solution by diluting the Fixation/Permeabilization Concentrate (1 part) with Fixation/Permeabilization Diluent (3 parts). You will need 1 mL of the Fixation/Permeabilization working solution for each sample, if staining in tubes. Do not store this buffer more than 1 day.
- Prepare a 1X working solution of Permeabilization Buffer by diluting the 10X concentrate with distilled water prior to use. You will need 8.5 mL of Permeabilization Buffer for each sample, if staining in tubes. Store excess at 2-8°C for up to 1 week.

Experimental procedure in tubes

1. Prepare cells of interest for evaluation of intracellular proteins. Refer to Best Protocols: 'Cell Preparation for Flow Cytometry.'
2. [Optional] To eliminate potential artifacts due to dead cell contamination, we recommend the use of a Fixable Viability Dye to allow the exclusion of dead cells from the analysis (See Best Protocols: Protocol C: 'Staining Dead Cells with Thermo Fisher Fixable Viability Dyes' staining protocol for instructions for use).
3. Stain cell surface antigen(s) as described in Best Protocols for antibodies conjugated to organic fluorochromes: 'Staining cell surface antigens' protocol.
4. After the last wash, discard the supernatant and pulse vortex the sample to completely dissociate the pellet.
5. Add 1 mL of Fixation/Permeabilization working solution to each tube and pulse vortex.
6. Incubate for 30-60 minutes at room temperature and protect samples from light.
7. Add 2 mL of 1X Permeabilization Buffer to each tube.
8. Centrifuge samples at 300-400 xg for 5 minutes at room temperature, then discard the supernatant.
9. [Optional] Repeat Steps 7-8.
10. Resuspend pellet in 100 µL of 1X Permeabilization Buffer. This is typically the residual volume after decanting.
11. [Optional] Block with 2% normal mouse or rat serum by adding 2 µL directly to the cells. Incubate for 15 minutes at room temperature.
12. Without washing, add 5 µL of fluorochrome-conjugated Foxp3 antibody to cells and incubate for at least 30 minutes at room temperature and protect samples from light.
13. Add 2 mL of 1X Permeabilization Buffer to each tube.
14. Centrifuge samples at 300-400 xg for 5 minutes at room temperature, then discard the supernatant.
15. Repeat Steps 13-14.
16. Resuspend stained cells in an appropriate volume of Flow Cytometry Staining Buffer and acquire samples on a flow cytometer.

Experimental procedure in 96-well plate

1. Prepare cells of interest for evaluation of intracellular proteins. Refer to Best Protocols: 'Cell Preparation for Flow Cytometry.'
2. [Optional] To eliminate potential artifacts due to dead cell contamination, we recommend the use of a Fixable Viability Dye to allow the exclusion of dead cells from the analysis (See Best Protocols: Protocol C: 'Staining Dead Cells with Fixable Viability Dyes' staining protocol for instructions for use).
3. Stain cell surface antigen(s) as described in Best Protocols for antibodies conjugated to organic fluorochromes: 'Staining cell surface antigens' protocol.
4. After the last wash, discard the supernatant and pulse vortex the sample to completely dissociate the pellet.
5. Add 200 μ L of Fixation/Permeabilization working solution to each well. It is ideal to add the solution such that the cells are fully resuspended in the solution. Pipetting is an option.
6. Incubate for 30-60 minutes at room temperature and protect samples from light.
7. Centrifuge samples at 300-400 xg at room temperature for 5 minutes, then discard the supernatant.
8. Add 200 μ L of 1X Permeabilization Buffer to each well.
9. Centrifuge samples at 300-400 xg for 5 minutes at room temperature, then discard the supernatant.
10. Repeat Steps 8-9.
11. Resuspend pellet in residual volume and adjust volume to about 100 μ L with 1X Permeabilization Buffer.
12. [Optional] Block with 2% normal mouse or rat serum by adding 2 μ L directly to the cells. Incubate for 15 minutes at room temperature.
13. Without washing, add 5 μ L of fluorochrome-conjugated Foxp3 antibody to cells and incubate for at least 30 minutes at room temperature and protect samples from light.
14. Add 200 μ L of 1X Permeabilization Buffer to each well.
15. Centrifuge samples at 300-400 xg for 5 minutes at room temperature, then discard the supernatant.
16. Repeat Steps 14-15.
17. Resuspend stained cells in an appropriate volume of Flow Cytometry Staining Buffer and acquire samples on a flow cytometer.

Documentation and support

Customer and technical support

Visit thermofisher.com/support for the latest in services and support, including:

- Worldwide contact telephone numbers
- Product support, including:
 - Product FAQs
 - Software, patches, and updates
- Order and web support
- Product documentation, including:
 - User guides, manuals, and protocols
 - Certificates of Analysis
 - Safety Data Sheets (SDSs; also known as MSDSs)

Note: For SDSs for reagents and chemicals from other manufacturers, contact the manufacturer.

Limited product warranty

Life Technologies Corporation and/or its affiliate(s) warrant their products as set forth in the Life Technologies' General Terms and Conditions of Sale found on Life Technologies' website at www.thermofisher.com/us/en/home/global/terms-and-conditions.html. If you have any questions, please contact Life Technologies at thermofisher.com/support.

The information in this guide is subject to change without notice.

DISCLAIMER: TO THE EXTENT ALLOWED BY LAW, LIFE TECHNOLOGIES AND/OR ITS AFFILIATE(S) WILL NOT BE LIABLE FOR SPECIAL, INCIDENTAL, INDIRECT, PUNITIVE, MULTIPLE, OR CONSEQUENTIAL DAMAGES IN CONNECTION WITH OR ARISING FROM THIS DOCUMENT, INCLUDING YOUR USE OF IT.

Important Licensing Information: These products may be covered by one or more Limited Use Label Licenses. By use of these products, you accept the terms and conditions of all applicable Limited Use Label Licenses.

Corporate entity: Life Technologies | Carlsbad, CA 92008 USA | Toll Free in USA 1.800.955.6288

©2017 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. All other trademarks are properties of their respective owners.

For support visit thermofisher.com/support or email techsupport@lifetech.com

thermofisher.com

23 January 2017

ThermoFisher
SCIENTIFIC