Thermo SCIENTIFIC

PRODUCT INFORMATION

NcoI

#ER0571 500 U

Lot: ___ **Expiry Date: _**

5'…**C↓C A T G G**…3'
3'…**G G T A C↑C**…5'

Concentration: 10 U/µL
Supplied with: 1 mL of 10X Buffer Tango

Store at -20°C

BSA included

www.thermoscientific.com/onebio

RECOMMENDATIONS

1X Thermo Scientific Tango Buffer (for 100% NcoI digestion)
33 mM Tris-acetate (pH 7.9), 10 mM magnesium acetate, 66 mM potassium acetate, 0.1 mg/mL BSA.

Incubation temperature
37°C.

Unit Definition
One unit is defined as the amount of NcoI required to digest 1 µg of lambda DNA in 1 hour at 37°C in 50 µL of recommended reaction buffer.

Dilution
Dilute with Dilution Buffer (#B19): 10 mM Tris-HCl (pH 7.4 at 25°C), 100 mM KCl, 1 mM EDTA, 1 mM DTT, 0.2 mg/mL BSA and 50% glycerol.

Double Digests
Tango™ Buffer provided simplifies buffer selection for double digests. 98% of Thermo Scientific restriction enzymes are active in a 1X or 2X concentration of Tango Buffer. Please go to www.thermoscientific.com/doubledigest to choose the best buffer for your experiments.

Storage Buffer
NcoI is supplied in: 10 mM Tris-HCl (pH 7.5 at 25°C), 50 mM KCl, 0.1 mM EDTA, 1 mM DTT, 0.2 mg/mL BSA and 50% glycerol.

Rev.10

Recommended Protocol for Digestion

- Add:

nuclease-free water	16 µL
10X Buffer Tango	2 µL
DNA (0.5-1 µg/µL)	1 µL
NcoI	0.5-2 µL*

- Mix gently and spin down for a few seconds.
- Incubate at 37°C for 1-16 hours*.

The digestion reaction may be scaled either up or down.

Recommended Protocol for Digestion of PCR Products Directly after Amplification

- Add:

PCR reaction mixture	10 µL (~0.1-0.5 µg of DNA)
nuclease-free water	18 µL
10X Buffer Tango	2 µL
NcoI	1-2 µL*

- Mix gently and spin down for a few seconds.
- Incubate at 37°C for 1-16 hours*.

---

* *See* Overdigestion Assay.

Thermal Inactivation

NcoI is inactivated by incubation at 65°C for 20 min.

ENZYME PROPERTIES

Enzyme Activity in Thermo Scientific REase Buffers, %

B	G	O	R	Tango	2X Tango
20-50	20-50	20-50	50-100	100	100

Methylation Effects on Digestion

Dam: never overlaps – no effect.
Dcm: never overlaps – no effect.
CpG: never overlaps – no effect.
EcoKI: never overlaps – no effect.
EcoBI: never overlaps – no effect.

Stability during Prolonged Incubation

A minimum of 0.1 units of the enzyme is required for complete digestion of 1 µg of DNA in 16 hours at 37°C.

Digestion of Agarose-embedded DNA

A minimum 5 units of the enzyme is required for complete digestion of 1 µg of agarose-embedded lambda DNA in 16 hours.

Compatible Ends

AflIII, PscI, BtgI, Eco130I, FatI, PagI.

Number of Recognition Sites in DNA

λ	ΦX174	pBR322	pUC57	pUC18/19	pTZ19R/U	M13mp18/19
4	0	0	0	0	0	0

For **CERTIFICATE OF ANALYSIS** *see* back page

CERTIFICATE OF ANALYSIS

Overdigestion Assay

No detectable change in the specific fragmentation pattern is observed after a 80-fold overdigestion with NcoI (5 U/µg lambda DNA × 16 hours).

Ligation and Recleavage (L/R) Assay

The ligation and recleavage assay was replaced with LO test after validating experiments showed LO test ability to trace nuclease and phosphatase activities with sensitivity that is higher than L/R by a factor of 100.

Labeled Oligonucleotide (LO) Assay

No detectable degradation of single-stranded or double-stranded labeled oligonucleotides occurred during incubation with 10 units of NcoI for 4 hours.

Blue/White (B/W) Cloning Assay

The B/W assay was replaced with LO test after validating experiments showed LO test ability to detect nuclease and phosphatase activities with sensitivity that equals to that of B/W test.

Quality authorized by:  Jurgita Zilinskiene

PRODUCT USE LIMITATION

This product is developed, designed and sold exclusively *for research purposes and in vitro use only.* The product was not tested for use in diagnostics or for drug development, nor is it suitable for administration to humans or animals.

Please refer to www.thermoscientific.com/onebio for Material Safety Data Sheet of the product.