

#### PRODUCT INFORMATION

# HhaT

#ER1851 2000 U

**Expiry Date:** Lot: \_\_\_\_

5'...**G C G↓C**...3' 3'...**C**↑**G C G**...5'

Concentration: 10 U/μL

Source: Haemophilus haemolyticus 1 mL of 10X Buffer Tango Supplied with:

Store at -20°C











BSA included

www.thermoscientific.com/onebio

#### RECOMMENDATIONS

**1X Thermo Scientific Tango Buffer** (for 100% Hhal digestion)

33 mM Tris-acetate (pH 7.9), 10 mM magnesium acetate, 66 mM potassium acetate, 0.1 mg/mL BSA.

# **Incubation temperature**

37°C.

#### **Unit Definition**

One unit is defined as the amount of Hhal required to digest 1 µg of lambda DNA in 1 hour at 37°C in 50 µL of recommended reaction buffer.

#### Dilution

Dilute with Dilution Buffer (#B19): 10 mM Tris-HCl (pH 7.4 at 25°C), 100 mM KCl, 1 mM EDTA, 1 mM DTT, 0.2 mg/mL BSA and 50% glycerol.

#### **Double Digests**

Tango<sup>™</sup> Buffer provided simplifies buffer selection for double digests. 98% of Thermo Scientific restriction enzymes are active in a 1X or 2X concentration of Tango Buffer. Please go to www.thermoscientific.com/doubledigest to choose the best buffer for your experiments.

# **Storage Buffer**

Hhal is supplied in: 10 mM Tris-HCl (pH 7.4 at 25°C), 100 mM KCl, 1 mM EDTA, 1 mM DTT, 0.2 mg/mL BSA and 50% glycerol.



# **Recommended Protocol for Digestion**

• Add:

nuclease-free water  $16~\mu L$  10X~Buffer~Tango  $2~\mu L$   $DNA~(0.5-1~\mu g/\mu L)$   $1~\mu L$  Hhal  $0.5-2~\mu L$ 

- Mix gently and spin down for a few seconds.
- Incubate at 37°C for 1-16 hours.

The digestion reaction may be scaled either up or down.

# **Recommended Protocol for Digestion of PCR Products Directly after Amplification**

• Add:

PCR reaction mixture 10  $\mu$ L (~0.1-0.5  $\mu$ g of DNA) nuclease-free water 18  $\mu$ L 10X Buffer Tango 2  $\mu$ L Hhal 1-2  $\mu$ L

- Mix gently and spin down for a few seconds.
- Incubate at 37°C for 1-16 hours.

#### **Thermal Inactivation**

Hhal is not inactivated by incubation at 80°C for 20 min.

#### **Inactivation Procedure**

- To prepare the digested DNA for electrophoresis:
  - stop the digestion reaction by adding 0.5 M EDTA, pH 8.0 (#R1021), to achieve a 20 mM final concentration. Mix thoroughly, add an electrophoresis loading dye and load onto gel.
- To prepare DNA suitable for further enzymatic reactions:
  - extract with phenol/chloroform, precipitate with ethanol or isopropanol, wash the pellet with 75% cold ethanol and air-dry;
  - dissolve DNA in either nuclease-free water, TE buffer, or a buffer suitable for further applications;
  - check the DNA concentration in the solution.

For **ENZYME PROPERTIES** and **CERTIFICATE OF ANALYSIS**see back page

#### **ENZYME PROPERTIES**

**Enzyme Activity in Thermo Scientific REase Buffers, %** 

В	G	0	R	Tango	2X Tango
50-100	50-100	20-50	20-50	100	20-50

# **Methylation Effects on Digestion**

Dam: never overlaps — no effect.

Dcm: never overlaps — no effect.

CpG: completely overlaps — blocked. EcoKI: never overlaps — no effect. EcoBI: never overlaps — no effect.

# **Stability during Prolonged Incubation**

A minimum of 0.1 units of the enzyme is required for complete digestion of 1  $\mu$ g of lambda DNA in 16 hours at 37°C.

# **Compatible Ends**

# **Number of Recognition Sites in DNA**

λ	ФХ174	pBR322	pUC57	pUC18/19	pTZ19R/U	M13mp18/19
215	18	31	17	17	20	26

#### **CERTIFICATE OF ANALYSIS**

# **Overdigestion Assay**

No detectable change in the specific fragmentation pattern is observed after a 160-fold overdigestion with Hhal (10 U/ $\mu$ g lambda DNA x 16 hours).

# **Ligation and Recleavage (L/R) Assay**

The ligation and recleavage assay was replaced with LO test after validating experiments showed LO test ability to trace nuclease and phosphatase activities with sensitivity that is higher than L/R by a factor of 100.

# **Labeled Oligonucleotide (LO) Assay**

No detectable degradation of single-stranded or doublestranded labeled oligonucleotides occurred during incubation with 10 units of Hhal for 4 hours.

**Quality authorized by:** 



Jurgita Zilinskiene

#### **PRODUCT USE LIMITATION**

This product is developed, designed and sold exclusively *for research purposes and in vitro use only.* The product was not tested for use in diagnostics or for drug development, nor is it suitable for administration to humans or animals.

Please refer to <a href="https://www.thermoscientific.com/onebio">www.thermoscientific.com/onebio</a> for Material Safety Data Sheet of the product.

© 2012 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries.