

Thermo Fisher Scientific hereby certifies that the product identified below is manufactured and/or distributed according to the requirements of product and quality specifications as maintained in our quality management system which is compliant to ISO 13485 (BSI Certificate Number: FM 653694) or ISO 9001 (BSI Certificate Number: FM 743358) in Rochester, NY, USA.



 Alan E. Hatch
 Sr. Quality Manager
 06/07/2025

 The following information represents Product Certification for: Item#: **374222**

 Description: **5mL Cryobank Uncoded Racked ST**

 Lot#: **1426783**

 Use Before: **04/17/2030**

 Manufactured: **04/17/2025**

| Part Number | Description | Common Name | DMF# | Cytotoxicity | USP Class VI | FDA Compliance - 21 CFR |
|-------------|-------------------------------------|---------------------------|-------|--------------|--------------|-----------------------------------------------------------------------|
| 1-0025-71 | VIAL, CRYOBANK, 5.0mL, W/BC HEAD | COMPONENT PART | | | | |
| 8-0071-22 | Resin, PP, Black, INJ, Cryobank | COMPONENT PART | | | | |
| 14117MR | RESIN, PP, HIMONT PF-511 | PP, HOMO, NATURAL, INJ. | 26106 | PASSED | PASSED | 177.1520(a)(1)(i) and (c)1.1a, 177.1520(b), use conditions A-H |
| 14288MR | COLORANT, BLACK, PP | COLORANT, BLACK, PP, INJ. | N/A | N/A | N/A | N/A |
| 8-0028-04 | RESIN, PPCO, RAD STER, INJ | POLYPROPYLENE COPOLYMER | 7478 | PASSED | PASSED | 177.1520 (a)(3)(i) & (c)3.1(a)except for cooking, (useconditions C-H) |
| 1-0025-73 | CAP, CRYOVIAL 2/5mL NON-PIERCEABLE | COMPONENT PART | | | | |
| 8-0028-04 | RESIN, PPCO, RAD STER, INJ | POLYPROPYLENE COPOLYMER | 7478 | PASSED | PASSED | 177.1520 (a)(3)(i) & (c)3.1(a)except for cooking, (useconditions C-H) |
| 8-0005-22 | RESIN, TPV, NAT, 45 DURO SANTOPRENE | THERMOPLASTIC RUBBER | 12719 | PASSED | PASSED | N/A |

If N/A appears in any of the columns above it means the information is not available. Any item listed as "COMPONENT PART" will show blank in the DMF#, Cytotoxicity, USP Class VI, and FDA Compliance Information columns.

If the word "PASSED" appears in the USP Class VI column next to the resin listing, this material has passed USP Class VI requirements, latest Volume, as part of our initial test approval protocol.

If the word "PASSED" appears in the Cytotoxicity column next to the resin listing, this material was tested and shown to be non-cytotoxic as part of our initial test approval protocol, using either mouse fibroblast L929 cells or the more sensitive human diploid lung cell lines WI-38 or MRC-5.

Product was E-Beamed Sterilized. Product was dosimetric released per ANSI/AAMI/ISO 11137 guidelines. Product was determined to be non-pyrogenic at a level < 0.5 EU/ml per USP < 85 > .

Product is certified to be free of detectable RNase/DNase contamination. This test is performed using the nuclease assay method with a detection limit of 8×10^{-7} Kunitz unit/ul for DNase and 1.9×10^{-10} Kunitz unit/ul for RNase.