Thermo Fisher

Page 1 of 3

OXOID QUALITY ASSURANCE PRODUCT SPECIFICATION

WATER PLATE COUNT AGAR (ISO) CM1012

WATER PLATE COUNT AGAR (ISO)

CM1012

Typical Formula*

Yeast extract	grams per litre	3.0
Tryptone		6.0
Agar	1	5.0

* adjusted as required to meet performance standards

Directions

Suspend 24g in 1 litre of distilled water. Bring to the boil to dissolve completely. Sterilize by autoclaving at 121° C for 15 minutes. Mix well and pour into sterile Petri dishes or hold at 45° C when using the pour plate technique.

Physical Characteristics

Straw, free-flowing powder Colour on reconstitution - straw 2-3 Moisture level - less than 7% pH 7.2 \pm 0.2 at 25°C Clarity - clear Gel strength - firm, comparable to 15.0g/litre of agar

Microbiological Tests Using Optimum Inoculum Dilution

Control Medium: Water Plate Count Agar (ISO)

Inoculation using pour plate technique

Medium is challenged with 10-300 colony-forming units

Reactions after incubation at $36 \pm 2^{\circ}C$ for 44 ± 4 hours

Enterococcus faecalis	ATCC® 19433	1-2mm straw colonies
Staphylococcus aureus	ATCC® 9144	0.5-2mm straw colonies
Pseudomonas aeruginosa	ATCC® 27853	0.5-2mm straw colonies
Proteus mirabilis	NCTC 10975	0.5-2mm straw colonies

A satisfactory result is represented by recovery of positive strains equal to or greater than 70% of the control medium.

Thermo Fisher

BT-SPEC-0254

Page 2 of 3

OXOID QUALITY ASSURANCE PRODUCT SPECIFICATION WATER PLATE COUNT AGAR (ISO) CM1012

Reactions after incubation at $22 \pm 2^{\circ}C$ for 68 ± 4 hours

Escherichia coli	ATCC® 25922	1-3mm straw colonies
Enterococcus faecalis	ATCC® 19433	1-2mm straw colonies
Staphylococcus aureus	ATCC® 9144	0.5-2mm straw colonies
Pseudomonas aeruginosa	ATCC® 27853	0.5-2mm straw colonies
Proteus mirabilis	NCTC 10975	0.5-2mm straw colonies
Bacillus subtilis	ATCC® 6633	0.5-2mm straw colonies

A satisfactory result is represented by recovery of positive strains equal to or greater than 70% of the control medium.

Testing performed in accordance with ISO11133:2014

Reactions after incubation at $36 \pm 2^{\circ}C$ for 44 ± 4 hours

Pour plate technique

Medium is challenged with 50-120 colony forming units

Escherichia coli	ATCC® 25922	WDCM00013	1-3mm straw colonies
Escherichia coli	ATCC® 8739	WDCM00012	1-3mm straw colonies
Bacillus subtilis	ATCC® 6633	WDCM00003	0.5-2mm straw colonies

A satisfactory result is represented by recovery of positive strains equal to or greater than 70% of the control medium.

Page 3 of 3

OXOID QUALITY ASSURANCE PRODUCT SPECIFICATION

WATER PLATE COUNT AGAR (ISO) CM1012

Revision History

Section / Step	Description of Change	Reason for Change	Reference
Creation of ISO11133 section	Update to include testing of ISO11133:2014	Change control	BT-CC-1210