

<b>ThermoFisher</b> SCIENTIFIC	Document Owner Department: QC	BT-SPEC-0393 Page 1 of 3
<b>OXOID QUALITY ASSURANCE PRODUCT SPECIFICATION</b>		
<b>'LAB-LEMCO' POWDER LP0029</b>		

## 'LAB-LEMCO' POWDER

LP0029

### Description

A refined product of very light colour. This extract has been specially developed for general bacteriological use wherever conventional meat extract is specified. Use with other refined ingredients, e.g. Neutralised bacteriological peptone (LP0034) to prepare culture media which do not require filtration. Generally used at a concentration of 0.2 - 1.0% (w/v) dependent on formulation.

### Physical Characteristics

Appearance	Straw, free-flowing powder
Absorbance at 450nm (2% soln.)	0.160 - 0.460 units
pH (25°C) (2% soln.)	7.2 ± 0.2
Clarity (2% soln.)	Clear, bright and free from sediment and insoluble particles.
Loss on drying	Less than or equal to 7.5%


### Chemical Characteristics

Ash	Less than or equal to 15.0%
Chloride (as NaCl)	Less than or equal to 5.0%
Formol nitrogen	2.3 – 3.6%
Total nitrogen	11.5 - 15.6%

### Microbiological Characteristics

The following tests are carried out:

Test	Solution	Organism	Incubation	Result
Fermentable carbohydrates	2% + 0.2ml of 1% phenol red solution and Durham tubes	<i>Escherichia coli</i> ATCC®25922	35 ± 2°C for 72 hours	Negative
Indole production	0.1%	<i>Escherichia coli</i> ATCC®25922	35 ± 2°C for 24 hours	<sup>1</sup> Positive
Hydrogen sulphide production	1%	<i>Salmonella enteritidis</i> ATCC®13076	35 ± 2°C for 42-48 hours	<sup>2</sup> Positive
Acetylmethylcarbinol	1% + 0.5% NaCl + 0.5% Dextrose	<i>Enterobacter aerogenes</i> ATCC®13048	37°C for 24 hours	<sup>3</sup> Positive

	Document Owner Department: QC	BT-SPEC-0393
		Page 2 of 3
OXOID QUALITY ASSURANCE PRODUCT SPECIFICATION		
'LAB-LEMCO' POWDER LP0029		

- 1 Indicator - Kovacs reagent
- 2 Indicator - lead acetate paper
- 3 Indicator - Voges-Proskauer test solutions


Test	Solution	Organism	Control Inoculum	Incubation	Result
Growth recovery in broth	2%	<i>Escherichia coli</i> ATCC®25922	10 - 100 CFU	37°C for 24 hours	Turbid growth
		<i>Staphylococcus aureus</i> ATCC®9144	10 - 100 CFU	37°C for 24 hours	Turbid growth
		<i>Enterococcus faecalis</i> ATCC®29212	10 - 100 CFU	37°C for 24 hours	Turbid growth

#### Total Viable Aerobic Count

A 2% peptone solution is further diluted and 1ml amounts are placed in sterile Petri dishes. Sterile Tryptone Soya Agar (CM0131) cooled to 44°C is added to the dilutions using the pour plate technique. Plates are incubated at 37°C for 18 hours. Colonies present are counted; they shall be less than 10,000 cfu/g.

#### Thermophilic Spore Count

A 2% peptone solution is further diluted and heated at 80°C for 10 minutes. 1ml amounts are placed in sterile Petri dishes. Sterile Tryptone Soya Agar (CM0131) cooled to 44°C is added to the dilutions using the pour plate technique. Plates are incubated at 37°C for 18 hours. Colonies present are counted; they shall be less than 1,000 spores/g.

	Document Owner Department: QC	BT-SPEC-0393
		Page 3 of 3
OXOID QUALITY ASSURANCE PRODUCT SPECIFICATION		
'LAB-LEMCO' POWDER LP0029		

## Revision History

Section / Step	Description of Change	Reason for Change	Reference
Entire document	Update to new format	Update to new format	BT-SOP-7767
Physical and chemical characteristics	Change colour from light straw to straw powder. Change loss on drying, ash and chloride to less than or equal to. Add formol nitrogen limits.	Change control	BT-CC-1811
Microbiological characteristics	Add limits for Total Viable Aerobic and Spore Count. Change non-selective medium for total viable aerobic and spore counts from Plate Count Agar (CM0325) to Tryptone Soya Agar (CM0131)		