

Thermo Fisher Scientific hereby certifies that the product identified below is manufactured and/or distributed according to the requirements of product and quality specifications as maintained in our quality management system which is compliant to ISO 13485 (BSI Certificate Number: FM 653694) or ISO 9001 (BSI Certificate Number: FM 743358) in Rochester, NY, USA.

*Alan E Hatch*

Alan E. Hatch  
Sr. Quality Manager  
06/17/2025

The following information represents Product Certification for: Item#: **374501**

Description: **1.8mL Ext Uncoded WP Uni Latch Rack**

Lot#: **1416891**

Use Before: **10/28/2026**

Manufactured: **10/28/2024**

Part Number	Description	Common Name	DMF#	Cytotoxicity	USP Class VI	FDA Compliance - 21 CFR
1-3830-91	VIAL,EXT THRD CRYO,1.8ML,FOIL BC	COMPONENT PART				
8-0028-04	RESIN,PPCO,RAD STER,INJ	POLYPROPYLENE COPOLYMER	7478	PASSED	PASSED	177.1520 (a)(3)(i) & (c)3.1(a)except for cooking, (useconditions C-H)
1-3830-89	Cap,Ext Thd Tube, WIP,INSPECTED	COMPONENT PART				
8-0028-04	RESIN,PPCO,RAD STER,INJ	POLYPROPYLENE COPOLYMER	7478	PASSED	PASSED	177.1520 (a)(3)(i) & (c)3.1(a)except for cooking, (useconditions C-H)
8-0005-22	RESIN,TPV,NAT,45 DURO SANTOPRENE	THERMOPLASTIC RUBBER	12719	PASSED	PASSED	N/A

If N/A appears in any of the columns above it means the information is not available. Any item listed as "COMPONENT PART" will show blank in the DMF#, Cytotoxicity, USP Class VI, and FDA Compliance Information columns.

If the word "PASSED" appears in the USP Class VI column next to the resin listing, this material has passed USP Class VI requirements, latest Volume, as part of our initial test approval protocol.

If the word "PASSED" appears in the Cytotoxicity column next to the resin listing, this material was tested and shown to be non-cytotoxic as part of our initial test approval protocol, using either mouse fibroblast L929 cells or the more sensitive human diploid lung cell lines WI-38 or MRC-5.

Product was E-Beamed Sterilized. Product was dosimetric released per ANSI/AAMI/ISO 11137 guidelines. Product was determined to be non-pyrogenic at a level < 0.5 EU/ml per USP < 85 >.

Product is certified to be free of detectable RNase/DNase contamination. This test is performed using the nuclease assay method with a detection limit of  $8 \times 10^{-7}$  Kunitz unit/ul for DNase and  $1.9 \times 10^{-10}$  Kunitz unit/ul for RNase.