CORNING

Certificate of Analysis

Product:	Fetal Bovine	e Serum	Descri	iption:	Premium, United States	Origin	
Catalog Number:	35-015-CF,	35-015-CV	Lot Nu	umber:	16522001		
Date of Manufacture:	15 JUN 202	2	Date c	of Expiration:	JUN 2027		
Country of Raw Material Origin:	United State	ted States Count Proces		ry of Final ssing:	United States		
Sterility Assurance Level:	10 ⁻³ (Triple (Filtered)).1 μm	Storaç	je:	-40°C to -10°C	2	
Test		Method		Specification	Results	Units	
Endotoxin		USP <85> & EP 2.6.7	14	≤ 5.0	<0.1	EU/mL	
Hemoglobin		USP <90>		≤ 25	5.32	mg/dL	
Mycoplasma		Barile and Kern & Hoechst Fluorochrom	na Stain	Not Detected	Not Detected	N/A	
Osmolality		USP <785> & EP 2.2		260 – 350	304	mOsm/kg H₂O	
pH		USP <791> & EP 2.2	.3	6.5 – 8.5	7.14	N/A	
Sterility (Bacteria & Fungi)		USP <71> & EP 2.6.7		No Growth	No Growth	N/A	
Total Protein		USP <1057> & EP 2.	5.33	3.0 – 4.5	3.5	g/dL	
Gamma-Glutamyl Transferase (GG	T)	Chemistry Analyzer		≤ 10	5	IU/L	
Cell Growth Performance Testing		MTT Assay		Passed	Passed	N/A	
Identification (Species ID)		EP 2.7.1		Bovine	Bovine	N/A	
Virus Testing		9 CFR Part 113.53c					
Bluetongue Virus				Not Detected	Not Detected	N/A	
Bovine Adenovirus 1 & 5				Not Detected	Not Detected	N/A	
Bovine Parvovirus				Not Detected	Not Detected	N/A	
Bovine Respiratory Syncytial Virus				Not Detected	Not Detected	N/A	
Bovine Viral Diarrhea Virus				As Reported	Not Detected	N/A	
Rabies Virus				Not Detected	Not Detected	N/A	
Reovirus				Not Detected	Not Detected	N/A	
Cytopathogenic Agents (IBR)				Not Detected	Not Detected	N/A N/A	
Hemadsorbing Agents (PI3) BVDV Serum Neutralization		Alpha Antibady Taat		Not Detected	Not Detected	N/A	
BVDV Serun Neutralization BVDV Antibody Type 1		Alpha Antibody Test		As Reported	10 ^{4.30}	TCID ₅₀ /mL	
BVDV Antibody Type 7 BVDV Antibody Type 2				As Reported	No Neutralization	N/A	
Biochemical Testing - Proteins & Organic Compounds							
Alkaline Phosphatase	game compoun			As Reported	260	IU/L	
Blood Urea Nitrogen (BUN)				As Reported	15	mg/dL	
Cholesterol				As Reported	26	mg/dL	
Creatinine				As Reported	2.8	mg/dL	
Glucose				As Reported	112	mg/dL	
Glutamic Oxaloacetic Transan	ninase (AST)			As Reported	34	IU/L	
Glutamic Pyruvic Transaminas	se (ALT)			As Reported	8	IU/L	
High Density Lipoprotein Chol	esterol (HDL)			As Reported	8	mg/dL	
Immunoglobulin G (IgG)		ELISA		As Reported	55.7	µg/mL	
Low Density Lipoprotein Chole	esterol (LDL)			As Reported	5	mg/dL	
Total Bilirubin				As Reported	0.2	mg/dL	
Triglyceride				As Reported	64	mg/dL	
Uric Acid				As Reported	3.5	mg/dL	

Mediatech, Inc. DBA J R Scientific 1242 Commerce Ave. Woodland, CA 95776 1-800-492-1110 www.corning.com

Biochemical Testing - Electrophoretic Profile	Cellulose Acetate Electrophoresis	Normal	Normal	N/A
Albumin		As Reported	2.1	g/dL
Alpha		As Reported	1.1	g/dL
Beta		As Reported	0.2	g/dL
Gamma		As Reported	0	g/dL
Biochemical Testing - Trace Metals				
Calcium		As Reported	13.1	mg/dL
Chloride		As Reported	98	mmol/L
Iron		As Reported	190	µg/dL
Magnesium		As Reported	3.2	mg/dL
Phosphorus		As Reported	9.7	mg/dL
Potassium		As Reported	12.2	mmol/L
Sodium		As Reported	137	mmol/L
Biochemical Testing - Hormones				
Cortisol		As Reported	<0.20	µg/dL
Insulin		As Reported	6.53	µIU/mL
Progesterone		As Reported	<0.1	ng/mL
Testosterone		As Reported	<0.01	ng/mL
Т3		As Reported	155	ng/dL
T4		As Reported	23.0	µg/dL

Notes:

For additional information on this Mediatech product, please contact our Technical Services department at (800) 492-1110 or via email at scientificsupport@corning.com.

This product was tested in accordance with Mediatech, Inc. specifications and procedures current as of date of manufacture. Testing procedures are maintained in compliance with the current versions of the USP and/or EP, where applicable.

Cell lines used in MTT Assay: 3T3, L929, MDCK and Vero. Cell lines used in 9CFR Part 113.53c virus testing: MDBK and Vero.

For research or further manufacturing uses only. Not for use as an excipient. Not for therapeutic or diagnostic uses. Not for human or animal consumption. Utilization of this product apart from the labeled intended use may be a violation of local and/or Federal Law.

Product meets European Union requirements for the production of technical blood products.

This product has been granted a Certificate of Suitability, R0-CEP 2018-271, by the European Directorate for the Quality of Medicines (EDQM) certifying that the product meets the criteria described in the current version of the monograph no. 1483 of the European Pharmacopoeia "Product with risk of transmitting agent of animal spongiform encephalopathies"

Origin and BSE/TSE Statements:

The aforementioned lot was manufactured from fetal bovine blood collected from government approved harvest facilities located in the United States, a country recognized by the United States Department of Agriculture - Animal and Plant Health Inspection Service (USDA-APHIS) and the World Organization for Animal Health (OIE) as having a negligible risk of Bovine Spongiform Encephalopathy (BSE), a bovine-specific Transmissible Spongiform Encephalopathy (TSE). All fetal bovine serum is derived from fetuses collected from healthy bovine cows and heifers that have passed ante and post mortem inspection and were found free of contagious diseases.

The following signatures indicate the above material has met all quality specifications and has been reviewed by a Quality representative.



