

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by TUV SUD America Inc.
Certificate Number. 951001163

Catalogue Number	022920
Lot Number	N27L701
Description	Chloroform, HPLC Grade, 99.5+% min
CAS Number	67-66-3
Quality Test/Release Date	12/Mar/2025
Suggested retest date	12/Mar/2028
Country of Origin	South Korea
Declaration of Origin	Synthetic
BSE/TSE	Not directly derived from or manufactured with any animal byproducts in any way (including but not limited to fermentation or nutrient broth, catalysts, enzymes).

Result Name	Units	Specifications	Test Value
Assay (GC)	%	> 99.5%	99.96
Comment	%	Ethanol, as stabilizer: 0.5 to 1.0%	0.7
Impurity content	ppt	GC-ECD responsive residue (single peak): ≤ 5ppt (As heptachlorepoide)	2
Water Content (Karl Fischer Titration)	%	≤ 0.03%	0.0004
Optical Absorbance at	AU	245 nm: ≤ 1.00 AU	0.69
Optical Absorbance at	AU	255 nm: ≤ 0.15 AU	0.10
Optical Absorbance at	AU	260 nm: ≤ 0.05 AU	0.04
Optical Absorbance at	AU	270 nm: ≤ 0.02 AU	0.01
Optical Absorbance at	AU	290 nm: ≤ 0.01 AU	0.002
Optical Absorbance at	AU	400 nm: ≤ 0.01 AU	0.001
Residue on Evaporation	ppm	≤ 3ppm	<0.3



John Astarita
Director, Quality

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.