

Test Report

– Eppendorf PCR clean & sterile –

ep Dualfilter T.I.P.S.[®] Reloads, BioBased



50 - 1250 µL L,
960 Tips (10 x 96
Eppendorf Tips in Trays)
REF 0030 081 102
GTIN 04043758040184
LOT 0219852H

 Eppendorf SE
Barkhausenweg 1
22339 Hamburg · Germany
eppendorf@eppendorf.com

PCR clean/ sterile

 2030-02-28

U.S. Pat. www.eppendorf.com/ip

 Read the instructions for use on
www.eppendorf.com/manuals

Distributed in North America by
Eppendorf North America, Inc. · USA
info@eppendorf.com
www.eppendorfn.com

0012 585 947-01

• Human DNA

Method: *real-time* PCR acc. to SOP 99880/V8
Limit: < 2 pg; less than one human cell

• DNase

Method: DNA Digestion acc. to SOP 100570/V4
Limit: Not detectable
(LOD: 1.0×10^{-7} Kunitz units)

• RNase

Method: RNA Digestion acc. to SOP 100571/V4
Limit: Not detectable
(LOD: 1.0×10^{-9} Kunitz units)

• PCR Inhibition

Method: *real-time* PCR acc. to SOP 100559/V4
Limit: less than 10 targets amplifiable

• Sterility

Method: Sterilization with SAL 10^{-6} by
 Irradiation according DIN EN ISO 11137
Test method: USP, Ph. Eur. 10.0 / 2.6.12

• Endotoxin

Method: Kinetic-chromogenic LAL test (Ph. Eur. 10.0 / 2.6.14)
Limit: < 0.001 EU/mL

Customer: Eppendorf SE, Barkhausenweg 1, D-22339 Hamburg

Date of sample receipt / examination: 18.03.25

Testing of the rinse solution of the above described lot showed conformity within the limits of detection.

25.03.25
Date of release

Epp 2803-5464
Registration number


Dr. rer. nat. Sybille Kuhnert (Head)

The test results refer exclusively to the items tested as arrived. The test report must not be copied partially without the approval of LADR GmbH.