

**CERTIFICATE OF ANALYSIS**

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by Intertek. Certificate Number. 2317548

Catalogue Number	16616		
Lot Number	A0483750		
Description	L-Methionine,98+%		
CAS Number	63-68-3		
Quality Test/Release Date	08/Jun/2026		
Suggested retest date	08/Jun/2031		
Country of Origin	CHINA		
Declaration of Origin	other		
BSE/TSE	made by fermentation		
Result Name	Units	Specifications	Test Value
Appearance (Color)		White	White
Appearance (Form)		Crystalline powder or crystals	Crystalline powder
Infrared spectrum		Conforms	Conforms
Titration with HClO4	%	98.0 to 102.0 (on dried basis)	99.8 (on dried basis)
Loss on drying	%	≤0.5 (1 g, 105°C)	(1 g, 105°C) (none detected)
Heavy metals (as Pb)	ppm	≤15	10
Sulfated ash	%	≤0.4	≤0.001
Specific optical rotation		+22.4° to +24.7° (20°C, 589 nm) (c=2, 6 N HCl)	+23.8° (20°C, 589 nm) (c=2, 6 N HCl)
pH		5.5 to 6.5 (1 % in water)	5.7 (1 % in water)
TLC	%	≤0.5 of any individual impurity	0.3 of any individual impurity
Chloride (Cl)	ppm	≤500	≤500
Sulfate (SO4)	ppm	≤300	≤300
Iron (Fe)	ppm	≤30	≤30

Geert Torfs  
Supervisor, QC

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.