

Test Report

– Eppendorf Biopur® –

epT.I.P.S.® Racks 50 - 1000 µL



5x 96 Eppendorf Tips
Eppendorf Biopur

LOT O2204211

2030-03-28

STERILE R

Order no.: 0030 075.250
Eppendorf SE
22331 Hamburg · Germany
Email: eppendorf@eppendorf.com

Cat. no.: 0030075250
Distributed in North America by
Eppendorf North America, Inc. · USA
Email: info@eppendorf.com

• Human DNA

Method: real-time PCR acc. to SOP 99880/V8
Limit: < 2 pg; less than one human cell

• Bacterial DNA

Method: real-time PCR acc. to SOP 100567/V5
Limit: < 50 fg; less than 10 *E. coli* cells

• DNase

Method: DNA Digestion acc. to SOP 100570/V4
Limit: Not detectable
(LOD: 1.0×10^{-7} Kunitz units)

• RNase

Method: RNA Digestion acc. to SOP 100571/V4
Limit: Not detectable
(LOD: 1.0×10^{-9} Kunitz units)

• PCR Inhibition

Method: real-time PCR acc. to SOP 100559/V4
Limit: Less than 10 targets amplifiable

• Sterility

Method: Sterilization with SAL 10^{-6} by
☑ Irradiation according DIN EN ISO 11137

Test method: USP, Ph. Eur. 10.0 / 2.6.12

• Endotoxin

Method: Kinetic-chromogenic LAL test (Ph. Eur. 10.0 / 2.6.14)
Limit: < 0.001 EU/mL

• ATP

Method: Pre-sterilization test / Bioburden test (Ph. Eur. 10.0 / 2.6.12)
Limit: < 5.5×10^{-12} mg

Customer: Eppendorf SE, Barkhausenweg 1, D-22339 Hamburg

Date of sample receipt / examination: 17.04.25

Testing of the rinse solution of the above described lot showed conformity within the limits of detection.

24.04.25

Date of release

Epp 2504-5623

Registration number

i.v. P. Kuhnert

Dr. rer. nat. Sybille Kuhnert (Head)

The test results refer exclusively to the items tested as arrived. The test report must not be copied partially without the approval of LADR GmbH.