


CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by Intertek. Certificate Number. 2317548

Catalogue Number 10279
Lot Number A0467551
Description Adenosine 5'-monophosphate,99%
CAS Number 61-19-8
Quality Test/Release Date 21/Nov/2024
Suggested retest date 21/Nov/2029
Country of Origin CHINA
Declaration of Origin other
BSE/TSE made by enzymatic hydrolysis from yeast RNA

Result Name	Units	Specifications	Test Value
Appearance (Color)		Colorless to white	White
Appearance (Form)		Crystalline powder	Crystalline powder
Infrared spectrum		Conforms	Conforms
UV spectrophotometry	%	>=98.0 (lambda max. 260 nm, pH 7)	98.4 (lambda max. 260 nm, pH 7)
UV spectrophotometry		molar absorptivity 15400 +/- 2%, on dry basis	molar absorptivity 15400 +/- 2%, on dry basis
HPLC	%	>=98.5	99.6
Loss on drying	%	=<6 (105°C, 5 hrs)	5.1 (105°C, 5 hrs)
Heavy metals (as Pb)	ppm	=<10	=<10
UV transmittance	%	>=95.0 (c=1, 0.2 N NaOH, 430 nm) 1 cm cell	99.2 (c=1, 0.2 N NaOH, 430 nm) 1 cm cell
Ratio of Absorbances		0.76 to 0.80 (A250/A260)	0.80 (A250/A260)
Ratio of Absorbances		0.14 to 0.16 (A280/A260)	0.16 (A280/A260)



Geert Torfs
Supervisor, QC

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.