

Certificate of Quality

Item Description: Overmolded Millex13 0.20Nylon NS 100PK P
 Catalogue Number: SLGNX13NL
 Lot Number: 0000242463

ISO 9001 Quality Standard

EMD Millipore Corporation certifies that the above-referenced product:

Was manufactured (or supplied) by a facility whose Quality Management System is approved by an accredited registering body to the appropriate ISO 9001 Quality Systems Standard.

Was manufactured in accordance with applicable document standard procedures.

Was tested in accordance with applicable documented quality specifications including: HPLC Extractable Analysis. HPLC analysis of 1 mL samples of both acetonitrile and water collected after discarding the first 1 mL of solvent showed no peaks greater in intensity than 0.004 AUFS (after the column frontal volume) at either 214 nm or 254 nm.

Catalogue Number	Pack Size	Membrane Type	Pore Size (µm)	Diameter	Typical Water Flow Rate at 21 degrees C and 2.1 bar (30 psi)	Bubble point
SLGNX13NL	100	Millex®-GN Nylon membrane, hydrophilic	0.2	13mm	18 mL/min	≥ 3.0 bar (≥ 43 psi)
SLGNX13NK	1000					
SLGNX13TL	100					
SLGN033NS	50					
SLGN033NB	250					
SLGN033NK	1000			33mm	75 mL/min	≥ 3.0 bar (≥ 43 psi)
SLHNX13NL	100	Millex®-HN Nylon membrane, hydrophilic	0.45	13mm	37 mL/min	≥ 2.2 bar (≥ 32 psi)
SLHNX13NK	1000					
SLHNX13TL	100					
SLHN033NS	50					
SLHN033NB	250					
SLHN033NK	1000			33mm	169 mL/min	≥ 2.2 bar (≥ 32 psi)

