

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by Intertek Global
Certificate Number: CERT-0120633

Catalogue Number	W8
Lot Number	261002
Description	WATER, UHPLC-MS GRADE
CAS Number	7732-18-5,Optima®
Quality Test/Release Date	14/Apr/2026
Suggested retest date	13/Apr/2031
Country of Origin	United States
Declaration of Origin	Inorganic-non animal
BSE/TSE	No animal products are used as starting raw material ingredients, or used in processing, including lubricants, processing aids, or any other material that might migrate to the finished product.

Result Name	Units	Specifications	Test Value
APPEARANCE		REPORT	Clear, colorless liquid
EVAPORATION RESIDUE	ppm	<= 1	1
IONIC IMPURITY - ALUMINUM (Al)	ppb	<= 2	<1
IONIC IMPURITY - CALCIUM (Ca)	ppb	<= 5	<1
IONIC IMPURITY - CHROMIUM (Cr)	ppb	<= 2	<1
IONIC IMPURITY - COPPER (Cu)	ppb	<= 5	<1
IONIC IMPURITY - IRON (Fe)	ppb	<= 2	<1
IONIC IMPURITY - LEAD (Pb)	ppb	<= 2	<1
IONIC IMPURITY - MAGNESIUM (Mg)	ppb	<= 2	<1
IONIC IMPURITY - MANGANESE (Mn)	ppb	<= 2	<1
IONIC IMPURITY - NICKEL (Ni)	ppb	<= 2	<1
IONIC IMPURITY - POTASSIUM (K)	ppb	<= 5	1
IONIC IMPURITY - SILVER (Ag)	ppb	<= 2	<1
IONIC IMPURITY - SODIUM (Na)	ppb	<= 20	3
IONIC IMPURITY - ZINC (Zn)	ppb	<= 2	<1
OPTICAL ABS AT 210 NM	AU	<= 0.01	<0.01
OPTICAL ABS AT 220 NM	AU	<= 0.01	<0.01
OPTICAL ABS AT 230 NM	AU	<= 0.01	<0.01
OPTICAL ABS AT 240 NM	AU	<= 0.01	<0.01
OPTICAL ABS AT 254 NM	AU	<= 0.005	<0.001
OPTICAL ABS AT 260 NM	AU	<= 0.005	<0.001
OPTICAL ABS AT 280 NM	AU	<= 0.005	<0.001
PROTEASE	DETECTED/ NOT DETECT.	= NOT DETECTED	NOT DETECTED
TOTAL HALOGEN	DETECTED/ NOT DETECT.	= NOT DETECTED	NOT DETECTED
UHPLC-MS GRAD. SUIT. NEG. (AS CHLORAMPHENICOL)	ppb	<= 25	<25
UHPLC-MS GRAD. SUIT. POS. (AS PROPAZINE)	ppb	<= 25	<25
UHPLC-UV GRAD. SUIT. PDA (200-400 NM)	mAU	<= 2	<2

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.

Additional Information HPLC/UHPLC-UV Gradient Suitability: Peak Height with PDA (200-400 nm) \leq 2 mAU



Harout Sahagian
QC Manager

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research use or further manufacturing. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.