

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by Intertek. Certificate Number. 2317548

Catalogue Number	15488		
Lot Number	A0328995		
Description	Cyclopropylamine,99%		
CAS Number	765-30-0		
Quality Test/Release Date	09/Jun/2026		
Suggested retest date	09/Jun/2029		
Country of Origin	CHINA		
Declaration of Origin	synthetic		
BSE/TSE	Not directly derived from or manufactured with any animal byproducts in any way (Including but not limited to fermentation or nutrient broth, catalysts, enzymes).		
Result Name	Units	Specifications	Test Value
Appearance		Clear and colourless, volatile liquid	Clear and colourless, volatile liquid
Infrared spectrum		Authentic	Authentic
Titration Total base	%	99 to 101	100.1
GC	%	>=99	99.6
Water	%	=<0.5	0.1
Refractive index		1.4190 to 1.4220 (20°C, 589 nm)	1.4195 (20°C, 589 nm)
GC			Ethylamine <0.1%
GC			n-Propylamine <0.1%
GC			Isopropylamine <0.1%
GC			Any other impurities <0.2%
GC			Total impurities (excluding GW410430X) <0.5%
Additional info			Producer: Zhejiang Sanhe Pharmachemco.
Manufacturing date			October 2012.

Geert Torfs
Supervisor, QC

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.